



current/voltage measuring module for dry-running protection of centrifugal pumps in hazardous areas, current setting 20...200 A voltage measurement up to 690 V, width 120 mm, straight-through transformer

product brand name	SIMOCODE
product designation	Current/voltage measuring module
General technical data	
measuring procedure	RMS value measurement
size of the circuit-breaker	S6
product function	<ul style="list-style-type: none"> • current measurement • voltage measurement • active power measurement • energy measurement • frequency measurement • active power monitoring for pump dry-run according to Ignition protection type Ex b
measuring procedure for current measurement	TRMS
current measuring range extension with external current transformers	No
measuring procedure for voltage measurement	TRMS
measurable supply voltage between the line conductors at AC maximum rated value	690 V
product component	<ul style="list-style-type: none"> • input for thermistor connection
consumed active power	0.5 W
insulation voltage	<ul style="list-style-type: none"> • with degree of pollution 3 at AC rated value • for wires of main circuit according to IEC 60947-1 rated value
surge voltage resistance rated value	6 000 V
shock resistance according to IEC 60068-2-27	15g / 11 ms; with basic unit snapped on
vibration resistance	1-6 Hz / 15 mm; 6-500 Hz / 2 g; with basic unit snapped on: 1g
Substance Prohibition (Date)	05/28/2009
SVHC substance name	Lead - 7439-92-1 Lead monoxide (lead oxide) - 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one - 71868-10-5
Net Weight	0.698 kg
Electromagnetic compatibility	
EMC emitted interference according to IEC 60947-1	class A
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
conducted interference	
• due to burst according to IEC 61000-4-4	2 kV
• due to conductor-earth surge according to IEC 61000-4-5	2 kV
• due to conductor-conductor surge according to IEC	1 kV

61000-4-5	
field-based interference according to IEC 61000-4-3	10 V/m
Inputs/ Outputs	
number of outputs as contact-affected switching element	0
Protective and monitoring functions	
product function	
• power factor monitoring	Yes
• ground-fault monitoring	Yes
• voltage detection	Yes
trip class	CLASS 5E
product function	
• current detection	Yes
• overload protection	Yes
Precision	
measuring precision	
• of frequency measurement	+/- 1.5 %, 15 A ... 400 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C
• for current measurement 1	+/- 1.5 %, in range 400 A ... 1600 A, in range 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), 50/60 Hz, 25 °C
• for current measurement 2	+/- 5 %, in range 400 A ... 1600 A, in range 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), 50/60 Hz, 25 °C
• for voltage measurement 1	+/- 1.5 %, in range 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), 50/60 Hz, 25 °C
• at cos phi-measurement 1	+/- 1.5 %, 15 A ... 400 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C
• at cos phi-measurement 2	+/- 5 %, 400 A ... 1600 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C
• for active power measurement 1	+/- 5 %, 15 A ... 400 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C
• for active power measurement 2	+/- 10 %, 400 A ... 1600 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C
• for energy measurement 1	+/- 5 %, 47 A ... 1260 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C
• for energy measurement 2	+/- 10 %, 400 A ... 1600 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C
• for apparent power measurement 1	+/- 3 %, 15 A ... 400 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C
• for apparent power measurement 2	+/- 5 %, 400 A ... 1600 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C
accuracy of ground-fault monitoring	In the range 30 % .. 120 %/Is: +/- 10 % (Class CI-A), in range 15 % .. 30 % le: +/- 25 % (Class CI-B), both values acc. to IEC 60947-1 Annex T
temperature drift per °C	0.01 %/°C; Reference temperature: 25°C
measured variable frequency	45 ... 65 Hz
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting
height	95 mm
width	120 mm
depth	145 mm
required spacing	
• top	30 mm
• bottom	30 mm
• left	0 mm
• right	0 mm
diameter of inlet opening	25 mm
diameter of inlet opening for current measurement	25 mm
Connections/ Terminals	
type of electrical connection	
• for main current circuit	straight-through transformers
• for auxiliary and control circuit	screw-type terminals
type of electrical connection at the measurement inputs for voltage	screw-type terminals
type of connectable conductor cross-sections at the	

measurement inputs for voltage		
• finely stranded with core end processing	1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1.5 mm ²)	
• solid	1x (0.5 ... 4 mm ²), 2x (0.5 ... 2.5 mm ²)	
• for AWG cables solid	1x (20 ... 12), 2x (20 ... 14)	
• for AWG cables stranded	1x (20 ... 14), 2x (20 ... 16)	
tightening torque at the measurement inputs for voltage	0.8 ... 1.2 N·m	
tightening torque [lbf·in] at the measurement inputs for voltage	7 ... 10.3 lbf·in	
Ambient conditions		
installation altitude at height above sea level		
• 1 maximum	2 000 m	
• 2 maximum	3 000 m; max. +50 °C (no protective separation)	
• 3 maximum	4 000 m; max. +40 °C (no protective separation)	
ambient temperature		
• during operation	-25 ... +60 °C	
• during storage	-40 ... +80 °C	
• during transport	-40 ... +80 °C	
environmental category		
• during operation according to IEC 60721	3K6 (no formation of ice, no condensation, relative humidity 10 ... 95%), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6	
• during storage according to IEC 60721	1K6 (no condensation, relative humidity 10 ... 95%), 1C2 (no salt mist), 1S2 (sand must not get into the devices), 1M4	
• during transport according to IEC 60721	2K2, 2C1, 2S1, 2M2	
relative humidity during operation	10 ... 95 %	
Short-circuit protection		
product function short circuit protection	No	
IEC 61508		
Safety Integrity Level (SIL) according to IEC 61508	1	
ATEX		
certificate of suitability		
• IECEx	Yes; IECEx PTB 18.0004X	
• according to ATEX directive 2014/34/EU	BVS 06 ATEX F001, PTB 18 ATEX 5003 X	
• according to UKCA	ITS21UKEX0464, ITS21UKEX0455X	
explosion device group and category according to ATEX directive 2014/34/EU	II (2) G, II (2) D, I (M2) / I (M2), II (1/2) G, II (1G/2D)	
Galvanic isolation		
(electrically) protective separation according to IEC 60947-1	All circuits with protective separation (double creepage paths and clearances), the information in the "Protective Separation" test report, No. A0258, must be observed (link see further information)	
Main circuit		
number of poles for main current circuit	3	
adjustable current response value current of the current-dependent overload release	20 ... 200 A	
operating voltage		
• at AC		
— at 50 Hz rated value	110 ... 690 V	
— at 60 Hz rated value	110 ... 690 V	
operating frequency rated value	50 ... 60 Hz	
Control circuit/ Control		
type of voltage	AC	
inrush current maximum	2 000 A; 10 x Io	
Approvals Certificates		
General Product Approval		EMV



**UK
CA**

CE
EG-Konf.

UL
UL

EAC

RCM

EMV

For use in hazardous locations

[KC](#)



IECEx

ATEX



IECEx

IECEx

[Miscellaneous](#)

[Test Certificates](#)

[Maritime application](#)

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

[Special Test Certificate](#)



LRS

[Maritime application](#)

[other](#)

[Environment](#)

[Industrial Communication](#)



[Confirmation](#)



[Environmental Confirmations](#)



Profibus

[Further information](#)

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UF7123-1AA01-0>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UF7123-1AA01-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3UF7123-1AA01-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UF7123-1AA01-0&lang=en



