



SITOP PSU200M/1-2AC/24VDC/10A

SITOP PSU200M 10 A stabilized power supply input: 120/230-500 V AC output: 24 V DC/10 A

Technical Product Detail Page

<https://i.siemens.com/1P6EP1334-3BA10>

input	
type of the power supply network	1-phase and 2-phase AC
supply voltage at AC	Set by means of selector switch on the device
supply voltage 1 at AC	120 ... 230 V
supply voltage 2 at AC	230 ... 500 V
input voltage 1 at AC	85 ... 264 V
input voltage 2 at AC	176 ... 550 V
wide range input	Yes
overvoltage overload capability	1300 Vpeak, 1.3 ms
buffering time for rated value of the output current in the event of power failure minimum	25 ms
operating condition of the mains buffering	at Vin = 120/230 V, typ. 150 ms at Vin = 400 V
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 120 V	4.4 A
• at rated input voltage 230 V	2.4 A
• at rated input voltage 500 V	1.1 A
current limitation of inrush current at 25 °C maximum	35 A
I _{2t} value maximum	4 A ² ·s
fuse protection type	T 6.3 A (not accessible)
fuse protection type in the feeder	Recommended miniature circuit breaker at 1-phase operation: from 6 A (10 A) characteristic C (B); required at 2-phase operation: circuit breaker 2-pole connected or circuit breaker 3RV2011-1EA10 (setting 3.8 A) or 3RV2711-1ED10 (UL 489) at 230 V; 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489) at 400/500 V
output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
output voltage adjustable	Yes; via potentiometer
adjustable output voltage	24 ... 28.8 V
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	0.1 %
residual ripple	
• maximum	50 mV

voltage peak	200 mV
• maximum	
display version for normal operation	Green LED for 24 V OK
type of signal at output	relay contact (normally open, contact rating (SELV (ES1) must be observed): 30 V DC/0.1 A
behavior of the output voltage when switching on	Overshoot of Vout approx. 3 %
response delay maximum	1 s
voltage increase time of the output voltage	
• typical	50 ms
output current	
• rated value	10 A
• rated range	0 ... 10 A; +60 ... +70 °C: Derating 2%/K (at 120 V, 230 V) or 3.5%/K (at 400 V)
supplied active power typical	240 W
short-term overload current	
• at short-circuit during operation typical	30 A
duration of overloading capability for excess current	
• at short-circuit during operation	25 ms
constant overload current	
• on short-circuiting during the start-up typical	12 A
bridging of equipment	Yes; switchable characteristic
number of parallel-switched equipment resources for increasing the power	2
efficiency	
efficiency in percent	91 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	24 W
• during no-load operation maximum	6 W
closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.1 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	3 %
setting time	
• load step 50 to 100% typical	2 ms
• load step 100 to 50% typical	2 ms
setting time	
• maximum	5 ms
protection and monitoring	
design of the overvoltage protection	< 35 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Alternatively, constant current characteristic approx. 12 A or latching shutdown
• typical	12 A
enduring short circuit current RMS value	
• typical	12 A
display version for overload and short circuit	LED yellow for "overload", LED red for "latching shutdown"
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Safety extra-low output voltage Uout acc. to EN 60950-1 and EN 50178
operating resource protection class	Class I
leakage current	
• maximum	3.5 mA
• typical	0.32 mA
protection class IP	IP20
EMC	
standard	
• for emitted interference	EN 55022 Class B
• for mains harmonics limitation	EN 61000-3-2
• for interference immunity	EN 61000-6-2
standards, specifications, approvals	

certificate of suitability	<ul style="list-style-type: none"> CE marking UL approval UKCA marking EAC approval Regulatory Compliance Mark (RCM) NEC Class 2 SEMI F47 	Yes Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 Yes Yes Yes No Yes	
type of certification	<ul style="list-style-type: none"> BIS CB-certificate 	Yes; R-41183539 Yes	
MTBF at 40 °C	1 055 408 h		
standards, specifications, approvals hazardous environments			
certificate of suitability	<ul style="list-style-type: none"> IECEx ATEX ULhazloc approval FM registration 	No No No No	
standards, specifications, approvals marine classification			
shipbuilding approval	Yes		
Marine classification association	<ul style="list-style-type: none"> American Bureau of Shipping Europe Ltd. (ABS) French marine classification society (BV) Det Norske Veritas (DNV) Lloyds Register of Shipping (LRS) 		
standards, specifications, approvals Environmental Product Declaration			
Environmental Product Declaration	Yes		
global warming potential [CO2 eq]	<ul style="list-style-type: none"> total during manufacturing during operation after end of life 	763.9 kg 12.6 kg 751 kg 0.18 kg	
ambient conditions			
ambient temperature	<ul style="list-style-type: none"> during operation during transport during storage 		
	-25 ... +70 °C; With natural convection; startup tested starting from -40 °C nominal voltage -40 ... +85 °C -40 ... +85 °C		
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation		
connection method			
type of electrical connection	<ul style="list-style-type: none"> at input at output for auxiliary contacts 	screw terminal L, N, PE: 1 screw terminal each for 0.2 ... 2.5 mm ² single-core/finely stranded +, -: 2 screw terminals each for 0.2 ... 2.5 mm ² 13, 14 (alarm signal): 1 screw terminal each for 0.14 ... 1.5 mm ²	
mechanical data			
width × height × depth of the enclosure	70 × 125 × 121 mm		
installation width × mounting height	70 mm × 225 mm		
required spacing	<ul style="list-style-type: none"> top bottom left right 	50 mm 50 mm 0 mm 0 mm	
fastening method	<ul style="list-style-type: none"> DIN-rail mounting S7 rail mounting wall mounting 		
housing can be lined up	Yes		
net weight	0.8 kg		
accessories			

electrical accessories	Buffer module																																										
further information internet links																																											
internet link	<ul style="list-style-type: none"> • to website: Industry Mall • to web page: selection aid TIA Selection Tool • to web page: power supplies • to website: CAx-Download-Manager • to website: Industry Online Support 																																										
identification link	Yes; acc. to IEC 61406-1:2022																																										
additional information																																											
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)																																										
security information																																											
security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)</p>																																										
Classifications																																											
	<table border="1"> <thead> <tr> <th></th> <th>Version</th> <th>Classification</th> </tr> </thead> <tbody> <tr> <td>eClass</td> <td>14</td> <td>27-04-07-01</td> </tr> <tr> <td>eClass</td> <td>12</td> <td>27-04-07-01</td> </tr> <tr> <td>eClass</td> <td>9.1</td> <td>27-04-07-01</td> </tr> <tr> <td>eClass</td> <td>9</td> <td>27-04-07-01</td> </tr> <tr> <td>eClass</td> <td>8</td> <td>27-04-90-02</td> </tr> <tr> <td>eClass</td> <td>7.1</td> <td>27-04-90-02</td> </tr> <tr> <td>eClass</td> <td>6</td> <td>27-04-90-02</td> </tr> <tr> <td>ETIM</td> <td>10</td> <td>EC002540</td> </tr> <tr> <td>ETIM</td> <td>9</td> <td>EC002540</td> </tr> <tr> <td>ETIM</td> <td>8</td> <td>EC002540</td> </tr> <tr> <td>ETIM</td> <td>7</td> <td>EC002540</td> </tr> <tr> <td>IDEA</td> <td>4</td> <td>4130</td> </tr> <tr> <td>UNSPSC</td> <td>15</td> <td>39-12-10-04</td> </tr> </tbody> </table>		Version	Classification	eClass	14	27-04-07-01	eClass	12	27-04-07-01	eClass	9.1	27-04-07-01	eClass	9	27-04-07-01	eClass	8	27-04-90-02	eClass	7.1	27-04-90-02	eClass	6	27-04-90-02	ETIM	10	EC002540	ETIM	9	EC002540	ETIM	8	EC002540	ETIM	7	EC002540	IDEA	4	4130	UNSPSC	15	39-12-10-04
	Version	Classification																																									
eClass	14	27-04-07-01																																									
eClass	12	27-04-07-01																																									
eClass	9.1	27-04-07-01																																									
eClass	9	27-04-07-01																																									
eClass	8	27-04-90-02																																									
eClass	7.1	27-04-90-02																																									
eClass	6	27-04-90-02																																									
ETIM	10	EC002540																																									
ETIM	9	EC002540																																									
ETIM	8	EC002540																																									
ETIM	7	EC002540																																									
IDEA	4	4130																																									
UNSPSC	15	39-12-10-04																																									

Approvals Certificates
General Product Approval



[Manufacturer Declara-
tion](#)

[Declaration of Con-
formity](#)



[China RoHS](#)

General Product Approval

Maritime application



[Miscellaneous](#)

[BIS CRS](#)





last modified:

12/12/2025 