



SITOP DC UPS Module/24VDC/6A/USB

SITOP DC UPS module 24 V/6 A uninterruptible power supply with USB interface
input: 24 V DC/6.85 A output: 24 V DC/6 A

Technical Product Detail Page

<https://i.siemens.com/1P6EP1931-2DC42>

input	
supply voltage at DC rated value	24 V
input voltage at DC	22 ... 29 V
adjustable response value voltage for buffer connection preset	22.5 V
adjustable response value voltage for buffer connection	22 ... 25.5 V; Adjustable in 0.5 V increments
input current at rated input voltage 24 V rated value	6 A; + approx. 0.6 A with empty battery
memory	
type of energy storage	with batteries
design of the mains power cut bridging-connection	Dependent on connected battery and load current, see selection table battery module and mains buffering times as well as the relevant important information notes!
output	
output voltage	
• in normal operation at DC rated value	24 V
• in buffering mode at DC rated value	24 V
formula for output voltage	$V_{in} - \text{approx. } 0.5 \text{ V}$
startup delay time typical	1 s
voltage increase time of the output voltage typical	60 ms
output voltage in buffering mode at DC	19 ... 28.5 V
output current	
• rated value	6 A
• in normal operation	0 ... 6 A
• in buffering mode	0 ... 6 A
peak current	6.3 A
property of the output short-circuit proof	Yes
charging current	0.2 A, 0.4 A
efficiency	
efficiency in percent	
• at rated output voltage for rated value of the output current typical	95 %
• in case of operation on rechargeable battery typical	94.5 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	7 W
• in case of operation on rechargeable battery typical	8 W
supplied active power typical	144 W
protection and monitoring	
product function	
• reverse polarity protection against energy storage unit	Yes

polarity reversal	Yes
• reverse polarity protection against input voltage polarity reversal	
display version	<p>Normal operation: LED green (OK), floating changeover contact "Bat/OK" to setting "OK" ("OK" means: Voltage of the supplying power supply unit is greater than cut-in threshold set at the DC UPS module); Lack of buffer standby: LED red (alarm), floating changeover contact "Alarm/Bat" to setting "Alarm"; Battery replacement required: LED red (alarm) flashing with approx. 0.25 Hz, floating changeover contact "Alarm/Bat" switching with approx. 0.25 Hz; Energy storage > 85%: LED green (Bat > 85%), floating NO contact "Bat > 85" closed; Permissible contact current capacity: DC 60 V/1 A or AC 30 V /1 A</p> <p>Buffered mode: LED yellow (Bat), floating changeover contact "OK/Bat" to setting "Bat"; Prewarning battery voltage < 20.4 VDC: LED red (alarm), floating changeover contact "Alarm/Bat" to setting "Alarm"; Energy storage > 85%: LED green (Bat > 85%), floating NO contact "Bat > 85" closed</p>
interfaces	
product component PC interface	Yes
product function communication function	No
design of the interface	USB
safety	
galvanic isolation between input and output	No
operating resource protection class	Class III
protection class IP	IP20
standard	
• for emitted interference	EN 55022 Class B
• for interference immunity	EN 61000-6-2
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
• EAC approval	Yes
MTBF at 40 °C	904 159 h
standards, specifications, approvals marine classification	
shipbuilding approval	Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• Det Norske Veritas (DNV)	Yes
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	221.8 kg
• during manufacturing	18.5 kg
• during operation	202.8 kg
• after end of life	0.34 kg
ambient conditions	
ambient temperature	
• during operation	-25 ... +60 °C; with natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection	screw terminal
• at input	24 V DC: 2 screw terminals for 1 ... 4 mm ² /17 ... 11 AWG
• at output	24 V DC: 4 screw terminals for 1 ... 4 mm ² /17 ... 11 AWG
• for rechargeable battery module	24 V DC: 2 screw terminals for 1 ... 4 mm ² /17 ... 11 AWG
• for control circuit and status message	10 screw terminals for 0.5 ... 2.5 mm ² /20 ... 13 AWG
mechanical data	
width x height x depth of the enclosure	50 x 125 x 125 mm
installation width x mounting height	50 mm x 225 mm
required spacing	
• top	50 mm

• bottom	50 mm	
• left	0 mm	
• right	0 mm	
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15	
• DIN-rail mounting	Yes	
• S7 rail mounting	No	
• wall mounting	No	
housing can be lined up	Yes	
net weight	0.45 kg	
accessories		
electrical accessories	Battery module	
further information internet links		
internet link	<ul style="list-style-type: none"> • to website: Industry Mall https://mall.industry.siemens.com • to web page: selection aid TIA Selection Tool https://www.siemens.com/tstcloud • to web page: power supplies https://siemens.com/sitop • to website: CAx-Download-Manager https://siemens.com/cax • to website: Industry Online Support https://support.industry.siemens.com 	
additional information		
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	
security information		
security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)</p>	
Classifications		
	Version	Classification
eClass	14	27-04-07-05
eClass	12	27-04-07-05
eClass	9.1	27-04-07-05
eClass	9	27-04-07-05
eClass	8	27-04-06-90
eClass	7.1	27-04-06-90
eClass	6	27-04-06-90
ETIM	10	EC000382
ETIM	9	EC000382
ETIM	8	EC000382
ETIM	7	EC000382
IDEA	4	4149
UNSPSC	15	39-12-10-11
Approvals Certificates		
General Product Approval		

[Manufacturer Declaration](#)

[Declaration of Conformity](#)



[China RoHS](#)



[Miscellaneous](#)

Maritime application

Environment



last modified:

12/8/2025