

**Siemens**  
EcoTech



SITOP PSE200U/4X0.5-3A/SEO

SITOP PSE200U 3 A selectivity module 4-channel input: 24 V DC/12 A output: 24 V DC/4x 3 A threshold value adjustable 0.5-3 A with status message for each output

Technical Product Detail Page

<https://i.siemens.com/1P6EP1961-2BA31>

input	
type of the power supply network	Controlled DC voltage
supply voltage at DC rated value	24 V
input voltage at DC	22 ... 30 V
overvoltage overload capability	35 V
input current at rated input voltage 24 V rated value	12 A
output	
voltage curve at output	controlled DC voltage
formula for output voltage	$V_{out} = V_{in} - \text{approx. } 0.2 \text{ V}$
relative overall tolerance of the voltage note	In accordance with the supplying input voltage
number of outputs	4
output current up to 60 °C per output rated value	3 A
adjustable current response value current of the current-dependent overload release	0.5 ... 3 A
type of response value setting	via potentiometer
response delay maximum	5 s
product feature parallel switching of outputs	No
type of outputs connection	Simultaneous connection of all outputs after power up of the supply voltage > 20 V, delay time of 25 ms, 100 ms or adjustable "load optimised" via DIP switch for sequential connection
efficiency	
efficiency in percent	97 %
power loss [W] at rated output voltage for rated value of the output current typical	9 W
switch-off characteristic	
switching characteristic	<ul style="list-style-type: none"> <li>• of the excess current</li> <li>• of the current limitation</li> <li>• of the immediate switch-off</li> </ul>
	$I_{out} = 1.0 \dots 1.5 \times \text{set value}$ , switch-off after approx. 5 s
	$I_{out} = 1.5 \times \text{set value}$ , switch-off after typ. 100 ms
	$I_{out} > \text{set value}$ and $V_{in} < 20 \text{ V}$ , switch-off after approx. 0.5 ms
residual current at switch-off typical	1 mA
design of the reset device/resetting mechanism	via sensor per output
remote reset function	Non-electrically isolated 24 V input (signal level "high" at > 15 V)
protection and monitoring	
fuse protection type at input	5 A per output (not accessible)
display version for normal operation	Three-color LED per output: green LED for "Output switched through"; yellow LED for "Output switched off manually"; red LED for "Output switched off due to overcurrent"

design of the switching contact for signaling function	Status signal output (pulse/pause signal, can be evaluated via Simatic function block)
<b>safety</b>	
galvanic isolation between input and output at switch-off	No
standard for safety	according to EN 62368-1
operating resource protection class	Class III
protection class IP	IP20
standard	
• for emitted interference	EN 55022 Class B
• for interference immunity	EN 61000-6-2
<b>standards, specifications, approvals</b>	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; UL-Recognized (UL 2367) File E328600; cULus-Listed (UL 508, CSA C22.2 No. 107.1) File E197259
• UKCA marking	Yes
• EAC approval	Yes
type of certification	
• CB-certificate	Yes
MTBF at 40 °C	755 915 h
<b>standards, specifications, approvals hazardous environments</b>	
certificate of suitability	
• IECEx	No
• ATEX	No
<b>standards, specifications, approvals marine classification</b>	
shipbuilding approval	Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• Det Norske Veritas (DNV)	Yes
<b>standards, specifications, approvals Environmental Product Declaration</b>	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	290.7 kg
• during manufacturing	8.8 kg
• during operation	281.7 kg
• after end of life	0.2 kg
Siemens Eco Profile (SEP)	Siemens EcoTech
<b>ambient conditions</b>	
ambient temperature	
• during operation	-25 ... +60 °C; with natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
<b>connection method</b>	
type of electrical connection	screw terminal
• at input	+24 V: 2 screw terminals for 0.5 ... 16 mm <sup>2</sup> ; 0 V: 2 screw terminals for 0.5 ... 4 mm <sup>2</sup>
• at output	Output 1 ... 4: 1 screw terminal each for 0.5 ... 4 mm <sup>2</sup>
• for auxiliary contacts	Remote reset: 1 screw terminal for 0.5 ... 4 mm <sup>2</sup>
• for signaling contact	1 screw terminal for 0.5 ... 4 mm <sup>2</sup>
<b>mechanical data</b>	
width x height x depth of the enclosure	72 x 80 x 72 mm
installation width x mounting height	72 mm x 180 mm
required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15

• DIN-rail mounting	Yes
• S7 rail mounting	No
• wall mounting	No
housing can be lined up	Yes

net weight	0.2 kg
------------	--------

#### accessories

mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20
------------------------	---

#### further information internet links

internet link	<ul style="list-style-type: none"> <li>• to website: Industry Mall</li> <li>• to web page: selection aid TIA Selection Tool</li> <li>• to web page: power supplies</li> <li>• to website: CAx-Download-Manager</li> <li>• to website: Industry Online Support</li> </ul>
identification link	Yes; acc. to IEC 61406-1:2022

#### additional information

other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
-------------------	---

#### security information

security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit <a href="http://www.siemens.com/cybersecurity-industry">www.siemens.com/cybersecurity-industry</a>. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <a href="https://www.siemens.com/cert">https://www.siemens.com/cert</a>. (V4.7)</p>
----------------------	---

#### Classifications

	Version	Classification
eClass	14	27-37-18-02
eClass	12	27-37-18-02
eClass	9.1	27-37-18-02
eClass	9	27-37-18-02
eClass	8	27-37-18-02
eClass	7.1	27-37-18-02
eClass	6	27-37-18-02
ETIM	10	EC001440
ETIM	9	EC001440
ETIM	8	EC001440
ETIM	7	EC001440
IDEA	4	4727
UNSPSC	15	39-12-15-21

#### Approvals Certificates

##### General Product Approval



[Manufacturer Declaration](#)



EG-Konf.



[Declaration of Conformity](#)

[China RoHS](#)

[Miscellaneous](#)

last modified:

12/12/2025