

## Data sheet

## 6EP3436-7SC00-3AX0



SITOP PSU6200/3AC/24VDC/20A/EX

SITOP PSU6200 Ex 24 V/20 A stabilized power supply input: 400 - 500 V AC  
output: 24 V DC/20 A with diagnostic interface with painted printed-circuit boards

Technical Product Detail Page

<https://i.siemens.com/1P6EP3436-7SC00-3AX0>

input	
type of the power supply network	3-phase AC or DC
supply voltage at AC	
• minimum rated value	400 V
• maximum rated value	500 V
• initial value	323 V
• full-scale value	576 V
supply voltage at DC	500 ... 550 V
input voltage at DC	450 ... 600 V
buffering time for rated value of the output current in the event of power failure minimum	25 ms
operating condition of the mains buffering	at $V_{in} = 400$ V
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 400 V	0.77 A
• at rated input voltage 500 V	0.62 A
current limitation of inrush current at 25 °C maximum	17 A
fuse protection type in the feeder	three-poled coupled circuit breaker from 4 A characteristic C to 16 A characteristic C or circuit breaker 3RV2011-1EA10 (setting 4 A) or 3RV2711-1ED10 (UL 489)
output	
voltage curve at output	Controlled, isolated DC voltage
number of outputs	1
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
output voltage adjustable	Yes; via potentiometer
adjustable output voltage	24 ... 28 V; max. 480 W (576 W up to 45°C)
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.2 %
• on slow fluctuation of ohm loading	0.1 %
residual ripple	
• maximum	30 mV
• typical	20 mV
voltage peak	
• maximum	30 mV
• typical	20 mV

display version for normal operation	Green LED for 24 V OK
type of signal at output	Electronic contact (NO contact, contact rating 30 V DC/0.1 A) for DC O.K. or diagnostic interface
behavior of the output voltage when switching on	Overshoot of Vout < 2 %
response delay maximum	0.5 s
voltage increase time of the output voltage	
• typical	100 ms
output current	
• rated value	20 A
• rated range	0 ... 20 A; 24 A up to +45°C; +60 ... +70 °C: Derating 3%/K
supplied active power typical	480 W
short-term overload current	
• on short-circuiting during the start-up typical	24 A
• at short-circuit during operation typical	24 A
parallel switching of outputs	can be set with DIP switch
bridging of equipment	Yes; switchable characteristic
number of parallel-switched equipment resources for increasing the power	2
<b>efficiency</b>	
efficiency in percent	95.9 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	23 W
• during no-load operation maximum	2.9 W
<b>closed-loop control</b>	
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	3 %
setting time	
• load step 10 to 90% typical	2 ms
• load step 90 to 10% typical	2 ms
• maximum	3 ms
<b>protection and monitoring</b>	
design of the overvoltage protection	< 32 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Shutdown and periodic restart attempts
• typical	24 A
overcurrent overload capability	
• in normal operation	overload capability 150 % Iout rated up to 5 s/min
<b>safety</b>	
galvanic isolation between input and output	Yes
galvanic isolation	ES1 output voltage Vout according to EN 62368-1
operating resource protection class	Class I
leakage current	
• maximum	3.5 mA
protection class IP	IP20
<b>EMC</b>	
standard	
• for emitted interference	EN 55022 Class B
• for mains harmonics limitation	EN 61000-3-2
• for interference immunity	EN 61000-6-2
<b>standards, specifications, approvals</b>	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
• UKCA marking	Yes
• EAC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
• NEC Class 2	No
• SEMI F47	Yes

type of certification		Yes; R-41188271
• BIS		Yes
<b>standards, specifications, approvals hazardous environments</b>		
certificate of suitability		Yes; IECEx Ex ec IIC T4 Gc
• IECEx		Yes; ATEX (EX) II 3G Ex ec IIC T4 Gc
• ATEX		Yes
• ULhazloc approval		Yes
• UKEX		Yes
• CCC for hazardous zone according to GB standard		Yes
• FM registration		No
<b>standards, specifications, approvals marine classification</b>		
shipbuilding approval		Yes
<b>Marine classification association</b>		
• American Bureau of Shipping Europe Ltd. (ABS)		Yes
• French marine classification society (BV)		No
• Det Norske Veritas (DNV)		Yes
• Lloyds Register of Shipping (LRS)		No
<b>standards, specifications, approvals Environmental Product Declaration</b>		
Environmental Product Declaration		Yes
global warming potential [CO2 eq]		
• total		749 kg
• during manufacturing		28 kg
• during operation		720 kg
• after end of life		0.7 kg
<b>ambient conditions</b>		
ambient temperature		
• during operation		-30 ... +70 °C; with natural convection a monotonically increasing start-up from -25 °C, safe start-up from -40 °C
• during transport		-40 ... +85 °C
• during storage		-40 ... +85 °C
environmental category according to IEC 60721		Climate class 3K3, 5 ... 95% no condensation
<b>connection method</b>		
type of electrical connection		push-in terminals
• at input		L1, L2, L3, PE: push-in for 0.5 ... 10 mm <sup>2</sup>
• at output		+1, +2, -1, -2, -3: push-in for 0.5 ... 6 mm <sup>2</sup>
• for auxiliary contacts		13, 14 (alarm signal): 1 push-in terminal each for 0.2 ... 1.5 mm <sup>2</sup>
<b>mechanical data</b>		
width x height x depth of the enclosure		70 x 135 x 155 mm
installation width x mounting height		70 mm x 225 mm
required spacing		
• top		45 mm
• bottom		45 mm
• left		0 mm
• right		0 mm
fastening method		Snaps onto DIN rail EN 60715 35x7.5/15
• DIN-rail mounting		Yes
• S7 rail mounting		No
• wall mounting		No
housing can be lined up		Yes
net weight		1.5 kg
<b>accessories</b>		
electrical accessories		Buffer module, redundancy module
mechanical accessories		Identification labels SIMATIC ET 200SP 6ES7193-6LF30-0AW0
<b>further information internet links</b>		
internet link		
• to website: Industry Mall		<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
• to web page: selection aid TIA Selection Tool		<a href="https://www.siemens.com/tstcloud">https://www.siemens.com/tstcloud</a>
• to web page: power supplies		<a href="https://siemens.com/sitop">https://siemens.com/sitop</a>

• to website: CAx-Download-Manager	<a href="https://siemens.com/cax">https://siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
identification link	Yes; acc. to IEC 61406-1:2022
<b>additional information</b>	
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
<b>security information</b>	
security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit <a href="http://www.siemens.com/cybersecurity-industry">www.siemens.com/cybersecurity-industry</a>. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <a href="https://www.siemens.com/cert">https://www.siemens.com/cert</a>. (V4.7)</p>

## Classifications

	Version	Classification
eClass	14	27-04-07-01
eClass	12	27-04-07-01
eClass	9.1	27-04-07-01
eClass	9	27-04-07-01
eClass	8	27-04-90-02
eClass	7.1	27-04-90-02
eClass	6	27-04-90-02
ETIM	10	EC002540
ETIM	9	EC002540
ETIM	8	EC002540
ETIM	7	EC002540
IDEA	4	4130
UNSPSC	15	39-12-10-04

## Approvals Certificates

### General Product Approval

[Manufacturer Declaration](#)



[Declaration of Conformity](#)

[China RoHS](#)



### General Product Approval



[BIS CRS](#)



### For use in hazardous locations

### For use in hazardous locations

### Maritime application

### Environment

[CCC-Ex](#)



---

last modified:

11/14/2025