

Siemens
EcoTech



SIMATIC ET 200SP, Analog input module, AI 8xI 2-/4-wire Basic, suitable for BU type A0, A1, Color code CC01, Module diagnostics, 16 bit

General information	
Product type designation	AI 8xI 2-/4-wire BA
HW functional status	FS23 or higher
Firmware version	V2.0.0
• FW update possible	Yes
usable BaseUnits	BU type A0, A1
Color code for module-specific color identification plate	CC01
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
• Measuring range scalable	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	TIA Portal V21
• STEP 7 configurable/integrated from version	V5.7 SP3
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.45
Operating mode	
• Oversampling	No
• MSI	No
CiR - Configuration in RUN	
Reparameterization possible in RUN	No
Calibration possible in RUN	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	25 mA; rated voltage, all channels active, no load
Current consumption, max.	725 mA; worst case voltage, all channels active, max. load, no derating
Encoder supply	
24 V encoder supply	
• 24 V	Yes
• Short-circuit protection	Yes
• Output current, max.	0.7 A; total current of all encoders/channels
Power loss	

Power loss, typ.	0.7 W; rated voltage, 50 % active channels, 50 % of range
Address area	
Address space per module	
• Address space per module, max.	16 byte
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	
• 1-wire connection	BU type A0, A1
• 2-wire connection	BU type A0, A1
• 4-wire connection	BU type A0, A1 + potential distributor module
Analog inputs	
Number of analog inputs	8; Single-ended
• For current measurement	8
permissible input current for current input (destruction limit), max.	50 mA
Cycle time (all channels), min.	1 ms; per channel
Input ranges (rated values), currents	
• 0 to 20 mA	Yes
— Input resistance (0 to 20 mA)	100 Ω; 15 bit
• -20 mA to +20 mA	Yes
— Input resistance (-20 mA to +20 mA)	100 Ω; 16 bit incl. sign
• 4 mA to 20 mA	Yes
— Input resistance (4 mA to 20 mA)	100 Ω; 15 bit
Cable length	
• shielded, max.	200 m
Analog value generation for the inputs	
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Integration time, parameterizable	Yes
• Interference voltage suppression for interference frequency f1 in Hz	16.67 / 50 / 60 / 4 800 (16.67 / 50 / 60)
• Conversion time (per channel)	180 / 60 / 50 / 0.625 (67.5 / 22.5 / 18.75) ms
Smoothing of measured values	
• Number of smoothing levels	4
• parameterizable	Yes
• Step: None	Yes
• Step: low	Yes; 4x smoothing
• Step: Medium	Yes; 8x smoothing
• Step: High	Yes; 16x smoothing
Encoder	
Connection of signal encoders	
• for voltage measurement	No
• for current measurement as 2-wire transducer	Yes
— Burden of 2-wire transmitter, max.	650 Ω
• for current measurement as 4-wire transducer	Yes
Errors/accuracies	
Linearity error (relative to input range), (+/-)	0.01 %
Temperature error (relative to input range), (+/-)	0.005 %/K
Crosstalk between the inputs, min.	50 dB
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.05 %
Operational error limit in overall temperature range	
• Current, relative to input range, (+/-)	0.5 %
Basic error limit (operational limit at 25 °C)	
• Current, relative to input range, (+/-)	0.3 %
Interference voltage suppression for $f = n \times (f1 \pm 1 \%)$, f1 = interference frequency	
• Series mode interference (peak value of interference < rated value of input range), min.	70 dB; With conversion time 67.5 / 22.5 / 18.75 ms: 40 dB

Interrupts/diagnostics/status information			
Diagnostics function	Yes		
Alarms			
• Diagnostic alarm	Yes		
• Limit value alarm	No		
Diagnoses			
• Monitoring the supply voltage	Yes		
• Wire-break	Yes; at 4 to 20 mA		
• Short-circuit	Yes; Sensor supply to M; module by module		
• Group error	Yes		
• Overflow/underflow	Yes; Module-wise		
Diagnostics indication LED			
• Monitoring of the supply voltage (PWR-LED)	Yes; green LED		
• Channel status display	Yes; green LED		
• for channel diagnostics	No		
• for module diagnostics	Yes; green/red DIAG LED		
Potential separation			
Potential separation channels			
• between the channels	No		
• between the channels and backplane bus	Yes		
• between the channels and the power supply of the electronics	No		
Isolation			
Isolation tested with	707 V DC (type test)		
Standards, approvals, certificates			
Ecological footprint			
• environmental product declaration	Yes		
Global warming potential			
— global warming potential, (total) [CO2 eq]	9.32 kg		
— global warming potential, (during production) [CO2 eq]	4.97 kg		
— global warming potential, (during operation) [CO2 eq]	4.79 kg		
— global warming potential, (after end of life cycle) [CO2 eq]	-0.449 kg		
Security			
signed firmware update	Yes; firmware V2.0.0 or higher		
safely removing data	Yes; firmware V2.0.0 or higher		
data integrity	Yes; firmware V2.0.0 or higher		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.	-30 °C; < 0 °C as of FS04		
• horizontal installation, max.	60 °C		
• vertical installation, min.	-30 °C; < 0 °C as of FS04		
• vertical installation, max.	50 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual		
Dimensions			
Width	15 mm		
Height	73 mm		
Depth	58 mm		
Weights			
Weight, approx.	31 g		
Classifications			
		Version	Classification
	eClass	14	27-24-26-01
	eClass	12	27-24-26-01
	eClass	9.1	27-24-26-01

eClass	9	27-24-26-01
eClass	8	27-24-26-01
eClass	7.1	27-24-26-01
eClass	6	27-24-26-01
ETIM	10	EC001596
ETIM	9	EC001596
ETIM	8	EC001596
ETIM	7	EC001596
IDEA	4	3562
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval

Miscellaneous




[Manufacturer Declaration](#)

[KC](#)

[China RoHS](#)

General Product Approval

EMV

For use in hazardous locations



[Metrological Approval](#)

[KC](#)



[KC](#)



For use in hazardous locations

[FM](#)

[CCC-Ex](#)





[Type Examination Certificate](#)

[Miscellaneous](#)

Maritime application









[NK / Nippon Kaiji Kyokai](#)



Maritime application

Environment



[CCS \(China Classification Society\)](#)







last modified: 10/23/2025 