



SIMATIC ET 200SP, Analog output module, AQ 2x U/I High Speed, suitable for BU type A0, A1, Color code CC00, channel diagnostics, 16 bit, +/-0.2%

General information	
Product type designation	AQ 2xU/I HS
HW functional status	From FS06
usable BaseUnits	BU type A0, A1
Color code for module-specific color identification plate	CC00
Product function	
I&M data	Yes; I&M0 to I&M3
Isochronous mode	Yes; 125 µs
Engineering with	
STEP 7 TIA Portal configurable/integrated from version	V13 SP1
STEP 7 configurable/integrated from version	V5.5 SP3 / -
PROFIBUS from GSD version/GSD revision	GSD Revision 5
PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
Oversampling	Yes; 2 channels per module
MSO	No
CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Calibration possible in RUN	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	45 mA; without load
Current consumption, max.	90 mA; 2 channels current output 20 mA
Power loss	
Power loss, typ.	0.9 W
Address area	
Address space per module	
Address space per module, max.	4 byte; + 1 byte for QI information (32 bytes in the oversampling operating mode)
Hardware configuration	
Automatic encoding	
Mechanical coding element	Yes
Type of mechanical coding element	Type A
Analog outputs	
Number of analog outputs	2

Voltage output, short-circuit protection	Yes
Voltage output, short-circuit current, max.	45 mA
Cycle time (all channels), min.	125 μ s
Analog output with oversampling	Yes
• Values per cycle, max.	16
• Resolution, min.	45 μ s; (2 channels), 35 μ s (1 channel)
Output ranges, voltage	
• 0 to 10 V	Yes; 15 bit
• 1 V to 5 V	Yes; 13 bit
• -5 V to +5 V	Yes; 15 bit incl. sign
• -10 V to +10 V	Yes; 16 bit incl. sign
Output ranges, current	
• 0 to 20 mA	Yes; 15 bit
• -20 mA to +20 mA	Yes; 16 bit incl. sign
• 4 mA to 20 mA	Yes; 14 bit
Connection of actuators	
• for voltage output two-wire connection	Yes
• for voltage output four-wire connection	Yes
• for current output two-wire connection	Yes
Load impedance (in rated range of output)	
• with voltage outputs, min.	2 k Ω
• with voltage outputs, capacitive load, max.	1 μ F
• with current outputs, max.	500 Ω
• with current outputs, inductive load, max.	1 mH
Destruction limits against externally applied voltages and currents	
• Voltages at the outputs	30 V
Cable length	
• shielded, max.	1 000 m; 200 m for voltage output
Analog value generation for the outputs	
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
Settling time	
• for resistive load	0.05 ms
• for capacitive load	0.05 ms; Max. 47 nF and 20 m cable length
• for inductive load	0.05 ms
Errors/accuracies	
Output ripple (relative to output range, bandwidth 0 to 50 kHz), (+/-)	0.02 %
Linearity error (relative to output range), (+/-)	0.03 %
Temperature error (relative to output range), (+/-)	0.003 %/K
Crosstalk between the outputs, max.	-50 dB
Repeat accuracy in steady state at 25 °C (relative to output range), (+/-)	0.03 %
Operational error limit in overall temperature range	
• Voltage, relative to output range, (+/-)	0.2 %
• Current, relative to output range, (+/-)	0.2 %
Basic error limit (operational limit at 25 °C)	
• Voltage, relative to output range, (+/-)	0.1 %
• Current, relative to output range, (+/-)	0.1 %
Isochronous mode	
Execution and activation time (TCO), min.	70 μ s
Bus cycle time (TDP), min.	125 μ s
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Monitoring the supply voltage	Yes

• Wire-break • Short-circuit • Group error • Overflow/underflow	Yes; channel-by-channel, only for output type "current"		
	Yes; channel-by-channel, only for output type "voltage"		
	Yes		
	Yes		
Diagnostics indication LED			
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED		
• Channel status display	Yes; green LED		
• for channel diagnostics	Yes; red LED		
• for module diagnostics	Yes; green/red DIAG LED		
Potential separation			
Potential separation channels			
• between the channels	No		
• between the channels and backplane bus	Yes		
• between the channels and the power supply of the electronics	Yes		
Isolation			
Isolation tested with	707 V DC (type test)		
Standards, approvals, certificates			
Ecological footprint			
• environmental product declaration	Yes		
Global warming potential			
— global warming potential, (total) [CO2 eq]	28.6 kg		
— global warming potential, (during production) [CO2 eq]	5.33 kg		
— global warming potential, (during operation) [CO2 eq]	23.6 kg		
— global warming potential, (after end of life cycle) [CO2 eq]	-0.343 kg		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.	-30 °C; < 0 °C as of FS06		
• horizontal installation, max.	60 °C		
• vertical installation, min.	-30 °C; < 0 °C as of FS06		
• vertical installation, max.	50 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual		
Dimensions			
Width	15 mm		
Height	73 mm		
Depth	58 mm		
Weights			
Weight, approx.	31 g		
Classifications			
		Version	Classification
	eClass	14	27-24-26-01
	eClass	12	27-24-26-01
	eClass	9.1	27-24-26-01
	eClass	9	27-24-26-01
	eClass	8	27-24-26-01
	eClass	7.1	27-24-26-01
	eClass	6	27-24-26-01
	ETIM	10	EC001596
	ETIM	9	EC001596
	ETIM	8	EC001596
	ETIM	7	EC001596
	IDEA	4	3562
	UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval



[Miscellaneous](#)

[Manufacturer Declaration](#)



[Metrological Approval](#)

General Product Approval For use in hazardous locations

[KC](#)



[CCC-Ex](#)

[FM](#)



For use in hazardous locations Maritime application

[Type Examination Certificate](#)



[Miscellaneous](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)



Environment



last modified: 10/23/2025