



SIMATIC ET 200SP, Potential distributor module, PotDis-BaseUnit, PotDis-BU Typ P1, dark-colored, 17 x P1-potential, 1 x P2-potential, Push-In terminals. P1-, P2- and AUX-rail bridged to left BU, Packaging Unit: 1 Piece, WxH: 15mm x 117mm

General information	
Product type designation	PotDis BU type P1, dark version
HW functional status	FS10 and higher
Color code for module-specific color identification plate	CC62
Supply voltage	
Rated value (DC)	
• For P1 and P2 bus	48 V; max.
• for process terminals	48 V; max.
external protection for power supply lines	Yes; 10 A miniature circuit breaker with type B or C tripping characteristic for the respective rated supply voltage
Current carrying capacity	
For P1 and P2 bus, max.	10 A
For process terminals, max.	10 A
Hardware configuration	
Formation of potential groups	
• New potential group	No
• Potential group continued from the left	Yes
Slots	
• Number of slots	1
Potential separation	
between backplane bus and supply voltage	Yes
Isolation	
Isolation tested with	3 250 V DC
Standards, approvals, certificates	
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	0.873 kg
— global warming potential, (during production) [CO2 eq]	0.866 kg
— global warming potential, (during operation) [CO2 eq]	0 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.0011 kg
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	

- Installation altitude above sea level, max.

5 000 m; Restrictions for installation altitudes > 2 000 m, see manual

Accessories

Color coding labels

- for process terminals

CC62

connection method

Terminals

- Terminal type
- Conductor cross-section, min.
- Conductor cross-section, max.
- Number of terminals with connection to P1 and P2 bus

Push-in terminal

0.14 mm²

2.5 mm²

17 terminals to P1, 1 terminal to P2

Dimensions

Width

15 mm

Height

117 mm

Depth

35 mm

Weights

Weight, approx.

40 g

Classifications

	Version	Classification
eClass	14	27-24-26-03
eClass	12	27-24-26-03
eClass	9.1	27-24-26-03
eClass	9	27-24-26-03
eClass	8	27-24-26-03
eClass	7.1	27-24-26-03
eClass	6	27-24-26-03
ETIM	10	EC001598
ETIM	9	EC001598
ETIM	8	EC001598
ETIM	7	EC001598
IDEA	4	3560
UNSPSC	15	32-15-17-04

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)



[KC](#)



For use in hazardous locations



[CCC-Ex](#)

[FM](#)



[Miscellaneous](#)

For use in hazardous locations

Maritime application

[Type Examination Certificate](#)



[NK / Nippon Kaiji Kyokai](#)

Maritime application

Environment



[CCS \(China Classification Society\)](#)



last modified:

9/19/2025