

Data sheet

6GK5786-2HC00-0AB0

product type designation



W786-2IA RJ45 (USA)

IWLAN Access Point, SCALANCE W786-2IA RJ45, 2 radios, 6 internal antennas, iFeatures support via key plug, IEEE 802.11a/b/g/h/n, 2.4/5GHz, gross 450 Mbit/s per radio, 1x RJ45 max. 1 Gbit/s, PoE, redundant 24 V DC, terminal block, 110 - 230 V AC via PS791-2AC IP65, -40..+60 °C, plug slot, WPA2/802.11i/e, observe national approvals! CERT ID: EAPN-W2-RJ-I3, includes: MPCIE-R1-ABGN-U3, scope of delivery: Manuals on CD-ROM, German/English, 1x terminal block; for operation in the USA

Technical Product Detail Page

<https://i.siemens.com/1P6GK5786-2HC00-0AB0>

transfer rate

transfer rate

- with WLAN / maximum 450 Mbit/s
- for Industrial Ethernet 10, 100, 1000 Mbit/s

interfaces

number of electrical connections

- for network components or terminal equipment 1
- for power supply 1
- for redundant voltage supply 1

type of electrical connection

- for network components or terminal equipment RJ45 socket
- for power supply 2-pole connector (24 V DC) or optionally available power supply adapter (4-pole 24 V DC or 3-pole 110 to 230 V AC)

memory

design of the removable storage

- C-PLUG Yes
- KEY-PLUG Yes

interfaces / wireless

number of radio cards / permanently installed

2

transmission mode / for multiple input multiple output (MIMO)

3x3

number of spatial streams

3

number of internal antennas

6

antenna gain compared to spherical radiator / of the WLAN antenna

- in the 2.4 GHz frequency band 3 dB
- in the 5 GHz frequency band 4 dB

supply voltage, current consumption, power loss

type of voltage / of the supply voltage

DC

supply voltage

- from Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af 48 V
- from Power-over-Ethernet according to IEEE802.3at for type 2 50 V
- from optional integrable power supply
 - at AC 100 ... 240 V
 - at DC 12 ... 24 V

consumed current

- at DC / at 24 V / typical 0.63 A

• at AC / at 230 V / typical • with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical	0.07 A 0.22 A
power loss [W] • at DC / at 24 V / typical • at AC / at 230 V / typical • with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical	15 W 15 W 15 W
supply voltage / 1 • from terminal block	19.2 V
supply voltage / 2 • from terminal block	28.8 V
ambient conditions	
ambient temperature • during operation • during storage • during transport	-40 ... +60 °C -40 ... +85 °C -40 ... +70 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	100 %
ambient condition / for operation	When using the 100 - 240 V AC power supply, an operating temperature of -40 °C to +60 °C is permissible
protection class IP	IP65
design, dimensions and weights	
width / of the enclosure / without antenna	251 mm
height / of the enclosure / without antenna	251 mm
depth / of the enclosure / without antenna	72 mm
net weight	2.24 kg
fastening method • S7-300 rail mounting • S7-1500 rail mounting • 35 mm DIN-rail mounting • wall mounting	For mast mounting, 35 mm DIN rail mounting and S7-300 rail mounting, an additional support plate is required Yes No Yes Yes
radio frequencies	
operating frequency • for WLAN in 2.4 GHz frequency band • for WLAN in 5 GHz frequency band	2.41 ... 2.48 GHz; depending on the country approvals 4.9 ... 5.8 GHz; depending on the country approvals
product features, product functions, product components / general	
product function / Access Point Mode	Yes
product function / client Mode	Yes
number of SSIDs	16
product function • iPCF Access Point • iPCF client • iPCF-MC Access Point • iPCF-MC client	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures' Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' Yes; Only in combination with 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
number of iPCF-capable radio modules	2
product function / iREF	Yes; In combination only with 'KEY-PLUG W780 iFeatures'
number of iREF-capable radio modules	2
product function / iPRP	Yes; In combination with the 'KEY-PLUG W780 iFeatures' only
product functions / management, configuration, engineering	
number of manageable IP addresses / in client	8
product function • CLI • web-based management • MIB support • TRAPs via email • configuration with STEP 7 • configuration with STEP 7 in the TIA Portal	Yes Yes Yes Yes Yes Yes

• operation with IWLAN controller	No
• operation with Enterasys WLAN controller	No
• forced roaming on IP down with IWLAN	Yes
• forced roaming on link down with IWLAN	Yes
• WDS	Yes
protocol / is supported	
• Address Resolution Protocol (ARP)	Yes
• ICMP	Yes
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• DCP	Yes
• LLDP	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
product functions / diagnostics	
product function	
• PROFINET IO diagnosis	Yes
• link check	No
• connection monitoring IP-Alive	No
• localization via Aeroscout	Yes
• SysLog	Yes
protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
product functions / VLAN	
product function	
• function VLAN with IWLAN	Yes
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP server	Yes
• DHCP Option 82	Yes
product functions / redundancy	
protocol / is supported	
• STP/RSTP	Yes
• MSTP	Yes
• RSTP	Yes
product functions / security	
product function	
• ACL - MAC-based	Yes
• management security, ACL-IP based	Yes
• IEEE 802.1x (radius)	Yes
• NAT/NAPT	No
• access protection according to IEEE802.11i	Yes
• WPA/WPA2	Yes
• TKIP/AES	Yes
protocol / is supported	
• SSH	Yes
• RADIUS	Yes
product functions / time	
protocol / is supported	
• NTP	Yes
• SNTP	Yes
• SIMATIC time synchronization (SIMATIC Time)	Yes

standards, specifications, approvals	
standard	<ul style="list-style-type: none"> for FM for safety / from CSA and UL
	<p>FM 3611: Class I, Division 2, Groups A,B,C,D, T4 / Class 1, Zone 2, Group IIC, T4, FM16US0205X</p> <p>UL 60950-1 E115352, CSA C22.2 No. 60950-1</p>
certificate of suitability	<ul style="list-style-type: none"> EC Declaration of Conformity CE marking C-Tick E1 approval railway application in accordance with EN 50155 railway application in accordance with EN 50121-4 NEMA TS2 IEC 61375 IEC 61850-3 NEMA4X Power-over-Ethernet according IEEE802.3at for type 1 and IEEE802.3af Power-over-Ethernet according to IEEE802.3at for type 2
standard for wireless communication	<ul style="list-style-type: none"> IEEE 802.11a IEEE 802.11b IEEE 802.11e IEEE 802.11g IEEE 802.11h IEEE 802.11i IEEE 802.11n
wireless approval	For operation in the USA, you will find more information under: www.siemens.de/funkzulassungen
standards, specifications, approvals / marine classification	
Marine classification association	<ul style="list-style-type: none"> American Bureau of Shipping Europe Ltd. (ABS) French marine classification society (BV) DNV GL Korean Register of Shipping (KRS) Lloyds Register of Shipping (LRS) Nippon Kaiji Kyokai (NK) Polski Rejestr Statkow (PRS) Royal Institution of Naval Architects (RINA)
standards, specifications, approvals / hazardous environments	
standard / for hazardous zone	<p>EN 60079-15:2005, EN 60079-0:2006, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X</p> <p>ANSI/ISA 12.12.01-2013, CAN/CSA C22.2 No.213-M1987, Cl. 1, div. 2, GP. A, B, C, D, T4 / Cl. 1, Zone 2, GP IIC E240480</p>
certificate of suitability / CCC / for hazardous zone according to GB standard	<p>Yes; GB3836.1, GB3836.8</p> <p>Ex nA IIC T4 Gc</p>
accessories	
accessories	24 V DC screw terminal included in scope of delivery
further information / internet links	
internet link	<ul style="list-style-type: none"> to website: Selection guide for cables and connectors to web page: selection aid TIA Selection Tool to web page: WLAN country approval to the website: WLAN to website: Industrial communication to web page: SiePortal to website: Image database to website: CAx-Download-Manager to website: Industry Online Support
	<p>https://support.industry.siemens.com/cs/ww/en/view/109766358</p> <p>https://www.siemens.com/tstcloud</p> <p>https://www.siemens.com/wireless-approvals</p> <p>https://www.siemens.com/wlan</p> <p>https://www.siemens.com/simatic-net</p> <p>https://sieportal.siemens.com/</p> <p>https://www.automation.siemens.com/bilddb</p> <p>https://www.siemens.com/cax</p> <p>https://support.industry.siemens.com</p>

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under [https://www.siemens.com/cert. \(V4.7\)](https://www.siemens.com/cert. (V4.7))

Approvals / Certificates

General Product Approval



[Declaration of Conformity](#)



[Manufacturer Declaration](#)

[China RoHS](#)

General Product Approval	For use in hazardous locations	Radio Equipment Type Approval Certificate	Maritime application
--------------------------	--------------------------------	---	----------------------

[Miscellaneous](#)



IECEx



ATEX

[CCC-Ex](#)

[Miscellaneous](#)



LRS

last modified:

10/29/2025