


product type designation

product description



PROFIBUS FC Ground Cable

Special bus cable (2-core) with additional protective jacket, sold by the meter, unassembled

PROFIBUS FC UNDERGROUND Cable, Underground cable 2-core shielded, sold by the meter delivery unit max. 1000 m minimum order quantity 20 m.

Technical Product Detail Page

<https://i.siemens.com/1P6XV1830-3FH10>

suitability for use

Used for buried cables

cable designation

02YSY (ST) CY2Y 1x2x0,64/2,55-150 SW KF 40

wire length

sold by the meter

electrical data

attenuation factor per length

- at 9.6 kHz / maximum 0.0025 dB/m
- at 38.4 kHz / maximum 0.004 dB/m
- at 4 MHz / maximum 0.022 dB/m
- at 16 MHz / maximum 0.042 dB/m

impedance

- rated value 150 Ω
- at 9.6 kHz 270 Ω
- at 38.4 kHz 185 Ω
- at 3 MHz ... 20 MHz 150 Ω

relative symmetrical tolerance

- of the characteristic impedance at 9.6 kHz 10 %
- of the characteristic impedance at 38.4 kHz 10 %
- of the characteristic impedance at 3 MHz ... 20 MHz 10 %

loop resistance per length / maximum

110 mΩ/m

shield resistance per length / maximum

9.5 Ω/km

capacity per length / at 1 kHz

28.5 pF/m

operating voltage

- RMS value 80 V

mechanical data

number of electrical cores

2

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

type of electrical connection / FastConnect

Yes

outer diameter

- of inner conductor 0.65 mm
- of the wire insulation 2.55 mm
- of the inner sheath of the cable 5.4 mm
- of cable sheath 10.8 mm
- of cable sheath / note The cable (diameter 8.0 mm +/- 0.4 mm) has an additional black outer cover (diameter 10.8 mm +/- 0.5 mm) as protection against damage if laid in the ground. because of outer diameter > 8 mm: Bus connectors can only be

	connected after removing the outer cover.
symmetrical tolerance of the outer diameter / of cable sheath material	0.5 mm
• of the wire insulation • of the inner sheath of the cable • of cable sheath	polyethylene (PE) PVC PE/PVC; PVC (sheath of the cable), PE (additional outer sheath)
color	red/green Black
bending radius	41 mm 81 mm
tensile load / maximum	100 N
weight per length	117 kg/km
ambient conditions	
ambient temperature	-40 ... +60 °C
• during operation • during storage • during transport • during installation	-40 ... +60 °C -40 ... +60 °C -40 ... +60 °C -40 ... +60 °C
fire behavior	inflammable
class of burning behaviour / according to EN 13501-6	Fca
chemical resistance	oil resistant according to IEC 60811-2-1 (4 h / 70°C) Conditional resistance Resistant
radiological resistance / to UV radiation	resistant / Sunlight resistant acc. to UL 444 Sec. 7.12
product features, product functions, product components / general	
product feature	
• halogen-free	No
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	No
certificate of suitability	CE, FCC, IC, cULus
• EAC approval • CE marking • RoHS conformity	Yes Yes Yes
• resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
• Polski Rejestr Statków (PRS)	No
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to web page: SiePortal	https://sieportal.siemens.com/
• to website: Image database	https://www.automation.siemens.com/bilddb
• to website: CAx-Download-Manager	https://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions

that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under [https://www.siemens.com/cert. \(V4.7\)](https://www.siemens.com/cert. (V4.7))

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)
tion



[Declaration of Con-](#)
formity



[China RoHS](#)

General Product Approval

Environment

[Fire safety / Physical](#)
security



[Environmental Con-](#)
firmations

last modified:

12/20/2025