



Circuit breaker size S0 for motor protection, CLASS 10 A-release 1.8...2.5 A N-release 33 A screw terminal Standard switching capacity

|   |                      |
|---|----------------------|
| product brand name  | SIRIUS               |
| product designation   | Circuit breaker      |
| design of the product   | For motor protection |
| product type designation  | 3RV2                 |
| <b>General technical data</b>   |                      |
| size of the circuit-breaker   | S0                   |
| size of contactor can be combined company-specific                                  | S00, S0              |
| product extension auxiliary switch  | Yes                  |
| power loss [W] for rated value of the current                                       |                      |
| • at AC in hot operating state  | 7.25 W               |
| • at AC in hot operating state per pole   | 2.4 W                |
| insulation voltage with degree of pollution 3 at AC rated value                     | 690 V                |
| surge voltage resistance rated value  | 6 kV                 |
| shock resistance according to IEC 60068-2-27  | 25g / 11 ms          |
| mechanical service life (operating cycles)  |                      |
| • of the main contacts typical  | 100 000              |
| • of auxiliary contacts typical   | 100 000              |
| electrical endurance (operating cycles) typical                                     | 100 000              |
| reference code according to IEC 81346-2   | Q                    |
| Substance Prohibitance (Date)   | 10/01/2009           |
| SVHC substance name   | Lead - 7439-92-1     |
| Net Weight  | 0.351 kg             |
| <b>Ambient conditions</b>   |                      |
| installation altitude at height above sea level maximum                             | 2 000 m              |
| ambient temperature   |                      |
| • during operation  | -20 ... +60 °C       |
| • during storage  | -50 ... +80 °C       |
| • during transport  | -50 ... +80 °C       |
| relative humidity during operation  | 10 ... 95 %          |
| <b>Main circuit</b>   |                      |
| number of poles for main current circuit  | 3                    |
| adjustable current response value current of the current-dependent overload release | 1.8 ... 2.5 A        |
| type of voltage for main current circuit  | AC                   |
| operating voltage   |                      |
| • rated value   | 20 ... 690 V         |

|  |                       |
|--|-----------------------|
| • at AC-3 rated value maximum  | 690 V                 |
| • at AC-3e rated value maximum                                       | 690 V                 |
| <b>operating frequency rated value</b>                               | 50 ... 60 Hz          |
| <b>operational current rated value</b>                               | 2.5 A                 |
| <b>operational current</b>   |                       |
| • at AC-3 at 400 V rated value                                       | 2.5 A                 |
| • at AC-3e at 400 V rated value                                      | 2.5 A                 |
| <b>operating power</b>   |                       |
| • at AC-3  |                       |
| — at 230 V rated value   | 0.4 kW                |
| — at 400 V rated value   | 0.8 kW                |
| — at 500 V rated value   | 1.1 kW                |
| — at 690 V rated value   | 1.5 kW                |
| • at AC-3e   |                       |
| — at 230 V rated value   | 0.4 kW                |
| — at 400 V rated value   | 0.8 kW                |
| — at 500 V rated value   | 1.1 kW                |
| — at 690 V rated value   | 1.5 kW                |
| <b>operating frequency</b>   |                       |
| • at AC-3 maximum  | 15 1/h                |
| • at AC-3e maximum   | 15 1/h                |
| <b>Auxiliary circuit</b>   |                       |
| <b>type of voltage for auxiliary and control circuit</b>             | AC/DC                 |
| <b>number of NC contacts for auxiliary contacts</b>                  | 0                     |
| <b>number of NO contacts for auxiliary contacts</b>                  | 0                     |
| number of CO contacts for auxiliary contacts                         | 0                     |
| <b>Protective and monitoring functions</b>                           |                       |
| <b>product function</b>  |                       |
| • ground fault detection   | No                    |
| • phase failure detection  | Yes                   |
| <b>trip class</b>  | CLASS 10              |
| <b>design of the overload release</b>                                | thermal               |
| <b>maximum short-circuit current breaking capacity (Icu)</b>         |                       |
| • at AC at 240 V rated value   | 100 kA                |
| • at AC at 400 V rated value   | 100 kA                |
| • at AC at 500 V rated value   | 100 kA                |
| • at AC at 690 V rated value   | 10 kA                 |
| <b>operating short-circuit current breaking capacity (Ics) at AC</b> |                       |
| • at 240 V rated value   | 100 kA                |
| • at 400 V rated value   | 100 kA                |
| • at 500 V rated value   | 100 kA                |
| • at 690 V rated value   | 10 kA                 |
| response value current of instantaneous short-circuit trip unit      | 33 A                  |
| <b>UL/CSA ratings</b>  |                       |
| <b>full-load current (FLA) for 3-phase AC motor</b>                  |                       |
| • at 480 V rated value   | 2.5 A                 |
| • at 600 V rated value   | 2.5 A                 |
| <b>yielded mechanical performance [hp]</b>                           |                       |
| • for single-phase AC motor  |                       |
| — at 230 V rated value   | 0.17 hp               |
| • for 3-phase AC motor   |                       |
| — at 200/208 V rated value   | 0.5 hp                |
| — at 220/230 V rated value   | 0.5 hp                |
| — at 460/480 V rated value   | 1 hp                  |
| — at 575/600 V rated value   | 1.5 hp                |
| <b>Category Control Number (CCN)</b>                                 | E156943 (NKJH, NKJH7) |
| <b>Short-circuit protection</b>                                      |                       |
| <b>product function short circuit protection</b>                     | Yes                   |
| <b>design of the short-circuit trip</b>                              | magnetic              |

| Installation/ mounting/ dimensions                                   |   |
|--|---|
| <b>mounting position</b>   | any   |
| <b>fastening method</b>  | screw and snap-on mounting onto 35 mm DIN rail according to DIN EN 60715                |
| <b>height</b>  | 97 mm   |
| <b>width</b>   | 45 mm   |
| <b>depth</b>   | 97 mm   |
| <b>required spacing</b>  |   |
| • with side-by-side mounting at the side                             | 0 mm  |
| • for grounded parts at 400 V  |   |
| — downwards  | 30 mm   |
| — upwards  | 30 mm   |
| — at the side  | 9 mm  |
| • for live parts at 400 V  |   |
| — downwards  | 30 mm   |
| — upwards  | 30 mm   |
| — at the side  | 9 mm  |
| • for grounded parts at 500 V  |   |
| — downwards  | 30 mm   |
| — upwards  | 30 mm   |
| — at the side  | 9 mm  |
| • for live parts at 500 V  |   |
| — downwards  | 30 mm   |
| — upwards  | 30 mm   |
| — at the side  | 9 mm  |
| • for grounded parts at 690 V  |   |
| — downwards  | 50 mm   |
| — upwards  | 50 mm   |
| — backwards  | 0 mm  |
| — at the side  | 30 mm   |
| — forwards   | 0 mm  |
| • for live parts at 690 V  |   |
| — downwards  | 50 mm   |
| — upwards  | 50 mm   |
| — backwards  | 0 mm  |
| — at the side  | 30 mm   |
| — forwards   | 0 mm  |
| Connections/ Terminals   |   |
| <b>type of electrical connection</b>                                 |   |
| • for main current circuit   | screw-type terminals  |
| <b>arrangement of electrical connectors for main current circuit</b> | Top and bottom  |
| <b>type of connectable conductor cross-sections</b>                  |   |
| • for main contacts  |   |
| — solid or stranded  | 2x (1 ... 2.5 mm <sup>2</sup> ), 2x (2.5 ... 10 mm <sup>2</sup> )                       |
| — finely stranded with core end processing                           | 2x (1 ... 2.5 mm <sup>2</sup> ), 2x (2.5 ... 6 mm <sup>2</sup> ), 1x 10 mm <sup>2</sup> |
| • for AWG cables for main contacts                                   | 2x (16 ... 12), 2x (14 ... 8)   |
| <b>tightening torque</b>   |   |
| • for main contacts with screw-type terminals                        | 2 ... 2.5 N·m   |
| <b>design of screwdriver shaft</b>                                   | Diameter 5 to 6 mm  |
| <b>size of the screwdriver tip</b>                                   | Pozidriv size 2   |
| <b>design of the thread of the connection screw</b>                  |   |
| • for main contacts  | M4  |
| Safety related data  |   |
| <b>product function suitable for safety function</b>                 | Yes   |
| <b>suitability for use</b>   |   |
| • safety-related switching on  | No  |
| • safety-related switching OFF                                       | Yes   |
| <b>service life maximum</b>  | 10 a  |
| <b>test wear-related service life necessary</b>                      | Yes   |

|  |  |
|--|--|
| <b>proportion of dangerous failures</b>                              |  |
| • with low demand rate according to SN 31920                         | 40 %   |
| • with high demand rate according to SN 31920                        | 50 %   |
| <b>B10 value with high demand rate according to SN 31920</b>         |  |
| <b>failure rate [FIT] with low demand rate according to SN 31920</b> |  |
| ISO 13849  |  |
| <b>device type according to ISO 13849-1</b>                          | 3  |
| <b>overdimensioning according to ISO 13849-2 necessary</b>           | Yes  |
| IEC 61508  |  |
| <b>safety device type according to IEC 61508-2</b>                   | Type A   |
| <b>T1 value</b>  |  |
| • for proof test interval or service life according to IEC 61508     | 10 a   |
| Electrical Safety  |  |
| <b>protection class IP on the front according to IEC 60529</b>       | IP20   |
| <b>touch protection on the front according to IEC 60529</b>          | finger-safe, for vertical contact from the front |
| <b>Display</b>   |  |
| display version for switching status                                 | Handle   |
| <b>Approvals Certificates</b>  |  |
| Environmental Product Declaration                                    |  |
| • global warming potential [CO2 eq] / during manufacturing           | 2.68 kg  |
| • global warming potential [CO2 eq] / during sales                   | 0.143 kg   |
| • global warming potential [CO2 eq] / during operation               | 72.7 kg  |
| • global warming potential [CO2 eq] / after end of life              | -0.445 kg  |
| • global warming potential [CO2 eq] / total                          | 75.078 kg  |

|                    |                                 |
|--------------------|---------------------------------|
| <b>Environment</b> | <b>General Product Approval</b> |
|--------------------|---------------------------------|



Siemens  
EcoTech



[Environmental Confirmations](#)



|                                 |                                       |
|---------------------------------|---------------------------------------|
| <b>General Product Approval</b> | <b>For use in hazardous locations</b> |
|---------------------------------|---------------------------------------|



|                                       |                          |                             |
|---------------------------------------|--------------------------|-----------------------------|
| <b>For use in hazardous locations</b> | <b>Test Certificates</b> | <b>Maritime application</b> |
|---------------------------------------|--------------------------|-----------------------------|



IECEx

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



|                             |              |
|-----------------------------|--------------|
| <b>Maritime application</b> | <b>other</b> |
|-----------------------------|--------------|



LRS



PRS



[Miscellaneous](#)



[Confirmation](#)

|              |                |
|--------------|----------------|
| <b>other</b> | <b>Railway</b> |
|--------------|----------------|



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2021-1CA10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RV2021-1CA10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RV2021-1CA10&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2021-1CA10&lang=en)

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2021-1CA10>

Characteristic curves

[https://curves.simaris.siemens.com/curves/<mmp\\_prod\\_noCOMP="HAUPT"></mmp\\_prod\\_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP=)



