



Load feeder fuseless, Direct-on-line starting 400 V AC, Size S00 1.80...2.50 A 230 V AC Spring-type terminal for installation on standard mounting rail (also fulfills type of coordination 1) Type of coordination 2, I<sub>q</sub> = 150 kA 1 NO (contactor)

|                                                                                     |                                |
|-------------------------------------------------------------------------------------|--------------------------------|
| product brand name                                                                  | SIRIUS                         |
| product designation                                                                 | Direct (on-line) starter       |
| design of the product                                                               | for DIN-rail or screw mounting |
| product type designation                                                            | 3RA21                          |
| manufacturer's article number                                                       |                                |
| • of the supplied contactor                                                         | <a href="#">3RT2015-2AP01</a>  |
| • of the supplied circuit-breakers                                                  | <a href="#">3RV2011-1CA20</a>  |
| • of the supplied link module                                                       | <a href="#">3RA2911-2AA00</a>  |
| <b>General technical data</b>                                                       |                                |
| size of the circuit-breaker                                                         | S00                            |
| size of load feeder                                                                 | S00                            |
| power loss [W] for rated value of the current                                       |                                |
| • at AC in hot operating state per pole                                             | 2.6 W                          |
| • without load current share typical                                                | 4.2 W                          |
| insulation voltage with degree of pollution 3 at AC rated value                     | 690 V                          |
| surge voltage resistance rated value                                                | 6 kV                           |
| degree of protection NEMA rating                                                    | other                          |
| shock resistance according to IEC 60068-2-27                                        | 6g / 11 ms                     |
| mechanical service life (operating cycles) of contactor typical                     | 30 000 000                     |
| type of coordination                                                                | 2                              |
| reference code according to IEC 81346-2:2019                                        | Q                              |
| Substance Prohibitance (Date)                                                       | 10/01/2009                     |
| SVHC substance name                                                                 | Lead - 7439-92-1               |
| Net Weight                                                                          | 0.697 kg                       |
| <b>Ambient conditions</b>                                                           |                                |
| ambient temperature                                                                 |                                |
| • during operation                                                                  | -20 ... +60 °C                 |
| • during storage                                                                    | -50 ... +80 °C                 |
| • during transport                                                                  | -50 ... +80 °C                 |
| temperature compensation                                                            | -20 ... +60 °C                 |
| relative humidity during operation                                                  | 10 ... 95 %                    |
| <b>Main circuit</b>                                                                 |                                |
| number of poles for main current circuit                                            | 3                              |
| design of the switching contact                                                     | electromechanical              |
| adjustable current response value current of the current-dependent overload release | 1.8 ... 2.5 A                  |
| operating voltage                                                                   |                                |
| • rated value                                                                       | 690 V                          |
| • at AC-3 rated value maximum                                                       | 690 V                          |

|                                                                                                                                                             |                                                |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------|
| <ul style="list-style-type: none"> <li>• at AC-3e rated value maximum</li> </ul>                                                                            | 690 V                                          |
| <b>operating frequency rated value</b>                                                                                                                      | 50 ... 60 Hz                                   |
| <b>operational current</b>                                                                                                                                  |                                                |
| <ul style="list-style-type: none"> <li>• at AC-3 at 400 V rated value</li> </ul>                                                                            | 2.5 A                                          |
| <ul style="list-style-type: none"> <li>• at AC-3e at 400 V rated value</li> </ul>                                                                           | 2.5 A                                          |
| <b>operating power</b>                                                                                                                                      |                                                |
| <ul style="list-style-type: none"> <li>• at AC-3 <ul style="list-style-type: none"> <li>— at 400 V rated value</li> </ul> </li> </ul>                       | 750 W                                          |
| <ul style="list-style-type: none"> <li>• at AC-3e <ul style="list-style-type: none"> <li>— at 400 V rated value</li> </ul> </li> </ul>                      | 750 W                                          |
| <b>Control circuit/ Control</b>                                                                                                                             |                                                |
| <b>type of voltage of the control supply voltage</b>                                                                                                        | AC                                             |
| <b>control supply voltage at AC</b>                                                                                                                         |                                                |
| <ul style="list-style-type: none"> <li>• at 50 Hz rated value</li> </ul>                                                                                    | 230 V                                          |
| <ul style="list-style-type: none"> <li>• at 60 Hz rated value</li> </ul>                                                                                    | 230 V                                          |
| <b>apparent holding power of magnet coil at AC</b>                                                                                                          | 4.2 VA                                         |
| <ul style="list-style-type: none"> <li>• at 50 Hz</li> </ul>                                                                                                | 4.2 VA                                         |
| <ul style="list-style-type: none"> <li>• at 60 Hz</li> </ul>                                                                                                | 3.3 VA                                         |
| <b>inductive power factor with the holding power of the coil</b>                                                                                            | 0.25                                           |
| <ul style="list-style-type: none"> <li>• at 50 Hz</li> </ul>                                                                                                | 0.25                                           |
| <ul style="list-style-type: none"> <li>• at 60 Hz</li> </ul>                                                                                                | 0.25                                           |
| <b>Auxiliary circuit</b>                                                                                                                                    |                                                |
| <b>product extension auxiliary switch</b>                                                                                                                   | Yes                                            |
| <b>Protective and monitoring functions</b>                                                                                                                  |                                                |
| <b>trip class</b>                                                                                                                                           | CLASS 10                                       |
| <b>design of the overload release</b>                                                                                                                       | thermal (bimetallic)                           |
| response value current of instantaneous short-circuit trip unit                                                                                             | 33 A                                           |
| <b>UL/CSA ratings</b>                                                                                                                                       |                                                |
| <b>full-load current (FLA) for 3-phase AC motor</b>                                                                                                         |                                                |
| <ul style="list-style-type: none"> <li>• at 480 V rated value</li> </ul>                                                                                    | 2.5 A                                          |
| <ul style="list-style-type: none"> <li>• at 600 V rated value</li> </ul>                                                                                    | 2.5 A                                          |
| <b>yielded mechanical performance [hp]</b>                                                                                                                  |                                                |
| <ul style="list-style-type: none"> <li>• for single-phase AC motor <ul style="list-style-type: none"> <li>— at 110/120 V rated value</li> </ul> </li> </ul> | 0.1 hp                                         |
| <ul style="list-style-type: none"> <li> <ul style="list-style-type: none"> <li>— at 230 V rated value</li> </ul> </li> </ul>                                | 0.25 hp                                        |
| <ul style="list-style-type: none"> <li>• for 3-phase AC motor <ul style="list-style-type: none"> <li>— at 200/208 V rated value</li> </ul> </li> </ul>      | 0.5 hp                                         |
| <ul style="list-style-type: none"> <li> <ul style="list-style-type: none"> <li>— at 220/230 V rated value</li> </ul> </li> </ul>                            | 0.8 hp                                         |
| <ul style="list-style-type: none"> <li> <ul style="list-style-type: none"> <li>— at 460/480 V rated value</li> </ul> </li> </ul>                            | 1.5 hp                                         |
| <ul style="list-style-type: none"> <li> <ul style="list-style-type: none"> <li>— at 575/600 V rated value</li> </ul> </li> </ul>                            | 2 hp                                           |
| <b>Short-circuit protection</b>                                                                                                                             |                                                |
| <b>product function short circuit protection</b>                                                                                                            | Yes                                            |
| <b>design of the short-circuit trip</b>                                                                                                                     | magnetic                                       |
| <b>conditional short-circuit current (I<sub>q</sub>)</b>                                                                                                    |                                                |
| <ul style="list-style-type: none"> <li>• at 400 V according to IEC 60947-4-1 rated value</li> </ul>                                                         | 150 000 A                                      |
| <b>Installation/ mounting/ dimensions</b>                                                                                                                   |                                                |
| <b>mounting position</b>                                                                                                                                    | vertical                                       |
| <b>fastening method</b>                                                                                                                                     | screw and snap-on mounting onto 35 mm DIN rail |
| <b>height</b>                                                                                                                                               | 198 mm                                         |
| <b>width</b>                                                                                                                                                | 45 mm                                          |
| <b>depth</b>                                                                                                                                                | 97 mm                                          |
| <b>required spacing</b>                                                                                                                                     |                                                |
| <ul style="list-style-type: none"> <li>• for grounded parts <ul style="list-style-type: none"> <li>— forwards</li> </ul> </li> </ul>                        | 20 mm                                          |
| <ul style="list-style-type: none"> <li> <ul style="list-style-type: none"> <li>— backwards</li> </ul> </li> </ul>                                           | 0 mm                                           |
| <ul style="list-style-type: none"> <li> <ul style="list-style-type: none"> <li>— upwards</li> </ul> </li> </ul>                                             | 50 mm                                          |
| <ul style="list-style-type: none"> <li> <ul style="list-style-type: none"> <li>— at the side</li> </ul> </li> </ul>                                         | 20 mm                                          |
| <ul style="list-style-type: none"> <li> <ul style="list-style-type: none"> <li>— downwards</li> </ul> </li> </ul>                                           | 10 mm                                          |
| <ul style="list-style-type: none"> <li>• for live parts</li> </ul>                                                                                          |                                                |

|               |       |
|---------------|-------|
| — forwards    | 20 mm |
| — backwards   | 0 mm  |
| — upwards     | 50 mm |
| — downwards   | 10 mm |
| — at the side | 20 mm |

#### Connections/ Terminals

##### type of electrical connection

- |                                     |                         |
|-------------------------------------|-------------------------|
| • for main current circuit          | spring-loaded terminals |
| • for auxiliary and control circuit | spring-loaded terminals |

#### Safety related data

product function suitable for safety function Yes

##### Electrical Safety

touch protection on the front according to IEC 60529 finger-safe, for vertical contact from the front

#### Communication/ Protocol

##### protocol is supported

- |                        |    |
|------------------------|----|
| • PROFINET IO protocol | No |
| • PROFIsafe protocol   | No |

protocol is supported AS-Interface protocol No

#### Approvals Certificates

##### Environment

##### General Product Approval

For use in hazardous locations

[Environmental Confirmations](#)



#### Test Certificates

#### Maritime application

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



#### Maritime application

#### other

#### Railway



[Confirmation](#)

[Special Test Certificate](#)

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2110-1CE15-1AP0>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-1CE15-1AP0>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)



[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RA2110-1CE15-1AP0&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2110-1CE15-1AP0&lang=en)

##### Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2110-1CE15-1AP0>

##### Characteristic curves

[https://curves.simaris.siemens.com/curves/<mmp\\_prod\\_noCOMP='HAUPT'></mmp\\_prod\\_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP='HAUPT'></mmp_prod_no>)



last modified:

4/1/2025