

reversing contactor assembly, AC-3e/AC-3, 7 A, 3 kW / 400 V, 3-pole, 24 V DC, screw terminal, electrical and mechanical interlock



product brand name	SIRIUS
product designation	Reversing contactor assembly
product type designation	3RA23
manufacturer's article number	<ul style="list-style-type: none"> • 1 of the supplied contactor • 2 of the supplied contactor • of the supplied RH assembly kit 3RT2015-1BB42 3RT2015-1BB42 3RA2913-2AA1
General technical data	
size of contactor	S00
product extension auxiliary switch	Yes
shock resistance at rectangular impulse	<ul style="list-style-type: none"> • at AC 6,7g / 5 ms, 4,2g / 10 ms • at DC 6,7g / 5 ms, 4,2g / 10 ms
shock resistance with sine pulse	<ul style="list-style-type: none"> • at AC 10,5g / 5 ms, 6,6g / 10 ms • at DC 10,5g / 5 ms, 6,6g / 10 ms
mechanical service life (operating cycles)	<ul style="list-style-type: none"> • of contactor typical 10 000 000 • of the contactor with added auxiliary switch block typical 10 000 000
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	10/01/2009
Net Weight	615 g
Ambient conditions	
installation altitude at height above sea level maximum	2 000 m
ambient temperature	<ul style="list-style-type: none"> • during operation -25 ... +60 °C • during storage -55 ... +80 °C
Main circuit	
number of poles for main current circuit	3
number of NO contacts for main contacts	3
number of NC contacts for main contacts	0
operating voltage	
• at AC-3 rated value maximum	690 V
• at AC-3e rated value maximum	690 V
operational current	
• at AC-3	
— at 400 V rated value	7 A
— at 500 V rated value	6 A
— at 690 V rated value	4.9 A

• at AC-3e		
— at 400 V rated value	7 A	
— at 500 V rated value	6 A	
— at 690 V rated value	4.9 A	
operating power		
• at AC-3		
— at 400 V rated value	3 kW	
— at 500 V rated value	3 kW	
— at 690 V rated value	4 kW	
• at AC-3e		
— at 400 V rated value	3 kW	
— at 690 V rated value	4 kW	
• at AC-4 at 400 V rated value	3 kW	
operating frequency		
• at AC-3 maximum	750 1/h	
• at AC-3e maximum	750 1/h	
Control circuit/ Control		
type of voltage of the control supply voltage	DC	
control supply voltage 1 at DC rated value	24 V	
closing power of magnet coil at DC	4 W	
holding power of magnet coil at DC	4 W	
Auxiliary circuit		
contact reliability of auxiliary contacts	< 1 error per 100 million operating cycles	
UL/CSA ratings		
full-load current (FLA) for 3-phase AC motor		
• at 480 V rated value	4.8 A	
• at 600 V rated value	6.1 A	
yielded mechanical performance [hp] for 3-phase AC motor		
• at 200/208 V rated value	1.5 hp	
• at 220/230 V rated value	2 hp	
• at 460/480 V rated value	3 hp	
• at 575/600 V rated value	5 hp	
contact rating of auxiliary contacts according to UL	A600 / Q600	
Short-circuit protection		
design of the fuse link		
• for short-circuit protection of the main circuit		
— with type of coordination 1 required	gG NH 3NA, DIAZED 5SB, NEOZED 5SE: 35 A	
— with type of coordination 2 required	gG NH 3NA, DIAZED 5SB, NEOZED 5SE: 20 A	
• for short-circuit protection of the auxiliary switch required	fuse gG: 10 A	
Installation/ mounting/ dimensions		
mounting position		+/-180° rotation possible on vertical mounting surface; can be tilted forward and backward by +/- 22.5° on vertical mounting surface
fastening method		screw and snap-on mounting onto 35 mm DIN rail
height		68 mm
width		90 mm
depth		73 mm
required spacing		
• with side-by-side mounting		
— forwards	6 mm	
— backwards	0 mm	
— upwards	6 mm	
— downwards	6 mm	
— at the side	6 mm	
• for grounded parts		
— forwards	6 mm	
— backwards	0 mm	
— upwards	6 mm	
— at the side	6 mm	
— downwards	6 mm	

• for live parts	6 mm
— forwards	0 mm
— backwards	6 mm
— upwards	6 mm
— downwards	6 mm
— at the side	6 mm

Connections/ Terminals

type of electrical connection	
• for main current circuit	screw-type terminals
• for auxiliary and control circuit	screw-type terminals
• at contactor for auxiliary contacts	Screw-type terminals
• of magnet coil	Screw-type terminals
type of connectable conductor cross-sections for main contacts	
• solid	2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²), 2x 4 mm ²
• solid or stranded	2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²), 2x (0.5 ... 4 mm ²)
• finely stranded with core end processing	2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²)
type of connectable conductor cross-sections	
• for auxiliary contacts	2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²)
— solid or stranded	2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²)
— finely stranded with core end processing	2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²)
• for AWG cables for auxiliary contacts	2x (20 ... 16), 2x (18 ... 14)

Safety related data

product function suitable for safety function	Yes
Electrical Safety	
protection class IP on the front according to IEC 60529	IP20
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front

Communication/ Protocol

product function bus communication	Yes
protocol is supported AS-Interface protocol	No
product function control circuit interface with IO link	No

Approvals Certificates

Environment	General Product Approval	Test Certificates
Environmental Confirmations	 	 

[Special Test Certificate](#)

Test Certificates	Maritime application
Type Test Certificates/Test Report	    

Maritime application	other	Railway	Dangerous goods
 		Confirmation	Special Test Certificate Transport Information

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875
Information for data generation and storage https://support.industry.siemens.com/cs/ww/en/view/109995012
Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10
Industry Mall (Online ordering system) https://mail.industry.siemens.com/mail/en/en/Catalog/product?mlfb=3RA2315-8XB30-1BB4

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2315-8XB30-1BB4>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2315-8XB30-1BB4&lang=en

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2315-8XB30-1BB4>

Characteristic curves

[https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP=)



