



Pushbutton, 22 mm, round, metal, shiny, green, pushbutton, raised momentary contact type, with laser labeling, upper case and lower case, always upper case at beginning of line

|  |  |
|--|--|
| product brand name                                 | SIRIUS ACT   |
| product designation                                | Pushbuttons  |
| design of the product                              | Actuating/signaling element  |
| product type designation                           | 3SU1   |
| product line                                       | Metal, shiny, 22 mm  |
| <b>Enclosure</b>                                   |  |
| number of command points                           | 1  |
| <b>Actuator</b>                                    |  |
| design of the actuating element                    | Raised button  |
| principle of operation of the actuating element    | momentary contact type   |
| product extension optional                         |  |
| • light source                                     | No   |
| • contact module                                   | Yes  |
| color of the actuating element                     | green  |
| material of the actuating element                  | plastic  |
| shape of the actuating element                     | round  |
| outer diameter of the actuating element            | 29.5 mm  |
| marking of the actuating element                   | Customized labeling, text in lower case/capital letters, all lines start with capital letter |
| <b>Front ring</b>                                  |  |
| product component front ring                       | Yes  |
| design of the front ring                           | Standard   |
| material of the front ring                         | Metal, high gloss  |
| color of the front ring                            | silver   |
| <b>General technical data</b>                      |  |
| protection class IP                                | IP66, IP67, IP69(IP69K)  |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13   |
| shock resistance                                   |  |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms   |
| vibration resistance                               |  |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g  |
| operating frequency maximum                        | 3 600 1/h  |
| mechanical service life (operating cycles) typical | 10 000 000   |
| reference code according to IEC 81346-2            | S  |
| Substance Prohibitance (Date)                      | 10/01/2014   |
| Net Weight   | 0.036 kg   |
| <b>Safety related data</b>                         |  |
| proportion of dangerous failures                   |  |
| • with low demand rate according to SN 31920       | 20 %   |

|  |            |
|--|------------|
| <ul style="list-style-type: none"> <li>with high demand rate per NC contact according to SN 31920</li> </ul> | 20 %       |
| <ul style="list-style-type: none"> <li>with high demand rate per NO contact according to SN 31920</li> </ul> | 50 %       |
| <b>B10 value with high demand rate according to SN 31920</b>   | 10 000 000 |
| <b>failure rate [FIT] with low demand rate per NC contact according to SN 31920</b>                          | 100 FIT    |
| <b>IEC 61508</b>   |            |
| T1 value for proof test interval or service life according to IEC 61508                                      | 20 a       |

|  |  |
|--|--|
| <b>Ambient conditions</b>  |  |
| <b>ambient temperature</b>   |  |
| <ul style="list-style-type: none"> <li>during operation</li> </ul> | -25 ... +70 °C   |
| <ul style="list-style-type: none"> <li>during storage</li> </ul>   | -40 ... +80 °C   |
| environmental category during operation according to IEC 60721     | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

|  |         |
|--|---------|
| <b>Installation/ mounting/ dimensions</b>          |         |
| <b>height</b>                                      | 29.5 mm |
| <b>width</b>                                       | 29.5 mm |
| <b>shape of the installation opening</b>           | round   |
| <b>mounting diameter</b>                           | 22.3 mm |
| <b>positive tolerance of installation diameter</b> | 0.4 mm  |
| <b>mounting height</b>                             | 16.2 mm |
| <b>installation width</b>                          | 29.5 mm |
| <b>installation depth</b>                          | 24.3 mm |

|  |                                 |
|--|---------------------------------|
| <b>Approvals Certificates</b>  |                                 |
| Environmental Product Declaration  |                                 |
| <ul style="list-style-type: none"> <li>global warming potential [CO2 eq] / during manufacturing</li> </ul> | 0.625 kg                        |
| <ul style="list-style-type: none"> <li>global warming potential [CO2 eq] / during operation</li> </ul>     | 0.235 kg                        |
| <ul style="list-style-type: none"> <li>global warming potential [CO2 eq] / after end of life</li> </ul>    | -0.267 kg                       |
| <ul style="list-style-type: none"> <li>global warming potential [CO2 eq] / total</li> </ul>                | 0.593 kg                        |
| <b>Environment</b>   | <b>General Product Approval</b> |



[Environmental Confirmations](#)



|                                 |                          |                             |
|---------------------------------|--------------------------|-----------------------------|
| <b>General Product Approval</b> | <b>Test Certificates</b> | <b>Maritime application</b> |
|---------------------------------|--------------------------|-----------------------------|



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



|                             |              |
|-----------------------------|--------------|
| <b>Maritime application</b> | <b>other</b> |
|-----------------------------|--------------|



[Confirmation](#)



**Further information**

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>  
 Information for data generation and storage  
<https://support.industry.siemens.com/cs/ww/en/view/109995012>  
 Information- and Downloadcenter (Catalogs, Brochures,...)  
<https://www.siemens.com/ic10>  
 Industry Mall (Online ordering system)  
[https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1050-0BB40-0AA0-Z\\_Y10](https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1050-0BB40-0AA0-Z_Y10)  
 Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1050-0BB40-0AA0-Z Y10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1050-0BB40-0AA0-Z Y10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1050-0BB40-0AA0-Z Y10&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1050-0BB40-0AA0-Z Y10&lang=en)

---

last modified:

5/17/2025 