



Siemens
EcoTech



RONIS key-operated switch, 22 mm, round, metal, shiny, lock number SB30, with 2 keys, 3 switch positions I-O-II, latching, actuating angle 2x45°, 10:30h/12h/13:30h, key removal O, possible special locks: SB31, 421, 455

product brand name	SIRIUS ACT
product designation	Key-operated switches
design of the product	Actuating/signaling element
product type designation	3SU1
product line	Metal, shiny, 22 mm
manufacturer's article number of included key	3SU1950-0FB80-0AA0
Actuator	
principle of operation of the actuating element	latching, 2x45° (10:30 h/12 h/13:30 h)
product extension optional light source	No
color	
• of the actuating element	silver
material of the actuating element	metal
shape of the actuating element	Key
outer diameter of the actuating element	29.5 mm
number of switching positions	3
switch position for key distraction	O
actuating angle	
• clockwise	45°
• anticlockwise	45°
lock make	RONIS
key number	SB30
Front ring	
product component front ring	Yes
design of the front ring	Standard
material of the front ring	Metal, high gloss
color of the front ring	silver
General technical data	
protection class IP	IP66, IP67, IP69(IP69K)
protection class IP of the terminal	IP20
degree of protection NEMA rating	1, 2, 3, 3R, 4, 4X, 12, 13
shock resistance	
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
vibration resistance	
• according to IEC 60068-2-6	10 ... 500 Hz: 5g
operating frequency maximum	1 800 1/h
mechanical service life (operating cycles) typical	300 000

reference code according to IEC 81346-2	S	
Substance Prohibance (Date)	10/01/2014	
Net Weight	78 g	
Ambient conditions		
ambient temperature		
• during operation	-25 ... +70 °C	
• during storage	-40 ... +80 °C	
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%)	
Installation/ mounting/ dimensions		
height	29.5 mm	
width	29.5 mm	
shape of the installation opening	round	
mounting diameter	22.3 mm	
positive tolerance of installation diameter	0.4 mm	
mounting height	49.4 mm	
installation width	29.5 mm	
installation depth	25.4 mm	
Approvals Certificates		
Environmental Product Declaration		
• global warming potential [CO2 eq] / during manufacturing	0.625 kg	
• global warming potential [CO2 eq] / during operation	0.235 kg	
• global warming potential [CO2 eq] / after end of life	-0.267 kg	
• global warming potential [CO2 eq] / total	0.593 kg	
Environment	General Product Approval	
  Environmental Confirmations   		
General Product Approval	Test Certificates	Maritime application
	Special Test Certificate	Type Test Certificates/Test Report
		
		
		
Maritime application	other	
	 Confirmation	
Further information		
Information on the packaging		
https://support.industry.siemens.com/cs/ww/en/view/109813875		
Information for data generation and storage		
https://support.industry.siemens.com/cs/ww/en/view/109995012		
Information- and Downloadcenter (Catalogs, Brochures,...)		
https://www.siemens.com/ic10		
Industry Mall (Online ordering system)		
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1050-4BL01-0AA0		
Cax online generator		
https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1050-4BL01-0AA0		
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)		
https://support.industry.siemens.com/cs/ww/en/ps/3SU1050-4BL01-0AA0		
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)		
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1050-4BL01-0AA0&lang=en		



last modified:

7/6/2025 