

product brand name	SIRIUS	
product designation	Power contactor	
product type designation	3RT2	
<b>General technical data</b>		
size of contactor	S3	
product extension	<ul style="list-style-type: none"> <li>• function module for communication</li> <li>• auxiliary switch</li> </ul>	
power loss [W] for rated value of the current	<ul style="list-style-type: none"> <li>• at AC in hot operating state 23.7 W</li> <li>• at AC in hot operating state per pole 7.9 W</li> <li>• without load current share typical 7.3 W</li> </ul>	
type of calculation of power loss depending on pole	quadratic	
insulation voltage	<ul style="list-style-type: none"> <li>• of main circuit with degree of pollution 3 rated value 1 000 V</li> <li>• of auxiliary circuit with degree of pollution 3 rated value 690 V</li> </ul>	
surge voltage resistance	<ul style="list-style-type: none"> <li>• of main circuit rated value 8 kV</li> <li>• of auxiliary circuit rated value 6 kV</li> </ul>	
maximum permissible voltage for protective separation between coil and main contacts according to EN 60947-1	690 V	
shock resistance at rectangular impulse	<ul style="list-style-type: none"> <li>• at AC 10.3g / 5 ms, 6,g / 10 ms</li> </ul>	
shock resistance with sine pulse	<ul style="list-style-type: none"> <li>• at AC 16.3g / 5 ms, 10.g / 10 ms</li> </ul>	
mechanical service life (operating cycles)	<ul style="list-style-type: none"> <li>• of contactor typical 10 000 000</li> <li>• of the contactor with added electronically optimized auxiliary switch block typical 5 000 000</li> <li>• of the contactor with added auxiliary switch block typical 10 000 000</li> </ul>	
reference code according to IEC 81346-2	Q	
Substance Prohibitance (Date)	03/01/2017	
Net Weight	1.735 kg	
<b>Ambient conditions</b>		
installation altitude at height above sea level maximum	2 000 m	
ambient temperature	<ul style="list-style-type: none"> <li>• during operation -25 ... +60 °C</li> <li>• during storage -55 ... +80 °C</li> </ul>	
relative humidity minimum	10 %	
relative humidity at 55 °C according to IEC 60068-2-30 maximum	95 %	
<b>Main circuit</b>		
number of poles for main current circuit	3	
number of NO contacts for main contacts	3	
number of NC contacts for main contacts	0	
operating voltage	<ul style="list-style-type: none"> <li>• at AC-3 rated value maximum 1 000 V</li> <li>• at AC-3e rated value maximum 1 000 V</li> </ul>	
operational current	<ul style="list-style-type: none"> <li>• at AC-1 at 400 V at ambient temperature 40 °C rated 130 A</li> </ul>	

value		
• at AC-1		
— up to 690 V at ambient temperature 40 °C rated value	130 A	
— up to 690 V at ambient temperature 60 °C rated value	110 A	
• at AC-3		
— at 400 V rated value	110 A	
— at 500 V rated value	110 A	
— at 690 V rated value	98 A	
— at 1000 V rated value	30 A	
• at AC-3e		
— at 400 V rated value	110 A	
— at 500 V rated value	110 A	
— at 690 V rated value	98 A	
— at 1000 V rated value	30 A	
• at AC-4 at 400 V rated value	97 A	
• at AC-5a up to 690 V rated value	120 A	
• at AC-5b up to 400 V rated value	110 A	
• at AC-6a		
— up to 230 V for current peak value n=20 rated value	98 A	
— up to 400 V for current peak value n=20 rated value	98 A	
— up to 500 V for current peak value n=20 rated value	98 A	
— up to 690 V for current peak value n=20 rated value	98 A	
• at AC-6a		
— up to 230 V for current peak value n=30 rated value	65.3 A	
— up to 400 V for current peak value n=30 rated value	65.3 A	
— up to 500 V for current peak value n=30 rated value	65.3 A	
— up to 690 V for current peak value n=30 rated value	65.3 A	
minimum cross-section in main circuit at maximum AC-1 rated value	50 mm <sup>2</sup>	
<b>operational current for approx. 200000 operating cycles at AC-4</b>		
• at 400 V rated value	46 A	
• at 690 V rated value	36 A	
<b>operational current</b>		
• <b>at 1 current path at DC-1</b>		
— at 24 V rated value	100 A	
— at 60 V rated value	60 A	
— at 110 V rated value	9 A	
— at 220 V rated value	2 A	
— at 440 V rated value	0.6 A	
— at 600 V rated value	0.4 A	
• <b>with 2 current paths in series at DC-1</b>		
— at 24 V rated value	100 A	
— at 60 V rated value	100 A	
— at 110 V rated value	100 A	
— at 220 V rated value	10 A	
— at 440 V rated value	1.8 A	
— at 600 V rated value	1 A	
• <b>with 3 current paths in series at DC-1</b>		
— at 24 V rated value	100 A	
— at 60 V rated value	100 A	
— at 110 V rated value	100 A	
— at 220 V rated value	80 A	
— at 440 V rated value	4.5 A	
— at 600 V rated value	2.6 A	
• <b>at 1 current path at DC-3 at DC-5</b>		
— at 24 V rated value	40 A	
— at 60 V rated value	6 A	

— at 110 V rated value	2.5 A
— at 220 V rated value	1 A
— at 440 V rated value	0.15 A
— at 600 V rated value	0.06 A
<b>• with 2 current paths in series at DC-3 at DC-5</b>	
— at 24 V rated value	100 A
— at 60 V rated value	100 A
— at 110 V rated value	100 A
— at 220 V rated value	7 A
— at 440 V rated value	0.42 A
— at 600 V rated value	0.16 A
<b>• with 3 current paths in series at DC-3 at DC-5</b>	
— at 24 V rated value	100 A
— at 60 V rated value	100 A
— at 110 V rated value	100 A
— at 220 V rated value	35 A
— at 440 V rated value	0.8 A
— at 600 V rated value	0.35 A
<b>operating power</b>	
• at AC-2 at 400 V rated value	55 kW
• at AC-3	
— at 230 V rated value	30 kW
— at 400 V rated value	55 kW
— at 500 V rated value	75 kW
— at 690 V rated value	90 kW
— at 1000 V rated value	37 kW
• at AC-3e	
— at 230 V rated value	30 kW
— at 400 V rated value	55 kW
— at 500 V rated value	75 kW
— at 690 V rated value	90 kW
— at 1000 V rated value	37 kW
<b>operating power for approx. 200000 operating cycles at AC-4</b>	
• at 400 V rated value	24.3 kW
• at 690 V rated value	32.9 kW
<b>operating apparent power at AC-6a</b>	
• up to 230 V for current peak value n=20 rated value	39 kVA
• up to 400 V for current peak value n=20 rated value	67 kVA
• up to 500 V for current peak value n=20 rated value	84 kVA
• up to 690 V for current peak value n=20 rated value	117 kVA
<b>operating apparent power at AC-6a</b>	
• up to 230 V for current peak value n=30 rated value	26 kVA
• up to 400 V for current peak value n=30 rated value	45.2 kVA
• up to 500 V for current peak value n=30 rated value	56.5 kVA
• up to 690 V for current peak value n=30 rated value	78 kVA
<b>short-time withstand current in cold operating state up to 40 °C</b>	
• limited to 1 s switching at zero current maximum	1 960 A; Use minimum cross-section acc. to AC-1 rated value
• limited to 5 s switching at zero current maximum	1 502 A; Use minimum cross-section acc. to AC-1 rated value
• limited to 10 s switching at zero current maximum	1 095 A; Use minimum cross-section acc. to AC-1 rated value
• limited to 30 s switching at zero current maximum	707 A; Use minimum cross-section acc. to AC-1 rated value
• limited to 60 s switching at zero current maximum	562 A; Use minimum cross-section acc. to AC-1 rated value
<b>no-load switching frequency</b>	
• at AC	5 000 1/h
<b>operating frequency</b>	
• at AC-1 maximum	900 1/h
• at AC-2 maximum	350 1/h
• at AC-3 maximum	850 1/h

• at AC-3e — maximum • at AC-4 maximum	850 1/h 200 1/h
<b>Control circuit/ Control</b>	
<b>type of voltage of the control supply voltage</b>	AC
<b>control supply voltage at AC</b>	
• at 50 Hz rated value	110 V
<b>operating range factor control supply voltage rated value of magnet coil at AC</b>	
• at 50 Hz	0.8 ... 1.1
<b>apparent pick-up power of magnet coil at AC</b>	
• at 50 Hz	296 VA
<b>inductive power factor with closing power of the coil</b>	
• at 50 Hz	0.61
<b>apparent holding power of magnet coil at AC</b>	
• at 50 Hz	19 VA
<b>inductive power factor with the holding power of the coil</b>	
• at 50 Hz	0.38
<b>closing delay</b>	
• at AC	13 ... 50 ms
<b>opening delay</b>	
• at AC	10 ... 21 ms
<b>arcing time</b>	10 ... 20 ms
<b>control version of the switch operating mechanism</b>	Standard A1 - A2
<b>Auxiliary circuit</b>	
number of NC contacts for auxiliary contacts instantaneous contact	1
number of NO contacts for auxiliary contacts instantaneous contact	1
operational current at AC-12 maximum	10 A
<b>operational current at AC-15</b>	
• at 230 V rated value	6 A
• at 400 V rated value	3 A
• at 500 V rated value	2 A
• at 690 V rated value	1 A
<b>operational current at DC-12</b>	
• at 24 V rated value	10 A
• at 48 V rated value	6 A
• at 60 V rated value	6 A
• at 110 V rated value	3 A
• at 125 V rated value	2 A
• at 220 V rated value	1 A
• at 600 V rated value	0.15 A
<b>operational current at DC-13</b>	
• at 24 V rated value	10 A
• at 48 V rated value	2 A
• at 60 V rated value	2 A
• at 110 V rated value	1 A
• at 125 V rated value	0.9 A
• at 220 V rated value	0.3 A
• at 600 V rated value	0.1 A
<b>contact reliability of auxiliary contacts</b>	1 faulty switching per 100 million (17 V, 1 mA)
<b>UL/CSA ratings</b>	
<b>full-load current (FLA) for 3-phase AC motor</b>	
• at 480 V rated value	96 A
• at 600 V rated value	99 A
<b>yielded mechanical performance [hp]</b>	
• for single-phase AC motor	
— at 110/120 V rated value	10 hp
— at 230 V rated value	20 hp

<ul style="list-style-type: none"> <li>for 3-phase AC motor           <ul style="list-style-type: none"> <li>— at 200/208 V rated value</li> <li>— at 220/230 V rated value</li> <li>— at 460/480 V rated value</li> <li>— at 575/600 V rated value</li> </ul> </li> </ul>	30 hp 40 hp 75 hp 100 hp
<b>contact rating of auxiliary contacts according to UL</b>	A600 / P600
<b>Short-circuit protection</b>	
design of the miniature circuit breaker for short-circuit protection of the auxiliary circuit up to 230 V	C characteristic: 10 A; 0.4 kA
<b>design of the fuse link</b>	
<ul style="list-style-type: none"> <li>for short-circuit protection of the main circuit           <ul style="list-style-type: none"> <li>— with type of coordination 1 required</li> <li>— with type of coordination 2 required</li> </ul> </li> <li>for short-circuit protection of the auxiliary switch required</li> </ul>	gG: 250 A (690 V, 100 kA), aM: 160 A (690 V, 100 kA), BS88: 200 A (415 V, 80 kA) gG: 200 A (690 V, 100 kA), aM: 100 A (690 V, 100 kA), BS88: 160 A (415 V, 80 kA) gG: 10 A (500 V, 1 kA)
<b>Installation/ mounting/ dimensions</b>	
<b>mounting position</b>	+/-180° rotation possible on vertical mounting surface; can be tilted forward and backward by +/- 22.5° on vertical mounting surface
fastening method side-by-side mounting	Yes
<b>fastening method</b>	screw and snap-on mounting onto 35 mm DIN rail according to DIN EN 60715
<b>height</b>	140 mm
<b>width</b>	70 mm
<b>depth</b>	152 mm
<b>required spacing</b>	
<ul style="list-style-type: none"> <li>with side-by-side mounting           <ul style="list-style-type: none"> <li>— forwards</li> <li>— upwards</li> <li>— downwards</li> <li>— at the side</li> </ul> </li> <li>for grounded parts           <ul style="list-style-type: none"> <li>— forwards</li> <li>— upwards</li> <li>— at the side</li> <li>— downwards</li> </ul> </li> <li>for live parts           <ul style="list-style-type: none"> <li>— forwards</li> <li>— upwards</li> <li>— downwards</li> <li>— at the side</li> </ul> </li> </ul>	20 mm 10 mm 10 mm 0 mm 20 mm 10 mm 10 mm 10 mm 20 mm 10 mm 10 mm 10 mm
<b>Connections/ Terminals</b>	
<b>type of electrical connection</b>	
<ul style="list-style-type: none"> <li>for main current circuit</li> <li>for auxiliary and control circuit</li> <li>at contactor for auxiliary contacts</li> <li>of magnet coil</li> </ul>	screw-type terminals screw-type terminals Screw-type terminals Screw-type terminals
<b>type of connectable conductor cross-sections</b>	
<ul style="list-style-type: none"> <li>for main contacts           <ul style="list-style-type: none"> <li>— finely stranded with core end processing</li> </ul> </li> <li>for AWG cables for main contacts</li> </ul>	2x (2.5 ... 35 mm <sup>2</sup> ), 1x (2.5 ... 50 mm <sup>2</sup> ) 2x (10 ... 1/0), 1x (10 ... 2/0)
<b>connectable conductor cross-section for main contacts</b>	
<ul style="list-style-type: none"> <li>solid</li> <li>stranded</li> <li>finely stranded with core end processing</li> </ul>	2.5 ... 16 mm <sup>2</sup> 6 ... 70 mm <sup>2</sup> 2.5 ... 50 mm <sup>2</sup>
<b>connectable conductor cross-section for auxiliary contacts</b>	
<ul style="list-style-type: none"> <li>solid or stranded</li> <li>finely stranded with core end processing</li> </ul>	0.5 ... 2.5 mm <sup>2</sup> 0.5 ... 2.5 mm <sup>2</sup>
<b>type of connectable conductor cross-sections</b>	
<ul style="list-style-type: none"> <li>for auxiliary contacts           <ul style="list-style-type: none"> <li>— solid or stranded</li> </ul> </li> </ul>	2x (0.5 ... 1.5 mm <sup>2</sup> ), 2x (0.75 ... 2.5 mm <sup>2</sup> )

— finely stranded with core end processing	2x (0.5 ... 1.5 mm <sup>2</sup> ), 2x (0.75 ... 2.5 mm <sup>2</sup> )
• for AWG cables for auxiliary contacts	2x (20 ... 16), 2x (18 ... 14)
<b>AWG number extended as coded connectable conductor cross section for main contacts</b>	10 ... 2/0
<b>AWG number as coded connectable conductor cross section for auxiliary contacts</b>	20 ... 14
<b>Safety related data</b>	
<b>product function</b>	
• mirror contact according to IEC 60947-4-1	Yes
• positively driven operation according to IEC 60947-5-1	No
• suitable for safety function	Yes
suitability for use safety-related switching OFF	Yes
<b>service life maximum</b>	20 a
<b>test wear-related service life necessary</b>	Yes
<b>proportion of dangerous failures</b>	
• with low demand rate according to SN 31920	40 %
• with high demand rate according to SN 31920	73 %
<b>B10 value with high demand rate according to SN 31920</b>	1 000 000
<b>failure rate [FIT] with low demand rate according to SN 31920</b>	100 FIT
ISO 13849	
<b>device type according to ISO 13849-1</b>	3
<b>overdimensioning according to ISO 13849-2 necessary</b>	Yes
IEC 61508	
<b>safety device type according to IEC 61508-2</b>	Type A
Electrical Safety	
<b>protection class IP on the front according to IEC 60529</b>	IP20
<b>touch protection on the front according to IEC 60529</b>	finger-safe, for vertical contact from the front

#### Approvals Certificates

##### Environmental Product Declaration

- global warming potential [CO<sub>2</sub> eq] / during manufacturing
- global warming potential [CO<sub>2</sub> eq] / during operation
- global warming potential [CO<sub>2</sub> eq] / after end of life
- global warming potential [CO<sub>2</sub> eq] / total

7.66 kg  
399 kg  
-1.19 kg  
405 kg

##### Environment

##### General Product Approval



[Environmental Confirmations](#)



##### General Product Approval

##### EMV

##### Test Certificates

##### Maritime application



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



##### Maritime application

##### other



##### other

##### Railway

##### Dangerous goods

[Confirmation](#)

[Special Test Certificate](#)

[Transport Information](#)

## Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT2047-1AF00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RT2047-1AF00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RT2047-1AF00&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT2047-1AF00&lang=en)

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT2047-1AF00>

Characteristic curves

[https://curves.simaris.siemens.com/curves/<mmp\\_prod\\_noCOMP="HAUPT"></mmp\\_prod\\_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP=)

---

last modified:

11/27/2025 