



Circuit breaker size S00 for motor protection, CLASS 10 A-release 1.8...2.5 A N-release 33 A screw terminal Standard switching capacity with transverse auxiliary switches 1 NO+1 NC

|                                                                 |                      |
|-----------------------------------------------------------------|----------------------|
| product brand name                                              | SIRIUS               |
| product designation                                             | Circuit breaker      |
| design of the product                                           | For motor protection |
| product type designation                                        | 3RV2                 |
| <b>General technical data</b>                                   |                      |
| size of the circuit-breaker                                     | S00                  |
| size of contactor can be combined company-specific              | S00, S0              |
| product extension auxiliary switch                              | Yes                  |
| power loss [W] for rated value of the current                   |                      |
| • at AC in hot operating state                                  | 7.25 W               |
| • at AC in hot operating state per pole                         | 2.4 W                |
| insulation voltage with degree of pollution 3 at AC rated value | 690 V                |
| surge voltage resistance rated value                            | 6 kV                 |
| shock resistance according to IEC 60068-2-27                    | 25g / 11 ms          |
| mechanical service life (operating cycles)                      |                      |
| • of the main contacts typical                                  | 100 000              |
| • of auxiliary contacts typical                                 | 100 000              |
| electrical endurance (operating cycles) typical                 | 100 000              |
| reference code according to IEC 81346-2                         | Q                    |
| Substance Prohibition (Date)                                    | 10/01/2009           |
| SVHC substance name                                             | Lead - 7439-92-1     |
| Net Weight                                                      | 0.361 kg             |
| <b>Ambient conditions</b>                                       |                      |
| installation altitude at height above sea level maximum         | 2 000 m              |
| ambient temperature                                             |                      |
| • during operation                                              | -20 ... +60 °C       |
| • during storage                                                | -50 ... +80 °C       |
| • during transport                                              | -50 ... +80 °C       |
| relative humidity during operation                              | 10 ... 95 %          |
| <b>Environmental footprint</b>                                  |                      |
| Environmental Product Declaration (EPD)                         | Yes                  |
| global warming potential [CO2 eq] total                         | 74.698 kg            |
| global warming potential [CO2 eq] during manufacturing          | 1.98 kg              |
| global warming potential [CO2 eq] during sales                  | 0.134 kg             |
| global warming potential [CO2 eq] during operation              | 72.7 kg              |
| global warming potential [CO2 eq] after end of life             | -0.116 kg            |

|                                                                                            |                 |
|--------------------------------------------------------------------------------------------|-----------------|
| Siemens Eco Profile (SEP)                                                                  | Siemens EcoTech |
| <b>Main circuit</b>                                                                        |                 |
| <b>number of poles for main current circuit</b>                                            | 3               |
| <b>adjustable current response value current of the current-dependent overload release</b> | 1.8 ... 2.5 A   |
| <b>type of voltage for main current circuit</b>                                            | AC              |
| <b>operating voltage</b>                                                                   |                 |
| • rated value                                                                              | 20 ... 690 V    |
| • at AC-3 rated value maximum                                                              | 690 V           |
| • at AC-3e rated value maximum                                                             | 690 V           |
| <b>operating frequency rated value</b>                                                     | 50 ... 60 Hz    |
| <b>operational current rated value</b>                                                     | 2.5 A           |
| <b>operational current</b>                                                                 |                 |
| • at AC-3 at 400 V rated value                                                             | 2.5 A           |
| • at AC-3e at 400 V rated value                                                            | 2.5 A           |
| <b>operating power</b>                                                                     |                 |
| • at AC-3                                                                                  |                 |
| — at 230 V rated value                                                                     | 0.4 kW          |
| — at 400 V rated value                                                                     | 0.75 kW         |
| — at 500 V rated value                                                                     | 1.1 kW          |
| — at 690 V rated value                                                                     | 1.5 kW          |
| • at AC-3e                                                                                 |                 |
| — at 230 V rated value                                                                     | 0.4 kW          |
| — at 400 V rated value                                                                     | 0.75 kW         |
| — at 500 V rated value                                                                     | 1.1 kW          |
| — at 690 V rated value                                                                     | 1.5 kW          |
| <b>operating frequency</b>                                                                 |                 |
| • at AC-3 maximum                                                                          | 15 1/h          |
| • at AC-3e maximum                                                                         | 15 1/h          |
| <b>Auxiliary circuit</b>                                                                   |                 |
| <b>design of the auxiliary switch</b>                                                      | transverse      |
| <b>type of voltage for auxiliary and control circuit</b>                                   | AC/DC           |
| <b>number of NC contacts for auxiliary contacts</b>                                        | 1               |
| <b>number of NO contacts for auxiliary contacts</b>                                        | 1               |
| number of CO contacts for auxiliary contacts                                               | 0               |
| <b>operational current of auxiliary contacts at AC-15</b>                                  |                 |
| • at 24 V                                                                                  | 2 A             |
| • at 120 V                                                                                 | 0.5 A           |
| • at 125 V                                                                                 | 0.5 A           |
| • at 230 V                                                                                 | 0.5 A           |
| <b>operational current of auxiliary contacts at DC-13</b>                                  |                 |
| • at 24 V                                                                                  | 1 A             |
| • at 60 V                                                                                  | 0.15 A          |
| <b>Protective and monitoring functions</b>                                                 |                 |
| <b>product function</b>                                                                    |                 |
| • ground fault detection                                                                   | No              |
| • phase failure detection                                                                  | Yes             |
| <b>trip class</b>                                                                          | CLASS 10        |
| <b>design of the overload release</b>                                                      | thermal         |
| <b>maximum short-circuit current breaking capacity (I<sub>cu</sub>)</b>                    |                 |
| • at AC at 240 V rated value                                                               | 100 kA          |
| • at AC at 400 V rated value                                                               | 100 kA          |
| • at AC at 500 V rated value                                                               | 100 kA          |
| • at AC at 690 V rated value                                                               | 10 kA           |
| <b>operating short-circuit current breaking capacity (I<sub>cs</sub>) at AC</b>            |                 |
| • at 240 V rated value                                                                     | 100 kA          |
| • at 400 V rated value                                                                     | 100 kA          |
| • at 500 V rated value                                                                     | 100 kA          |
| • at 690 V rated value                                                                     | 10 kA           |

|                                                                                                |                                                                                                  |
|------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|
| response value current of instantaneous short-circuit trip unit                                | 33 A                                                                                             |
| <b>UL/CSA ratings</b>                                                                          |                                                                                                  |
| <b>full-load current (FLA) for 3-phase AC motor</b>                                            |                                                                                                  |
| • at 480 V rated value                                                                         | 2.5 A                                                                                            |
| • at 600 V rated value                                                                         | 2.5 A                                                                                            |
| <b>yielded mechanical performance [hp]</b>                                                     |                                                                                                  |
| • for single-phase AC motor                                                                    |                                                                                                  |
| — at 230 V rated value                                                                         | 0.17 hp                                                                                          |
| • for 3-phase AC motor                                                                         |                                                                                                  |
| — at 200/208 V rated value                                                                     | 0.5 hp                                                                                           |
| — at 220/230 V rated value                                                                     | 0.5 hp                                                                                           |
| — at 460/480 V rated value                                                                     | 1 hp                                                                                             |
| — at 575/600 V rated value                                                                     | 1.5 hp                                                                                           |
| <b>contact rating of auxiliary contacts according to UL</b>                                    | C300 / R300                                                                                      |
| <b>Category Control Number (CCN)</b>                                                           | E156943 (NKJH, NKJH7)                                                                            |
| <b>Short-circuit protection</b>                                                                |                                                                                                  |
| <b>product function short circuit protection</b>                                               | Yes                                                                                              |
| <b>design of the short-circuit trip</b>                                                        | magnetic                                                                                         |
| <b>design of the fuse link</b>                                                                 |                                                                                                  |
| • for short-circuit protection of the auxiliary switch required                                | Fuse gL/gG: 10 A, miniature circuit breaker C 6 A (short-circuit current I <sub>k</sub> < 400 A) |
| <b>design of the fuse link for IT network for short-circuit protection of the main circuit</b> |                                                                                                  |
| • at 400 V                                                                                     | gL/gG 25 A                                                                                       |
| • at 500 V                                                                                     | gL/gG 25 A                                                                                       |
| • at 690 V                                                                                     | gL/gG 20 A                                                                                       |
| <b>Installation/ mounting/ dimensions</b>                                                      |                                                                                                  |
| <b>mounting position</b>                                                                       | any                                                                                              |
| <b>fastening method</b>                                                                        | screw and snap-on mounting onto 35 mm DIN rail according to DIN EN 60715                         |
| <b>height</b>                                                                                  | 97 mm                                                                                            |
| <b>width</b>                                                                                   | 45 mm                                                                                            |
| <b>depth</b>                                                                                   | 97 mm                                                                                            |
| <b>required spacing</b>                                                                        |                                                                                                  |
| • with side-by-side mounting at the side                                                       | 0 mm                                                                                             |
| • for grounded parts at 400 V                                                                  |                                                                                                  |
| — downwards                                                                                    | 30 mm                                                                                            |
| — upwards                                                                                      | 30 mm                                                                                            |
| — at the side                                                                                  | 9 mm                                                                                             |
| • for live parts at 400 V                                                                      |                                                                                                  |
| — downwards                                                                                    | 30 mm                                                                                            |
| — upwards                                                                                      | 30 mm                                                                                            |
| — at the side                                                                                  | 9 mm                                                                                             |
| • for grounded parts at 500 V                                                                  |                                                                                                  |
| — downwards                                                                                    | 30 mm                                                                                            |
| — upwards                                                                                      | 30 mm                                                                                            |
| — at the side                                                                                  | 9 mm                                                                                             |
| • for live parts at 500 V                                                                      |                                                                                                  |
| — downwards                                                                                    | 30 mm                                                                                            |
| — upwards                                                                                      | 30 mm                                                                                            |
| — at the side                                                                                  | 9 mm                                                                                             |
| • for grounded parts at 690 V                                                                  |                                                                                                  |
| — downwards                                                                                    | 50 mm                                                                                            |
| — upwards                                                                                      | 50 mm                                                                                            |
| — backwards                                                                                    | 0 mm                                                                                             |
| — at the side                                                                                  | 30 mm                                                                                            |
| — forwards                                                                                     | 0 mm                                                                                             |
| • for live parts at 690 V                                                                      |                                                                                                  |
| — downwards                                                                                    | 50 mm                                                                                            |
| — upwards                                                                                      | 50 mm                                                                                            |

|                                                                      |                                                                       |
|----------------------------------------------------------------------|-----------------------------------------------------------------------|
| — backwards                                                          | 0 mm                                                                  |
| — at the side                                                        | 30 mm                                                                 |
| — forwards                                                           | 0 mm                                                                  |
| <b>Connections/ Terminals</b>                                        |                                                                       |
| <b>type of electrical connection</b>                                 |                                                                       |
| • for main current circuit                                           | screw-type terminals                                                  |
| • for auxiliary and control circuit                                  | screw-type terminals                                                  |
| <b>arrangement of electrical connectors for main current circuit</b> | Top and bottom                                                        |
| <b>type of connectable conductor cross-sections</b>                  |                                                                       |
| • for main contacts                                                  |                                                                       |
| — solid or stranded                                                  | 2x (0,75 ... 2,5 mm <sup>2</sup> ), 2x 4 mm <sup>2</sup>              |
| — finely stranded with core end processing                           | 2x (0.5 ... 1.5 mm <sup>2</sup> ), 2x (0.75 ... 2.5 mm <sup>2</sup> ) |
| • for AWG cables for main contacts                                   | 2x (18 ... 14), 2x 12                                                 |
| <b>type of connectable conductor cross-sections</b>                  |                                                                       |
| • for auxiliary contacts                                             |                                                                       |
| — solid or stranded                                                  | 2x (0.5 ... 1.5 mm <sup>2</sup> ), 2x (0.75 ... 2.5 mm <sup>2</sup> ) |
| — finely stranded with core end processing                           | 2x (0.5 ... 1.5 mm <sup>2</sup> ), 2x (0.75 ... 2.5 mm <sup>2</sup> ) |
| • for AWG cables for auxiliary contacts                              | 2x (20 ... 16), 2x (18 ... 14)                                        |
| <b>tightening torque</b>                                             |                                                                       |
| • for main contacts with screw-type terminals                        | 0.8 ... 1.2 N·m                                                       |
| • for auxiliary contacts with screw-type terminals                   | 0.8 ... 1.2 N·m                                                       |
| <b>design of screwdriver shaft</b>                                   | Diameter 5 to 6 mm                                                    |
| <b>size of the screwdriver tip</b>                                   | Pozidriv size 2                                                       |
| <b>design of the thread of the connection screw</b>                  |                                                                       |
| • for main contacts                                                  | M3                                                                    |
| • of the auxiliary and control contacts                              | M3                                                                    |
| <b>Safety related data</b>                                           |                                                                       |
| product function suitable for safety function                        | Yes                                                                   |
| <b>suitability for use</b>                                           |                                                                       |
| • safety-related switching on                                        | No                                                                    |
| • safety-related switching OFF                                       | Yes                                                                   |
| <b>service life maximum</b>                                          | 10 a                                                                  |
| <b>test wear-related service life necessary</b>                      | Yes                                                                   |
| <b>proportion of dangerous failures</b>                              |                                                                       |
| • with low demand rate according to SN 31920                         | 40 %                                                                  |
| • with high demand rate according to SN 31920                        | 50 %                                                                  |
| <b>B10 value with high demand rate according to SN 31920</b>         | 5 000                                                                 |
| <b>failure rate [FIT] with low demand rate according to SN 31920</b> | 50 FIT                                                                |
| <b>ISO 13849</b>                                                     |                                                                       |
| <b>device type according to ISO 13849-1</b>                          | 3                                                                     |
| <b>overdimensioning according to ISO 13849-2 necessary</b>           | Yes                                                                   |
| <b>IEC 61508</b>                                                     |                                                                       |
| <b>safety device type according to IEC 61508-2</b>                   | Type A                                                                |
| <b>T1 value</b>                                                      |                                                                       |
| • for proof test interval or service life according to IEC 61508     | 10 a                                                                  |
| <b>Electrical Safety</b>                                             |                                                                       |
| <b>protection class IP on the front according to IEC 60529</b>       | IP20                                                                  |
| <b>touch protection on the front according to IEC 60529</b>          | finger-safe, for vertical contact from the front                      |
| <b>Display</b>                                                       |                                                                       |
| display version for switching status                                 | Handle                                                                |
| <b>Approvals Certificates</b>                                        |                                                                       |
| <b>General Product Approval</b>                                      |                                                                       |



|                                                                                                                                                                                             |  |                                                                                                      |  |                                                                                                                                                                                                                         |  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| General Product Approval                                                                                                                                                                    |  | Test Certificates                                                                                    |  | Maritime application                                                                                                                                                                                                    |  |
| <div>AR</div> <div></div> |  | <a href="#">Special Test Certificate</a>                                                             |  | <a href="#">Type Test Certificates/Test Report</a>                                                                                                                                                                      |  |
|                                                                                                                                                                                             |  |                                                                                                      |  | <div><br/>ABS</div> <div></div>                   |  |
| Maritime application                                                                                                                                                                        |  |                                                                                                      |  | other                                                                                                                                                                                                                   |  |
| <div><br/>DNV</div>                                                                                        |  | <div><br/>LRS</div> |  | <div><br/>PRS</div> <div><br/>RINA</div>              |  |
|                                                                                                                                                                                             |  |                                                                                                      |  | <a href="#">Miscellaneous</a> <a href="#">Confirmation</a>                                                                                                                                                              |  |
| other                                                                                                                                                                                       |  | Railway                                                                                              |  | Environment                                                                                                                                                                                                             |  |
| <div><br/>VDE</div>                                                                                        |  | <a href="#">Special Test Certificate</a>                                                             |  | <div><br/>EPD</div> <div><br/>Siemens EcoTech</div> |  |
|                                                                                                                                                                                             |  |                                                                                                      |  | <div></div> <a href="#">Environmental Confirmations</a>                                                                              |  |

#### Further information

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage  
<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)  
<https://www.siemens.com/ic10>




Industry Mall (Online ordering system)  
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2011-1CA15>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)  
<https://support.industry.siemens.com/cs/ww/en/ps/3RV2011-1CA15>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)  
[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RV2011-1CA15&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2011-1CA15&lang=en)

Cax online generator  
<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2011-1CA15>

Characteristic curves  
[https://curves.simaris.siemens.com/curves/<mmp\\_prod\\_noCOMP="HAUPT"></mmp\\_prod\\_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP=)





last modified:

11/13/2025