




SIRIUS ACT: terminal module (command and LED module), integrated LED white, for front plate mounting



product brand name	SIRIUS ACT
product designation	Terminal module
design of the product	with 2 contacts and integrated LED
product type designation	3SU1

### Display

display version	
• for diagnostic function: Supply voltage monitoring power LED	Yes
• status Tx/Rx link	No

### General technical data

product function	Yes; Ribbon cable can be rotated 180°. Yes
firmware version	1.0.0
hardware version	1
software version with STEP 7 in the TIA Portal required	V13 SP1 (V13 SP1 and V14 with HSP0132)
power loss [W] typical	0.115 W
degree of pollution	3
type of voltage	
• of the operating voltage	DC
• of the input voltage	DC
surge voltage resistance rated value	0.8 kV
consumed current	
• maximum	27 mA
• rated value	23 mA
protection class IP	IP20
shock resistance	
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
• for railway applications according to EN 61373	Category 1, Class B
vibration resistance	
• according to IEC 60068-2-6	10 ... 500 Hz: 5g
• for railway applications according to EN 61373	Category 1, Class B
reference code according to IEC 81346-2	K
Substance Prohibitance (Date)	12/19/2016
SVHC substance name	Lead - 7439-92-1 Lead monoxide (lead oxide) - 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one - 71868-10-5

Net Weight	19 g
<b>Communication/ Protocol</b>	
protocol is supported	No
• PROFIsafe protocol	
<b>Connections/ Terminals</b>	
type of electrical connection	Insulation displacement connection
type of connectable conductor cross-sections	Ribbon cable 7-pole, 7 x 0.08 mm <sup>2</sup>
connectable conductor cross-section for auxiliary contacts	
• solid or stranded	0.08 ... 0.08 mm <sup>2</sup>
• finely stranded with core end processing maximum	0.08 mm <sup>2</sup>
connectable conductor cross-section	
• solid	0.08 ... 0.08 mm <sup>2</sup>
• solid with core end processing	0.08 ... 0.08 mm <sup>2</sup>
• finely stranded with core end processing	0.08 ... 0.08 mm <sup>2</sup>
• finely stranded without core end processing	0.08 ... 0.08 mm <sup>2</sup>
<b>Lamp</b>	
color of the light source	white
<b>Safety related data</b>	
product function suitable for safety function	No
service life maximum	20 a
<b>Ambient conditions</b>	
ambient temperature	
• during operation	-25 ... +60 °C
• during storage	-40 ... +80 °C
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted)
explosion protection marking for intrinsic safety of related equipment EEx ia	No
explosion protection marking for intrinsic safety of related equipment EEx ib	No
<b>Installation/ mounting/ dimensions</b>	
fastening method of modules and accessories	Front plate mounting
height	32.6 mm
width	30 mm
depth	31.5 mm
<b>Approvals Certificates</b>	
Environmental Product Declaration	
• global warming potential [CO <sub>2</sub> eq] / during manufacturing	0.566 kg
• global warming potential [CO <sub>2</sub> eq] / during operation	0.235 kg
• global warming potential [CO <sub>2</sub> eq] / after end of life	-0.0145 kg
• global warming potential [CO <sub>2</sub> eq] / total	0.787 kg
Environment	General Product Approval



Siemens  
EcoTech



[Environmental Confirmations](#)



General Product Approval	Test Certificates	other
<b>EAC</b>	<a href="#">Type Test Certificates/Test Report</a>	<a href="#">Special Test Certificate</a>



[Confirmation](#)

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1401-1MC60-1CA1>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1401-1MC60-1CA1>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1401-1MC60-1CA1>




Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1401-1MC60-1CA1&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1401-1MC60-1CA1&lang=en)



-K

SIEMENS



---

last modified:

4/2/2025