


Siemens
EcoTech



holder, 3-way, plastic, minimum order quantity 5 or a multiple thereof

product brand name	SIRIUS ACT
product designation	Holders
design of the product	holder for plastic
product type designation	3SU1
manufacturer's article number	
• of the supplied holder	3SU1500-0AA10-0AA0
Actuator	
design of the actuating element	3-way without module
number of contact modules	0
Holder	
material of the holder	Plastic
Display	
number of LED modules	0
General technical data	
product function positive opening	No
product component	
• diode	No
• lamp transformer	No
• light source	No
• series resistor	No
insulation voltage rated value	500 V
degree of pollution	3
surge voltage resistance rated value	6 kV
shock resistance	
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
• for railway applications according to EN 61373	Category 1, Class B
vibration resistance	
• according to IEC 60068-2-6	10 ... 500 Hz: 5g
• for railway applications according to EN 61373	Category 1, Class B
reference code according to IEC 81346-2	U
Substance Prohibitance (Date)	10/01/2014
Net Weight	15.6 g
Auxiliary circuit	
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
Connections/ Terminals	

tightening torque of the screws in the bracket	1 ... 1.2 N·m			
Ambient conditions				
ambient temperature				
• during operation	-25 ... +70 °C			
• during storage	-40 ... +80 °C			
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted)			
Environmental footprint				
Environmental Product Declaration(EPD)	Yes			
global warming potential [CO ₂ eq] total	0.787 kg			
global warming potential [CO ₂ eq] during manufacturing	0.566 kg			
global warming potential [CO ₂ eq] during operation	0.235 kg			
global warming potential [CO ₂ eq] after end of life	-0.015 kg			
Siemens Eco Profile (SEP)	Siemens EcoTech			
Installation/ mounting/ dimensions				
fastening method	without			
• of modules and accessories	Front plate mounting			
height	40 mm			
width	30 mm			
shape of the installation opening	round			
installation width	30 mm			
installation depth	30.1 mm			
thickness of the front plate usable	1 ... 6 mm			
Approvals Certificates				
General Product Approval	Test Certificates			
	Maritime application			
 EG-Konf.		 US		Type Test Certificates/Test Report
				
Maritime application	other		Environment	
 LRS				Confirmation
				
Environment				
	Environmental Confirmations			
Further information				
Information on the packaging				
https://support.industry.siemens.com/cs/ww/en/view/109813875				
Information for data generation and storage				
https://support.industry.siemens.com/cs/ww/en/view/109995012				
Information- and Downloadcenter (Catalogs, Brochures,...)				
https://www.siemens.com/ic10				
Industry Mall (Online ordering system)				
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1500-0AA10-0AA0				
Cax online generator				
https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1500-0AA10-0AA0				
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)				
https://support.industry.siemens.com/cs/ww/en/ps/3SU1500-0AA10-0AA0				
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)				
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1500-0AA10-0AA0&lang=en				



last modified:

4/2/2025 