



current/voltage measuring module for dry-running protection of centrifugal pumps in hazardous areas, current setting 20...200 A voltage measurement up to 690 V, width 120 mm, straight-through transformer

|   |  |
|---|--|
| product brand name  | SIMOCODE   |
| product designation   | Current/voltage measuring module   |
| <b>General technical data</b>   |  |
| measuring procedure   | RMS value measurement  |
| size of the circuit-breaker   | S6   |
| product function  | <ul style="list-style-type: none"> <li>• current measurement</li> <li>• voltage measurement</li> <li>• active power measurement</li> <li>• energy measurement</li> <li>• frequency measurement</li> <li>• active power monitoring for pump dry-run according to Ignition protection type Ex b</li> </ul> |
| measuring procedure for current measurement                                     | TRMS   |
| current measuring range extension with external current transformers            | No   |
| measuring procedure for voltage measurement                                     | TRMS   |
| measurable supply voltage between the line conductors at AC maximum rated value | 690 V  |
| product component   | <ul style="list-style-type: none"> <li>• input for thermistor connection</li> </ul>  |
| consumed active power   | 0.5 W  |
| insulation voltage  | <ul style="list-style-type: none"> <li>• with degree of pollution 3 at AC rated value</li> <li>• for wires of main circuit according to IEC 60947-1 rated value</li> </ul>   |
| surge voltage resistance rated value  | 6 000 V  |
| shock resistance according to IEC 60068-2-27                                    | 15g / 11 ms; with basic unit snapped on  |
| vibration resistance  | 1-6 Hz / 15 mm; 6-500 Hz / 2 g; with basic unit snapped on: 1g   |
| Substance Prohibitance (Date)   | 05/28/2009   |
| SVHC substance name   | Lead - 7439-92-1<br>Lead monoxide (lead oxide) - 1317-36-8<br>2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one - 71868-10-5  |
| Net Weight  | 0.698 kg   |
| <b>Electromagnetic compatibility</b>  |  |
| EMC emitted interference according to IEC 60947-1                               | class A  |
| EMC immunity according to IEC 60947-1   | corresponds to degree of severity 3  |
| conducted interference  | <ul style="list-style-type: none"> <li>• due to burst according to IEC 61000-4-4</li> <li>• due to conductor-earth surge according to IEC 61000-4-5</li> <li>• due to conductor-conductor surge according to IEC</li> </ul>  |
| 2 kV  |  |
| 2 kV  |  |
| 1 kV  |  |

|   |  |
|---|--|
| 61000-4-5   |  |
| field-based interference according to IEC 61000-4-3                 | 10 V/m   |
| <b>Inputs/ Outputs</b>  |  |
| number of outputs as contact-affected switching element             | 0  |
| <b>Protective and monitoring functions</b>                          |  |
| product function  |  |
| • power factor monitoring   | Yes  |
| • ground-fault monitoring   | Yes  |
| • voltage detection   | Yes  |
| trip class  | CLASS 5E   |
| product function  |  |
| • current detection   | Yes  |
| • overload protection   | Yes  |
| <b>Precision</b>  |  |
| <b>measuring precision</b>  |  |
| • of frequency measurement  | +/- 1.5 %, 15 A ... 400 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C                            |
| • for current measurement 1   | +/- 1.5 %, in range 400 A ... 1600 A, in range 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), 50/60 Hz, 25 °C                           |
| • for current measurement 2   | +/- 5 %, in range 400 A ... 1600 A, in range 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), 50/60 Hz, 25 °C                             |
| • for voltage measurement 1   | +/- 1.5 %, in range 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), 50/60 Hz, 25 °C  |
| • at cos phi-measurement 1  | +/- 1.5 %, 15 A ... 400 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C                            |
| • at cos phi-measurement 2  | +/- 5 %, 400 A ... 1600 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C                            |
| • for active power measurement 1                                    | +/- 5 %, 15 A ... 400 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C                              |
| • for active power measurement 2                                    | +/- 10 %, 400 A ... 1600 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C                           |
| • for energy measurement 1  | +/- 5 %, 47 A ... 1260 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C                             |
| • for energy measurement 2  | +/- 10 %, 400 A ... 1600 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C                           |
| • for apparent power measurement 1                                  | +/- 3 %, 15 A ... 400 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C                              |
| • for apparent power measurement 2                                  | +/- 5 %, 400 A ... 1600 A, 0.85 x 110 V ... 1.1 x 690 V (line-to-line voltages), cos phi (0.5...1), 50/60 Hz, 25 °C                            |
| accuracy of ground-fault monitoring                                 | In the range 30 % .. 120 %/Is: +/- 10 % (Class CI-A), in range 15 % .. 30 % le: +/- 25 % (Class CI-B), both values acc. to IEC 60947-1 Annex T |
| temperature drift per °C  | 0.01 %/°C; Reference temperature: 25°C   |
| measured variable frequency   | 45 ... 65 Hz   |
| <b>Installation/ mounting/ dimensions</b>                           |  |
| mounting position   | any  |
| fastening method  | screw and snap-on mounting   |
| height  | 95 mm  |
| width   | 120 mm   |
| depth   | 145 mm   |
| required spacing  |  |
| • top   | 30 mm  |
| • bottom  | 30 mm  |
| • left  | 0 mm   |
| • right   | 0 mm   |
| diameter of inlet opening   | 25 mm  |
| diameter of inlet opening for current measurement                   | 25 mm  |
| <b>Connections/ Terminals</b>                                       |  |
| type of electrical connection                                       |  |
| • for main current circuit  | straight-through transformers  |
| • for auxiliary and control circuit                                 | screw-type terminals   |
| type of electrical connection at the measurement inputs for voltage | screw-type terminals   |
| type of connectable conductor cross-sections at the                 |  |

|  |  |
|--|--|
| <b>measurement inputs for voltage</b>  |  |
| • finely stranded with core end processing   | 1x (0.5 ... 2.5 mm <sup>2</sup> ), 2x (0.5 ... 1.5 mm <sup>2</sup> )   |
| • solid  | 1x (0.5 ... 4 mm <sup>2</sup> ), 2x (0.5 ... 2.5 mm <sup>2</sup> )   |
| • for AWG cables solid   | 1x (20 ... 12), 2x (20 ... 14)   |
| • for AWG cables stranded  | 1x (20 ... 14), 2x (20 ... 16)   |
| <b>tightening torque at the measurement inputs for voltage</b>                             | 0.8 ... 1.2 N·m  |
| <b>tightening torque [lbf·in] at the measurement inputs for voltage</b>                    | 7 ... 10.3 lbf·in  |
| <b>Ambient conditions</b>  |  |
| <b>installation altitude at height above sea level</b>                                     |  |
| • 1 maximum  | 2 000 m  |
| • 2 maximum  | 3 000 m; max. +50 °C (no protective separation)  |
| • 3 maximum  | 4 000 m; max. +40 °C (no protective separation)  |
| <b>ambient temperature</b>   |  |
| • during operation   | -25 ... +60 °C   |
| • during storage   | -40 ... +80 °C   |
| • during transport   | -40 ... +80 °C   |
| <b>environmental category</b>  |  |
| • during operation according to IEC 60721  | 3K6 (no formation of ice, no condensation, relative humidity 10 ... 95%), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6  |
| • during storage according to IEC 60721  | 1K6 (no condensation, relative humidity 10 ... 95%), 1C2 (no salt mist), 1S2 (sand must not get into the devices), 1M4   |
| • during transport according to IEC 60721  | 2K2, 2C1, 2S1, 2M2   |
| <b>relative humidity during operation</b>  | 10 ... 95 %  |
| <b>Short-circuit protection</b>  |  |
| <b>product function short circuit protection</b>   | No   |
| IEC 61508  |  |
| Safety Integrity Level (SIL) according to IEC 61508  | 1  |
| <b>ATEX</b>  |  |
| <b>certificate of suitability</b>  |  |
| • IECEx  | Yes; IECEx PTB 18.0004X  |
| • according to ATEX directive 2014/34/EU   | BVS 06 ATEX F001, PTB 18 ATEX 5003 X   |
| • according to UKCA  | ITS21UKEX0464, ITS21UKEX0455X  |
| explosion device group and category according to ATEX directive 2014/34/EU                 | II (2) G, II (2) D, I (M2) / I (M2), II (1/2) G, II (1G/2D)  |
| <b>Galvanic isolation</b>  |  |
| <b>(electrically) protective separation according to IEC 60947-1</b>                       | All circuits with protective separation (double creepage paths and clearances), the information in the "Protective Separation" test report, No. A0258, must be observed (link see further information) |
| <b>Main circuit</b>  |  |
| <b>number of poles for main current circuit</b>  | 3  |
| <b>adjustable current response value current of the current-dependent overload release</b> | 20 ... 200 A   |
| <b>operating voltage</b>   |  |
| • at AC  |  |
| — at 50 Hz rated value   | 110 ... 690 V  |
| — at 60 Hz rated value   | 110 ... 690 V  |
| <b>operating frequency rated value</b>   | 50 ... 60 Hz   |
| <b>Control circuit/ Control</b>  |  |
| <b>type of voltage</b>   | AC   |
| <b>inrush current maximum</b>  | 2 000 A; 10 x Io   |
| <b>Approvals Certificates</b>  |  |
| <b>Environment</b>   | <b>General Product Approval</b>  |



[Environmental Confirmations](#)



General Product Approval

EMV

For use in hazardous locations



| For use in hazardous locations | Test Certificates             |  |  | Maritime application                     |
|--------------------------------|-------------------------------|--|--|--|
|                                | <a href="#">Miscellaneous</a> | <a href="#">Type Test Certificates/Test Report</a> | <a href="#">Special Test Certificate</a> | <a href="#">Special Test Certificate</a> |
| IECEx                          |                               |  |  | AMERICAN BUREAU<br>OF SHIPPING           |
| Maritime application           | other                         |  | Confirmation                             | Industrial Communication                 |
|                                |                               |  |  |  |

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UF7123-1AA01-0>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UF7123-1AA01-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3UF7123-1AA01-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3UF7123-1AA01-0&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UF7123-1AA01-0&lang=en)



