



Figure similar

transformer SITAS; phases: 1; Pn/Pn(S6)(kVA): 4 /16.1; Upri(V): 500+/-5%; Usec(V): 110; Isec(A): 36.4; F(Hz): 50...60; vector group/shielding winding: II0 /0; temperature rise/insulation class: 55 /H; IP00; connection: screw connection; mounting: screws; EN 61558-2-1, -2-2, -2-4 >UL/CSA-recognized< >control transformer< >isolation transformer<

General technical data

product designation		transformer SITAS
product brand name		SIDAC
operating apparent power rated value	VA	4 000
efficiency		0.95
connection method for transformers		II0
certificate of suitability		CE
product function		
• temperature monitoring		No
• insulation monitoring		No
• short-circuit and overload proof		No
number of shielding windings		0
short-term vector power	VA	17 800
relative short-circuit voltage	%	2.8

Inputs

phase number of the inputs		1
input voltage		
• _1 rated value	V	525
• _2 rated value	V	500
• _3 rated value	V	475
electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60

Outputs

phase number of the outputs		1
output voltage		
• _1 rated value	V	110
electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50

Ambient conditions

thermal class according to IEC 60085		H
ambient temperature rated value	°C	55
protection class IP		IP00

Mechanical data

type of electrical connection		
• at output for main current circuit		screw-type terminals
• at input for main current circuit		screw-type terminals

fastening method		screws
construction form of the iron core		UI 150/75
width	m	0.164
height	m	0.27
depth	m	0.155

Certificates/ approvals

General Product Approval	other	Environment
--------------------------	-------	-------------



[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AT3032-5FJ10-0FA0>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AT3032-5FJ10-0FA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AT3032-5FJ10-0FA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AT3032-5FJ10-0FA0&lang=en

last modified:

4/2/2025