

Siemens  
EcoTech



Illuminated mushroom pushbutton, 22 mm, round, metal, shiny, amber, 40 mm, momentary contact type



|                                                    |                                  |
|----------------------------------------------------|----------------------------------|
| product brand name                                 | SIRIUS ACT                       |
| product designation                                | Mushroom pushbuttons             |
| design of the product                              | Actuating/signaling element      |
| product type designation                           | 3SU1                             |
| product line                                       | Metal, shiny, 22 mm              |
| <b>Enclosure</b>                                   |                                  |
| number of command points                           | 1                                |
| <b>Actuator</b>                                    |                                  |
| design of the actuating element                    | illuminated                      |
| principle of operation of the actuating element    | momentary contact type           |
| product extension optional light source            | Yes                              |
| color of the actuating element                     | amber                            |
| material of the actuating element                  | plastic                          |
| shape of the actuating element                     | round                            |
| outer diameter of the actuating element            | 40 mm                            |
| number of switching positions                      | 2                                |
| <b>Front ring</b>                                  |                                  |
| product component front ring                       | Yes                              |
| design of the front ring                           | Standard                         |
| material of the front ring                         | Metal, high gloss                |
| color of the front ring                            | silver                           |
| <b>General technical data</b>                      |                                  |
| product function                                   |                                  |
| • EMERGENCY OFF function                           | No                               |
| • EMERGENCY STOP function                          | No                               |
| protection class IP                                | IP66, IP67, IP69(IP69K)          |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13       |
| shock resistance                                   |                                  |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms |
| vibration resistance                               |                                  |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                |
| operating frequency maximum                        | 3 600 1/h                        |
| mechanical service life (operating cycles) typical | 3 000 000                        |
| reference code according to IEC 81346-2            | S                                |
| Substance Prohibitance (Date)                      | 10/01/2014                       |
| Net Weight                                         | 49 g                             |

| Ambient conditions                                             |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| <b>ambient temperature</b>                                     |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

| Installation/ mounting/ dimensions                 |         |
|----------------------------------------------------|---------|
| <b>height</b>                                      | 40 mm   |
| <b>width</b>                                       | 40 mm   |
| <b>shape of the installation opening</b>           | round   |
| <b>mounting diameter</b>                           | 22.3 mm |
| <b>positive tolerance of installation diameter</b> | 0.4 mm  |
| <b>mounting height</b>                             | 27.5 mm |
| <b>installation width</b>                          | 40 mm   |
| <b>installation depth</b>                          | 24.4 mm |

| Approvals Certificates                                     |                                 |
|------------------------------------------------------------|---------------------------------|
| Environmental Product Declaration                          |                                 |
| • global warming potential [CO2 eq] / during manufacturing | 0.625 kg                        |
| • global warming potential [CO2 eq] / during operation     | 0.235 kg                        |
| • global warming potential [CO2 eq] / after end of life    | -0.267 kg                       |
| • global warming potential [CO2 eq] / total                | 0.593 kg                        |
| <b>Environment</b>                                         | <b>General Product Approval</b> |




[Environmental Confirmations](#)



| General Product Approval | Test Certificates                                  | Maritime application |
|--------------------------|----------------------------------------------------|----------------------|
|                          | <a href="#">Type Test Certificates/Test Report</a> |                      |
|                          |                                                    |                      |
|                          |                                                    |                      |
|                          |                                                    |                      |

| other                        |
|------------------------------|
|                              |
| <a href="#">Confirmation</a> |

| Further information                                                                                                                                                                                                                                                                                                |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Information on the packaging<br><a href="https://support.industry.siemens.com/cs/ww/en/view/109813875">https://support.industry.siemens.com/cs/ww/en/view/109813875</a>                                                                                                                                            |
| Information for data generation and storage<br><a href="https://support.industry.siemens.com/cs/ww/en/view/109995012">https://support.industry.siemens.com/cs/ww/en/view/109995012</a>                                                                                                                             |
| Information- and Downloadcenter (Catalogs, Brochures,...)<br><a href="https://www.siemens.com/ic10">https://www.siemens.com/ic10</a>                                                                                                                                                                               |
| Industry Mall (Online ordering system)<br><a href="https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1051-1BD00-0AA0">https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1051-1BD00-0AA0</a>                                                                                  |
| Cax online generator<br><a href="https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&amp;mlfb=3SU1051-1BD00-0AA0">https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&amp;mlfb=3SU1051-1BD00-0AA0</a>                                                                      |
| Service&Support (Manuals, Certificates, Characteristics, FAQs,...)<br><a href="https://support.industry.siemens.com/cs/ww/en/ps/3SU1051-1BD00-0AA0">https://support.industry.siemens.com/cs/ww/en/ps/3SU1051-1BD00-0AA0</a>                                                                                        |
| Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)<br><a href="https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1051-1BD00-0AA0&amp;lang=en">https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1051-1BD00-0AA0&amp;lang=en</a> |



last modified:

4/2/2025 