



SIMATIC ET 200SP, digital output module, DQ 16x 24VDC/0.5A Basic, Pack quantity: 10 units, suitable for BU type A0, Color code CC00, Module diagnostics



Figure similar

General information	
Product type designation	DQ 16x24VDC/0.5A BA
HW functional status	From FS03
Firmware version	V0.0
• FW update possible	No
usable BaseUnits	BU type A0
Color code for module-specific color-coded label	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V14
• STEP 7 configurable/integrated from version	STEP 7 V5.5 or higher
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• DQ	Yes
• DQ with energy-saving function	No
• PWM	No
• Oversampling	No
• MSO	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	55 mA; without load
Output voltage	
Rated value (DC)	24 V
Power loss	
Power loss, typ.	1 W
Address area	
Address space per module	
• Outputs	2 byte

Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	
• 1-wire connection	BU type A0
• 2-wire connection	BU type A0 + Potential distributor module
• 3-wire connection	BU type A0 + Potential distributor module
• 4-wire connection	BU type A0 + Potential distributor module
Digital outputs	
Type of digital output	Source output (PNP, current-sourcing)
Number of digital outputs	16
Current-sinking	No
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
Short-circuit protection	Yes
• Response threshold, typ.	1.4 A; 0.7 to 1.9 A
Open-circuit detection	No
Limitation of inductive shutdown voltage to	Typ. L+ (-53 V)
Controlling a digital input	Yes
Switching capacity of the outputs	
• with resistive load, max.	0.5 A
• on lamp load, max.	5 W
Load resistance range	
• lower limit	48 Ω
• upper limit	100 kΩ
Output current	
• for signal "1" rated value	0.5 A
• for signal "0" residual current, max.	30 μA
Output delay with resistive load	
• "0" to "1", typ.	80 μs; at rated load
• "0" to "1", max.	150 μs; at rated load
• "1" to "0", typ.	100 μs; at rated load
• "1" to "0", max.	200 μs; at rated load
Parallel switching of two outputs	
• for uprating	No
• for redundant control of a load	Yes
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load, max.	2 Hz
• on lamp load, max.	10 Hz
Total current of the outputs	
• Current per channel, max.	0.5 A
• Current per module, max.	8 A
Total current of the outputs (per module)	
horizontal installation	
— up to 60 °C, max.	8 A
vertical installation	
— up to 50 °C, max.	8 A
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Monitoring the supply voltage	Yes

• Wire-break • Short-circuit • Group error	No No Yes																																										
Diagnostics indication LED																																											
• Monitoring of the supply voltage (PWR-LED) • Channel status display • for channel diagnostics • for module diagnostics	Yes; green PWR LED Yes; green LED No Yes; green/red DIAG LED																																										
Potential separation																																											
Potential separation channels																																											
• between the channels • between the channels and backplane bus	No Yes																																										
Isolation																																											
Isolation tested with	707 V DC (type test)																																										
Standards, approvals, certificates																																											
Suitable for safety functions	No																																										
Ecological footprint																																											
• environmental product declaration	Yes																																										
Global warming potential																																											
— global warming potential, (total) [CO2 eq] — global warming potential, (during production) [CO2 eq] — global warming potential, (during operation) [CO2 eq] — global warming potential, (after end of life cycle) [CO2 eq]	29.3 kg 3.98 kg 25.6 kg -0.245 kg																																										
Ambient conditions																																											
Ambient temperature during operation																																											
• horizontal installation, min. • horizontal installation, max. • vertical installation, min. • vertical installation, max.	-30 °C 60 °C -30 °C 50 °C																																										
Altitude during operation relating to sea level																																											
• Installation altitude above sea level, max.	2 000 m; On request: Installation altitudes greater than 2 000 m																																										
Dimensions																																											
Width	15 mm																																										
Height	73 mm																																										
Depth	58 mm																																										
Weights																																											
Weight, approx.	30 g																																										
Classifications																																											
	<table><tr><td></td><td>Version</td><td>Classification</td></tr><tr><td>eClass</td><td>14</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>12</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>9.1</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>9</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>8</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>7.1</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>6</td><td>27-24-26-04</td></tr><tr><td>ETIM</td><td>10</td><td>EC001599</td></tr><tr><td>ETIM</td><td>9</td><td>EC001599</td></tr><tr><td>ETIM</td><td>8</td><td>EC001599</td></tr><tr><td>ETIM</td><td>7</td><td>EC001599</td></tr><tr><td>IDEA</td><td>4</td><td>3566</td></tr><tr><td>UNSPSC</td><td>15</td><td>32-15-17-05</td></tr></table>		Version	Classification	eClass	14	27-24-26-04	eClass	12	27-24-26-04	eClass	9.1	27-24-26-04	eClass	9	27-24-26-04	eClass	8	27-24-26-04	eClass	7.1	27-24-26-04	eClass	6	27-24-26-04	ETIM	10	EC001599	ETIM	9	EC001599	ETIM	8	EC001599	ETIM	7	EC001599	IDEA	4	3566	UNSPSC	15	32-15-17-05
	Version	Classification																																									
eClass	14	27-24-26-04																																									
eClass	12	27-24-26-04																																									
eClass	9.1	27-24-26-04																																									
eClass	9	27-24-26-04																																									
eClass	8	27-24-26-04																																									
eClass	7.1	27-24-26-04																																									
eClass	6	27-24-26-04																																									
ETIM	10	EC001599																																									
ETIM	9	EC001599																																									
ETIM	8	EC001599																																									
ETIM	7	EC001599																																									
IDEA	4	3566																																									
UNSPSC	15	32-15-17-05																																									
Approvals / Certificates																																											
General Product Approval																																											



[Manufacturer Declaration](#)

[China RoHS](#)

[Miscellaneous](#)



Maritime application

Environment



Siemens
EcoTech



last modified:

10/23/2025