



Selector switch, illuminable, 22 mm, round, plastic with metal front ring, white, selector switch, short, 3 switch positions I-O-II, latching, actuating angle 2x45°, 10:30h/12h/13:30h, with holder, 1 NO, 1 NO, spring-type terminal, with laser labeling, upper case

|                                                 |                                              |
|-------------------------------------------------|----------------------------------------------|
| product brand name                              | SIRIUS ACT                                   |
| product designation                             | Selector switches                            |
| design of the product                           | Complete unit                                |
| product type designation                        | 3SU1                                         |
| product line                                    | Plastic with metal front ring, matt, 22 mm   |
| manufacturer's article number                   |                                              |
| • of supplied contact module at position 1      | <a href="#">3SU1400-1AA10-3BA0</a>           |
| • of supplied contact module at position 2      | <a href="#">3SU1400-1AA10-3BA0</a>           |
| • of the supplied holder                        | <a href="#">3SU1550-0AA10-0AA0</a>           |
| • of the supplied actuator                      | <a href="#">3SU1032-2BL60-0AA0</a>           |
| <b>Enclosure</b>                                |                                              |
| number of command points                        | 1                                            |
| <b>Actuator</b>                                 |                                              |
| design of the actuating element                 | Selector, short                              |
| principle of operation of the actuating element | latching, 2x45° (10:30 h/12 h/13:30 h)       |
| product extension optional light source         | Yes                                          |
| color of the actuating element                  | white                                        |
| material of the actuating element               | plastic                                      |
| shape of the actuating element                  | round                                        |
| outer diameter of the actuating element         | 32.3 mm                                      |
| marking of the actuating element                | Customized labeling, text in capital letters |
| number of contact modules                       | 2                                            |
| number of switching positions                   | 3                                            |
| actuating angle                                 |                                              |
| • clockwise                                     | 45°                                          |
| • anticlockwise                                 | 45°                                          |
| <b>Front ring</b>                               |                                              |
| product component front ring                    | Yes                                          |
| design of the front ring                        | standard                                     |
| material of the front ring                      | Metal, matt                                  |
| color of the front ring                         | sand gray                                    |
| <b>Holder</b>                                   |                                              |
| material of the holder                          | Plastic                                      |
| <b>Display</b>                                  |                                              |
| number of LED modules                           | 0                                            |
| <b>General technical data</b>                   |                                              |
| product function positive opening               | No                                           |
| product component light source                  | No                                           |
| insulation voltage rated value                  | 500 V                                        |

|                                                                         |                                                                                                                                               |
|-------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| <b>degree of pollution</b>                                              | 3                                                                                                                                             |
| type of voltage of the operating voltage                                | AC/DC                                                                                                                                         |
| <b>surge voltage resistance rated value</b>                             | 6 kV                                                                                                                                          |
| <b>protection class IP</b>                                              | IP66, IP67, IP69(IP69K)                                                                                                                       |
| protection class IP of the terminal                                     | IP20                                                                                                                                          |
| <b>degree of protection NEMA rating</b>                                 | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                                                                    |
| <b>shock resistance</b>                                                 |                                                                                                                                               |
| • according to IEC 60068-2-27                                           | sinusoidal half-wave 15g / 11 ms                                                                                                              |
| • for railway applications according to EN 61373                        | Category 1, Class B                                                                                                                           |
| <b>vibration resistance</b>                                             |                                                                                                                                               |
| • according to IEC 60068-2-6                                            | 10 ... 500 Hz: 5g                                                                                                                             |
| • for railway applications according to EN 61373                        | Category 1, Class B                                                                                                                           |
| <b>operating frequency maximum</b>                                      | 1 800 1/h                                                                                                                                     |
| <b>mechanical service life (operating cycles) typical</b>               | 1 000 000                                                                                                                                     |
| electrical endurance (operating cycles) typical                         | 10 000 000                                                                                                                                    |
| <b>thermal current</b>                                                  | 10 A                                                                                                                                          |
| <b>reference code according to IEC 81346-2</b>                          | S                                                                                                                                             |
| <b>continuous current of the C characteristic MCB</b>                   | 10 A; for a short-circuit current smaller than 400 A                                                                                          |
| <b>continuous current of the quick DIAZED fuse link</b>                 | 10 A                                                                                                                                          |
| <b>continuous current of the DIAZED fuse link gG</b>                    | 10 A                                                                                                                                          |
| <b>Substance Prohibitance (Date)</b>                                    | 10/01/2014                                                                                                                                    |
| <b>Net Weight</b>                                                       | 0.1 kg                                                                                                                                        |
| <b>operating voltage</b>                                                |                                                                                                                                               |
| • at AC                                                                 |                                                                                                                                               |
| — at 50 Hz rated value                                                  | 5 ... 500 V                                                                                                                                   |
| — at 60 Hz rated value                                                  | 5 ... 500 V                                                                                                                                   |
| • at DC rated value                                                     | 5 ... 500 V                                                                                                                                   |
| <b>Power Electronics</b>                                                |                                                                                                                                               |
| <b>contact reliability</b>                                              | One maloperation per 100 million (17 V, 5 mA), one maloperation per 10 million (5 V, 1 mA)                                                    |
| <b>Auxiliary circuit</b>                                                |                                                                                                                                               |
| <b>design of the contact of auxiliary contacts</b>                      | Silver alloy                                                                                                                                  |
| <b>number of NC contacts for auxiliary contacts</b>                     | 0                                                                                                                                             |
| <b>number of NO contacts for auxiliary contacts</b>                     | 2                                                                                                                                             |
| <b>Connections/ Terminals</b>                                           |                                                                                                                                               |
| <b>type of electrical connection</b>                                    | spring-loaded terminals                                                                                                                       |
| • of modules and accessories                                            | Spring-type terminal                                                                                                                          |
| <b>type of connectable conductor cross-sections</b>                     |                                                                                                                                               |
| • solid without core end processing                                     | 2x (0.25 ... 1.5 mm <sup>2</sup> )                                                                                                            |
| • finely stranded with core end processing                              | 2x (0.25 ... 0.75 mm <sup>2</sup> )                                                                                                           |
| • finely stranded without core end processing                           | 2x (0.25 ... 1.5 mm <sup>2</sup> )                                                                                                            |
| • for AWG cables                                                        | 2x (24 ... 16)                                                                                                                                |
| <b>tightening torque of the screws in the bracket</b>                   | 1 ... 1.2 N·m                                                                                                                                 |
| <b>Safety related data</b>                                              |                                                                                                                                               |
| <b>proportion of dangerous failures</b>                                 |                                                                                                                                               |
| • with low demand rate according to SN 31920                            | 20 %                                                                                                                                          |
| <b>B10 value with high demand rate according to SN 31920</b>            | 300 000                                                                                                                                       |
| <b>IEC 61508</b>                                                        |                                                                                                                                               |
| T1 value for proof test interval or service life according to IEC 61508 | 20 a                                                                                                                                          |
| <b>Ambient conditions</b>                                               |                                                                                                                                               |
| <b>ambient temperature</b>                                              |                                                                                                                                               |
| • during operation                                                      | -25 ... +70 °C                                                                                                                                |
| • during storage                                                        | -40 ... +80 °C                                                                                                                                |
| environmental category during operation according to IEC 60721          | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted for all devices behind front panel) |
| <b>Installation/ mounting/ dimensions</b>                               |                                                                                                                                               |
| <b>fastening method</b>                                                 |                                                                                                                                               |
| • of modules and accessories                                            | Front plate mounting                                                                                                                          |

|                                             |         |
|---------------------------------------------|---------|
| height                                      | 40 mm   |
| width                                       | 32.3 mm |
| shape of the installation opening           | round   |
| mounting diameter                           | 22.3 mm |
| positive tolerance of installation diameter | 0.4 mm  |
| mounting height                             | 28.8 mm |
| installation width                          | 32.3 mm |
| installation depth                          | 49.7 mm |

#### Approvals Certificates

|             |                          |                   |
|-------------|--------------------------|-------------------|
| Environment | General Product Approval | Test Certificates |
|-------------|--------------------------|-------------------|

[Environmental Conformations](#)



[Type Test Certificates/Test Report](#)

|                   |                      |       |
|-------------------|----------------------|-------|
| Test Certificates | Maritime application | other |
|-------------------|----------------------|-------|

[Special Test Certificate](#)



[Confirmation](#)

other



#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1130-2BL60-3NA0-Z Y11>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1130-2BL60-3NA0-Z Y11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1130-2BL60-3NA0-Z Y11>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1130-2BL60-3NA0-Z Y11&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1130-2BL60-3NA0-Z Y11&lang=en)



last modified:

4/2/2025 