



SIMATIC ET 200SP, digital output module, DQ 4x 24...230V AC/2A Standard suitable for BU type B1, Color code CC41, Module diagnostics

General information	
Product type designation	DQ 4x24 ... 230 V AC/2 A ST
HW functional status	From FS05
Firmware version	V1.0
• FW update possible	Yes
usable BaseUnits	BU type B1
Color code for module-specific color-coded label	CC41
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V13 / V13
• STEP 7 configurable/integrated from version	V5.5 SP3 / -
• PROFIBUS from GSD version/GSD revision	GSD Revision 5
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• DQ	Yes
• DQ with energy-saving function	No
• PWM	No
• Oversampling	No
• MSO	No
Supply voltage	
Rated value (AC)	230 V
permissible range, lower limit (AC)	20.4 V
permissible range, upper limit (AC)	264 V
Input current	
Current consumption (rated value)	11.5 mA
Output voltage	
Rated value (AC)	230 V; 24V AC to 230V AC
Power loss	
Power loss, typ.	9 W; Active power, load voltage 230 V, all outputs loaded with 2 A, 50 Hz
Address area	
Address space per module	
• Address space per module, max.	1 byte; + 1 byte for QI information
• Inputs	1 byte; With QI
• Outputs	1 byte

Hardware configuration	
Automatic encoding	
• Type of mechanical coding element	type C
Digital outputs	
Type of digital output	Triac with zero point detection
Number of digital outputs	4
Current-sinking	No
Current-sourcing	Yes
Digital outputs, parameterizable	No
Short-circuit protection	No; When using BU type B1, a miniature, quick-response fuse with 10 A tripping current must be provided
Controlling a digital input	Yes
Size of motor starters according to NEMA, max.	5
Switching capacity of the outputs	
• with resistive load, max.	2 A
• on lamp load, max.	100 W
Output voltage	
• for signal "1", min.	20.4 V
Output current	
• for signal "1" rated value	2 A
• for signal "1" permissible range, min.	10 mA
• for signal "1" permissible range, max.	2 A
• for signal "0" residual current, max.	460 µA
Output delay with resistive load	
• "0" to "1", max.	10 ms
• "1" to "0", max.	10 ms
Parallel switching of two outputs	
• for logic links	No
• for uprating	No
• for redundant control of a load	Yes
Switching frequency	
• with resistive load, max.	10 Hz
• with inductive load, max.	0.5 Hz; Higher frequencies are possible, see Equipment Manual / Product Information
• on lamp load, max.	1 Hz
Total current of the outputs	
• Current per channel, max.	2 A
• Current per module, max.	8 A
Total current of the outputs (per module)	
horizontal installation	
— up to 40 °C, max.	8 A
— up to 50 °C, max.	6 A
— up to 60 °C, max.	4 A
vertical installation	
— up to 30 °C, max.	8 A
— up to 40 °C, max.	6 A
— up to 50 °C, max.	4 A
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Interrupts/diagnostics/status information	
Diagnostics function	No
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	No
Diagnoses	
• Monitoring the supply voltage	No
• Wire-break	No
• Short-circuit	No

• Group error	Yes		
Diagnostics indication LED			
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED		
• Channel status display	Yes; green LED		
• for channel diagnostics	No		
• for module diagnostics	Yes; green/red DIAG LED		
Potential separation			
Potential separation channels			
• between the channels	No		
• between the channels and backplane bus	Yes		
• between the channels and the power supply of the electronics	No		
Isolation			
Isolation tested with	2 545 V DC/2 s (routine test)		
Standards, approvals, certificates			
Suitable for safety functions	No		
Ecological footprint			
• environmental product declaration	Yes		
Global warming potential			
— global warming potential, (total) [CO2 eq]	13.9 kg		
— global warming potential, (during production) [CO2 eq]	5.53 kg		
— global warming potential, (during operation) [CO2 eq]	8.71 kg		
— global warming potential, (after end of life cycle) [CO2 eq]	-0.359 kg		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.	-30 °C		
• horizontal installation, max.	60 °C		
• vertical installation, min.	-30 °C		
• vertical installation, max.	60 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	2 000 m; On request: Installation altitudes greater than 2 000 m		
Dimensions			
Width	20 mm		
Height	73 mm		
Depth	58 mm		
Weights			
Weight, approx.	50 g		
Classifications			
		Version	Classification
	eClass	14	27-24-26-04
	eClass	12	27-24-26-04
	eClass	9.1	27-24-26-04
	eClass	9	27-24-26-04
	eClass	8	27-24-26-04
	eClass	7.1	27-24-26-04
	eClass	6	27-24-26-04
	ETIM	10	EC001599
	ETIM	9	EC001599
	ETIM	8	EC001599
	ETIM	7	EC001599
	IDEA	4	3566
	UNSPSC	15	32-15-17-05
Approvals / Certificates			
General Product Approval			



[Manufacturer Declaration](#)

[Miscellaneous](#)

[China RoHS](#)



General Product Approval

For use in hazardous locations

Maritime application



[EM](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)

Maritime application

Environment



Siemens
EcoTech



last modified:

9/19/2025