



SIMATIC DP, electronic module ET 200SP, F-AI 4xI0(4)..20 mA HF fail-safe analog inputs up to PL e (ISO 13849) up to SIL 3 (IEC 61508)

General information	
Product type designation	F-AI 4xI 0(4)..20mA 2-/4-wire HF
Firmware version	
• FW update possible	Yes
usable BaseUnits	BU type A0, A1
Color code for module-specific color-coded label	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V15 with HSP 203
CiR - Configuration in RUN	
Reparameterization possible in RUN	No
Calibration possible in RUN	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
power supply according to NEC Class 2 required	No
Input current	
Current consumption (rated value)	0.38 A
Current consumption, max.	0.4 A
Encoder supply	
24 V encoder supply	
• 24 V	Yes; min. L+ (-1.5 V)
• Short-circuit protection	Yes
• Output current, max.	300 mA; total current of all encoders/channels
Power	
Power consumption from the backplane bus	70 mW
Power loss	
Power loss, typ.	2 W
Address area	
Address space per module	
• Inputs	14 byte; S7-300/400F CPU, 13 byte
• Outputs	5 byte; S7-300/400F CPU, 4 byte
Hardware configuration	
Automatic encoding	Yes
• Electronic coding element type F	Yes

Analog inputs	
Number of analog inputs	4
• For current measurement	4
permissible input current for current input (destruction limit), max.	35 mA
Input ranges (rated values), currents	
• 0 to 20 mA	Yes
— Input resistance (0 to 20 mA)	125 Ω
• 4 mA to 20 mA	Yes
— Input resistance (4 mA to 20 mA)	125 Ω
Cable length	
• shielded, max.	1 000 m
Analog value generation for the inputs	
Measurement principle	Sigma Delta
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Integration time, parameterizable	Yes
• Integration time (ms)	20 / 16,667
• Interference voltage suppression for interference frequency f_1 in Hz	50 / 60 Hz
Smoothing of measured values	
• Number of smoothing levels	7
• parameterizable	Yes
• Step: None	Yes; 1x conversion cycle time
• Step: low	Yes; 2x / 4x conversion cycle time
• Step: Medium	Yes; 8x / 16x conversion cycle time
• Step: High	Yes; 32x / 64x conversion cycle time
Encoder	
Connection of signal encoders	
• for current measurement as 2-wire transducer	Yes
— Burden of 2-wire transmitter, max.	650 Ω
• for current measurement as 4-wire transducer	Yes
Errors/accuracies	
Linearity error (relative to input range), (+/-)	0.1 %
Temperature error (relative to input range), (+/-)	0.023 %/K
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.1 %
Operational error limit in overall temperature range	
• Current, relative to input range, (+/-)	2 %
Basic error limit (operational limit at 25 °C)	
• Current, relative to input range, (+/-)	0.1 %
Interference voltage suppression for $f = n \times (f_1 +/ - 1 \%)$, f_1 = interference frequency	
• Series mode interference (peak value of interference < rated value of input range), min.	40 dB
• Common mode interference, min.	70 dB
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
• Diagnostic alarm	Yes
• Limit value alarm	No
Diagnoses	
• Monitoring the supply voltage	Yes
• Wire-break	Yes
• Short-circuit	Yes
Diagnostics indication LED	
• RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for channel diagnostics	Yes; red LED

• for module diagnostics	Yes; green/red DIAG LED					
Potential separation						
Potential separation channels						
• between the channels	No					
• between the channels and backplane bus	Yes					
• between the channels and the power supply of the electronics	Yes					
Permissible potential difference						
between the inputs (UCM)	10 Vpp					
Isolation						
Isolation tested with	707 V DC (type test)					
Standards, approvals, certificates						
Ecological footprint						
• environmental product declaration	Yes					
Global warming potential						
— global warming potential, (total) [CO ₂ eq]	88.3 kg					
— global warming potential, (during production) [CO ₂ eq]	13.1 kg					
— global warming potential, (during operation) [CO ₂ eq]	76.6 kg					
— global warming potential, (after end of life cycle) [CO ₂ eq]	-1.37 kg					
Highest safety class achievable in safety mode						
• Performance level according to ISO 13849-1	PLe					
• Category according to ISO 13849-1	Cat. 4					
• SIL acc. to IEC 61508	SIL 3					
Probability of failure (for service life of 20 years and repair time of 100 hours)						
— Low demand mode: PFDavg in accordance with SIL3	< 5.00E-05					
— High demand/continuous mode: PFH in accordance with SIL3	< 1.00E-09 1/h					
Ambient conditions						
Ambient temperature during operation						
• horizontal installation, min.	0 °C					
• horizontal installation, max.	60 °C					
• vertical installation, min.	0 °C					
• vertical installation, max.	50 °C					
Dimensions						
Width	15 mm					
Height	73 mm					
Depth	58 mm					
Weights						
Weight, approx.	48 g					
Classifications						
		Version	Classification			
	eClass	14	27-24-26-01			
	eClass	12	27-24-26-01			
	eClass	9.1	27-24-26-01			
	eClass	9	27-24-26-01			
	eClass	8	27-24-26-01			
	eClass	7.1	27-24-26-01			
	eClass	6	27-24-26-01			
	ETIM	10	EC001596			
	ETIM	9	EC001596			
	ETIM	8	EC001596			
	ETIM	7	EC001596			
	IDEA	4	3562			
	UNSPSC	15	32-15-17-05			



last modified:

10/23/2025