



*** Spare part *** SIMATIC DP, Electronics module for ET 200S, 1 SSI 25 bit/1 MHz 15 mm width, Module for connection of absolute value encoders with SSI Synchronous Serial Interface with DI and comparison value with clock synchronization

Supply voltage	
Load voltage L+	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V
• Reverse polarity protection	Yes
Input current	
from load voltage L+ (without load), max.	40 mA
from backplane bus 3.3 V DC, max.	10 mA
Encoder supply	
24 V encoder supply	
• 24 V	Yes
• Short-circuit protection	Yes
• Output current, max.	500 mA
Absolute encoder (SSI) encoder supply	
• Absolute encoder (SSI)	Yes
• Type of output voltage	L+ (-0.8 V)
• Short-circuit protection	Yes
• Output current, max.	500 mA
Power loss	
Power loss, typ.	1 W
Hardware configuration	
Module exchange	
• Module exchange during operation of the IM-DP	Yes
• Module exchange under process voltage	Yes
Digital inputs	
Number of digital inputs	1
Input voltage	
• for signal "0"	-30 to +5 V
• for signal "1"	+11 to +30V
Input current	
• for signal "0", max. (permissible quiescent current)	2 mA
• for signal "1", typ.	9 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— at "0" to "1", max.	300 µs
— at "1" to "0", max.	300 µs
Cable length	
• shielded, max.	50 m

Encoder			
Number of connectable encoders, max.	1		
Connectable encoders			
• Absolute encoder (SSI)	Yes		
• 2-wire sensor	Yes; Type 2		
Encoder signals, absolute encoder (SSI)			
• Input signal	to RS-422		
• Telegram length, parameterizable	13, 14, 16, 21, 24 & 25 bit		
• Binary code	Yes		
• Gray code	Yes		
• Cable length, shielded, max.	320 m; At 125 kHz		
• Monoflop time	16/32/48/64 µs		
Interrupts/diagnostics/status information			
Diagnostics indication LED			
• Group error SF (red)	Yes		
• Status indicator digital input (green)	Yes		
• Status indicator forward counting (green)	Yes		
• Status indicator backward counting (green)	Yes		
Potential separation			
Potential separation digital inputs			
• Potential separation digital inputs	No; same potential with L+ and SSI		
Potential separation counter			
• between the channels and backplane bus	Yes		
• Between the channels and load voltage L+	No		
Dimensions			
Width	15 mm		
Height	81 mm		
Depth	52 mm		
Weights			
Weight, approx.	40 g		
Classifications			
		Version	Classification
	eClass	14	27-24-26-05
	eClass	12	27-24-26-05
	eClass	9.1	27-24-26-05
	eClass	9	27-24-26-05
	eClass	8	27-24-26-05
	eClass	7.1	27-24-26-05
	eClass	6	27-24-26-05
	ETIM	10	EC001601
	ETIM	9	EC001601
	ETIM	8	EC001601
	ETIM	7	EC001601
	IDEA	4	3567
	UNSPSC	15	32-15-17-05
Approvals / Certificates			
General Product Approval			
 EG-Konf.  Manufacturer Declaration Miscellaneous China RoHS  UL			
General Product Approval	EMV	For use in hazardous locations	



[FM](#)



For use in hazardous locations

Maritime application



[Miscellaneous](#)

[CCC-Ex](#)



Maritime application



[NK / Nippon Kaiji Ky-
okai](#)



[CCS \(China Classifica-
tion Society\)](#)

last modified:

8/22/2025