



SIMATIC ET 200SP, BaseUnit BU15-P16+A0+12D/T, BU type A1, Push-in terminals, with 2x 5 add-on terminals, New load group, WxH: 15 mm x 141 mm, with temperature acquisition

General information	
Product type designation	BU type A1
HW functional status	FS10 and higher
Supply voltage	
Rated value (DC)	24 V
external protection for power supply lines	Yes; 24 V DC/10 A miniature circuit breaker with type B or C tripping characteristic
Current carrying capacity	
For P1 and P2 bus, max.	10 A
For process terminals, max.	2 A
Hardware configuration	
Additional terminals	Yes
Temperature sensor	Yes
Formation of potential groups	
• New potential group	Yes
• Potential group continued from the left	No
Slots	
• Number of slots	1; Type A1
Potential separation	
between the potential groups	Yes
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO <sub>2</sub> eq]	1.09 kg
— global warming potential, (during production) [CO <sub>2</sub> eq]	1.08 kg
— global warming potential, (during operation) [CO <sub>2</sub> eq]	0 kg
— global warming potential, (after end of life cycle) [CO <sub>2</sub> eq]	-0.0045 kg
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	

- Installation altitude above sea level, max.

5 000 m; Restrictions for installation altitudes > 2 000 m, see manual

## Accessories

### Color coding labels

- for process terminals
- for AUX terminals
- for add-on terminals

CC00 to CC09  
does not exist  
CC74

## Connection method

### Terminals

- Terminal type
- system-integrated shield connection
- Conductor cross-section, min.
- Conductor cross-section, max.
- Number of process terminals to I/O module
- Number of terminals to AUX bus
- Number of add-on terminals
- Number of terminals with connection to P1 and P2 bus

Push-in terminal  
Yes; Optional  
0.14 mm<sup>2</sup>; AWG 26  
2.5 mm<sup>2</sup>; AWG 14  
16  
0  
2x5  
2

## Dimensions

Width	15 mm
Height	141 mm
Depth	35 mm

## Weights

Weight, approx.	50 g
-----------------	------

## Classifications

	Version	Classification
eClass	14	27-24-26-03
eClass	12	27-24-26-03
eClass	9.1	27-24-26-03
eClass	9	27-24-26-03
eClass	8	27-24-26-03
eClass	7.1	27-24-26-03
eClass	6	27-24-26-03
ETIM	10	EC001598
ETIM	9	EC001598
ETIM	8	EC001598
ETIM	7	EC001598
IDEA	4	3560
UNSPSC	15	32-15-17-04

## Approvals / Certificates

### General Product Approval



last modified:

10/23/2025