

Data sheet

6GK1907-0DC00-6AA5

product type designation

product description

M12 Power T-Tap

Power T-piece with two M12 female contact inserts and one M12 male contact insert, both 5-pin, A-coded

M12 Power T-TAP PRO (A-coded) Power T piece for XP-200 with 2 M12 female contact inserts and one M12 male contact insert; packing unit 5 units.



Technical Product Detail Page

<https://i.siemens.com/1P6GK1907-0DC00-6AA5>

suitability for use

for power connection and power distribution, e.g. to SCALANCE XP-200 switches; suitable for up to 60 V DC and 48 V AC

interfaces

number of electrical connections

- for network components or terminal equipment

3

type of electrical connection

- for network components or terminal equipment

M12 plug (2 x female contact insert, 1 x male contact insert)

type of electrical connection / FastConnect

No

electrical data

voltage / rated value / maximum

60 V

ampacity / of the contacts / maximum

4 A

mechanical data

material / of the enclosure

plastic

locking mechanism design

Screwed joint

tightening torque / for M12 round connector / maximum

0.6 N·m

connector coding / of the M12 circular connector

A

design, dimensions and weights

width

39 mm

height

51.7 mm

depth

21 mm

net weight

34 g

ambient conditions

ambient temperature

-25 ... +90 °C

- during operation

-25 ... +90 °C

- during storage

-25 ... +90 °C

- during transport

chemical resistance

resistant

- to water

protection class IP

IP65/67

product features, product functions, product components / general

product feature

Yes

- silicon-free

product component

Yes

- strain relief

standards, specifications, approvals

certificate of suitability	Yes
• RoHS conformity	No
• UL approval	No
• railway application in accordance with EN 50155	

further information / internet links

internet link	<ul style="list-style-type: none"> • to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to web page: SiePortal • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support 	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/simatic-net https://sieportal.siemens.com https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com
---------------	---	---

security information

security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)</p>
----------------------	---

Approvals / Certificates

General Product Approval



[China RoHS](#)

last modified:

10/30/2025