



SCALANCE XB108-2 unmanaged IE switch, 8x 10/100 Mbit/s Ports, 2x 100 Mbit/s multimode BFOC, for setting up small star and line topologies, LED diagnostics, IP20, redundant power supply 24 V AC/DC Manual available as a download .

product type designation	
product brand name	SCALANCE
product type designation	XB108-2
Technical Product Detail Page	https://i.siemens.com/1P6GK5108-2BB00-2AB2
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	8; RJ45
number of 100 Mbit/s ST(BFOC) ports	
• for multimode	2
transmission method / of the optical interface	100BaseFX
interfaces / other	
number of electrical connections	
• for power supply	1
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	
• supply voltage / 1 / rated value	DC
• power loss [W] / 1 / rated value	24 V
• supply voltage / 1 / voltage range	7.2 W
• consumed current / 1 / maximum	19.2 ... 28.8
• product component / 1 / fusing at power supply input	0.3 A
• fuse protection type / 1 / at input for supply voltage	Yes
• fuse protection type / 1 / at input for supply voltage	0.6 A / 60 V
type of voltage / 2 / of the supply voltage	
• supply voltage / 2 / voltage range	AC
• supply voltage / 2 / voltage range	19.2 ... 28.8
ambient conditions	
ambient temperature	
• during operation	0 ... 60 °C
• during storage	-40 ... +80 °C
• during transport	-40 ... +80 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	80 mm
height	117 mm

depth	109 mm
net weight	0.34 kg
fastening method	
• 35 mm DIN-rail mounting	Yes
• wall mounting	No
• S7-300 rail mounting	No
• S7-1500 rail mounting	No
product functions / management, configuration, engineering	
product function	
• multiport mirroring	No
• CoS	Yes
• switch-managed	No
PROFINET conformity class	A
product functions / redundancy	
product function	
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• cULus approval	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC interference emission	EN 61000-6-4 (Class B)
• for immunity to EMC	61000-6-2
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• ATEX	Yes
• UKEx	Yes
• IECEx	Yes
• ULhazloc approval	Yes
• CCC / for hazardous zone according to GB standard	Yes
• FM registration	Yes
standards, specifications, approvals / other	
certificate of suitability	
• RoHS conformity	Yes
resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	266.77 kg
• during manufacturing	40.94 kg
• during operation	225.32 kg
• after end of life	0.51 kg
product functions / general	
MTBF	71 a
warranty period	5 a
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to website: Industrial communication	https://www.siemens.com/simatic-net
• to web page: SiePortal	https://sieportal.siemens.com/
• to website: Image database	https://www.automation.siemens.com/bilddb

- to website: CAx-Download-Manager
- to website: Industry Online Support

<https://www.siemens.com/cax>
<https://support.industry.siemens.com>

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval



[Declaration of Conformity](#)



[China RoHS](#)



General Product Approval

EMV

For use in hazardous locations



FM

[CCC-Ex](#)

Test Certificates

Environment

Industrial Communication

[Type Test Certificates/Test Report](#)



[PROFINET](#)

last modified:

1/23/2026