

SCALANCE X208PRO, managed IE switch, 8x 10/100 Mbit/s M12 ports, IP65/67, LED diagnostics, error signaling contact, Redundant power supply, PROFINET IO device, network management, can be operated in redundant ring, dust caps, including electronic manual on CD-ROM, C-plug optional.

product type designation	
product brand name	SCALANCE
product type designation	X208PRO
Technical Product Detail Page	https://i.siemens.com/1P6GK5208-0HA10-2AA6
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	8
number of 10/100 Mbit/s M12-ports (D-coded)	8
interfaces / other	
number of electrical connections	
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for signaling contact	5-pole M12 port (B-coded)
• for power supply	4-pole M12 connection (A-coded)
design of the removable storage	
• C-PLUG	Yes
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	
• supply voltage / 1 / rated value	DC
• power loss [W] / 1 / rated value	24 V
• supply voltage / 1 / voltage range	4.4 W
• consumed current / 1 / maximum	18 ... 32
• type of electrical connection / 1 / for power supply	0.185 A
• product component / 1 / fusing at power supply input	4-pole M12 connection (A-coded)
• fuse protection type / 1 / at input for supply voltage	Yes
	0,6 A / 60 V
ambient conditions	
ambient temperature	
• during operation	-40 ... +70 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP65/67
design, dimensions and weights	
design	compact
width	90 mm
height	125 mm
depth	124 mm
net weight	1 kg

fastening method	
• 35 mm DIN-rail mounting	Yes
• wall mounting	Yes
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	No
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <~0.3~s	100
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• port mirroring	Yes
• multiport mirroring	No
• with IRT / PROFINET IO switch	No
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
PROFINET conformity class	B
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	No
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
product functions / DHCP	
product function	
• DHCP client	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• ring redundancy	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	No
• passive listening	Yes
product functions / security	
protocol / is supported	
• SSH	Yes

product functions / time	
product function	
• SICLOCK support	Yes
protocol / is supported	
• NTP	No
• SNTP	Yes
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• cULus approval	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC interference emission	EN 61000-6-4 (Class A)
• for immunity to EMC	EN 61000-6-2
• for safety / from CSA and UL	UL 60950-1 E115352, CSA C22.2 No. 60950-1
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• ATEX	Yes
• UKEX	Yes
• IECEx	Yes
• ULhazloc approval	Yes
• CCC / for hazardous zone according to GB standard	Yes
• FM registration	Yes
standards, specifications, approvals / other	
certificate of suitability	
• railway application in accordance with EN 50155	No
• RoHS conformity	Yes
standards, specifications, approvals / marine classification	
Marine classification association	
• French marine classification society (BV)	Yes
• Det Norske Veritas (DNV)	Yes
• Lloyds Register of Shipping (LRS)	Yes
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	167.64 kg
• during manufacturing	29.12 kg
• during operation	138.29 kg
• after end of life	0.23 kg
product functions / general	
MTBF	83 a
warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to website: Industrial communication	https://www.siemens.com/simatic-net
• to web page: SiePortal	https://sieportal.siemens.com/
• to website: Image database	https://www.automation.siemens.com/bilddb
• to website: CAx-Download-Manager	https://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible

for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under [https://www.siemens.com/cert. \(V4.7\)](https://www.siemens.com/cert. (V4.7))

Approvals / Certificates

General Product Approval

[Declaration of Conformity](#)

[China RoHS](#)

General Product Approval

EMV

For use in hazardous locations

[Miscellaneous](#)

For use in hazardous locations

[FM](#)

Maritime application

[CCC-Ex](#)

Environment

Industrial Communication

[PROFINET](#)

last modified:

1/23/2026 