

SCALANCE XR324WG; managed IE switch; 19" rack; 24 x 10/100 Mbit/s electrical ports; LED diagnostics; reset button; console port; PROFINET device; IEC 62443-4-2 certified network management function; redundancy manager; power supply 24 V DC;



product type designation	
product brand name	SCALANCE
product type designation	XR324 WG
Technical Product Detail Page	https://i.siemens.com/1P6GK5324-0BA00-2AR3
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	24; RJ45
number of 10/100 Mbit/s RJ45 ports	24
interfaces / other	
number of electrical connections	
• for operator console	1
• for power supply	1
type of electrical connection	
• for power supply	2 x 2-pole terminal block
supply voltage, current consumption, power loss	
type of voltage supply / redundant power supply unit	No
type of voltage / 1 / of the supply voltage	
• supply voltage / 1 / rated value	DC
• power loss [W] / 1 / rated value	24 V
• supply voltage / 1 / voltage range	7.2 W
• consumed current / 1 / maximum	19.2 ... 28.8
• type of electrical connection / 1 / for power supply	0.3 A
• product component / 1 / fusing at power supply input	2 x 2-pole terminal block
• fuse protection type / 1 / at input for supply voltage	Yes
	F 5 A / 60 V
ambient conditions	
ambient temperature	
• during operation	0 ... 60 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP30
design, dimensions and weights	
design	19-inch rack
number of modular height units / relating to 19-inch cabinet	1
width	483 mm

height	44 mm
depth	127 mm
net weight	2.7 kg
fastening method	
• 19-inch installation	Yes
• 35 mm DIN-rail mounting	No
• wall mounting	No
• S7-300 rail mounting	No
• S7-1500 rail mounting	No
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.3~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• RMON	Yes
• port mirroring	Yes
• multiport mirroring	No
• CoS	Yes
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
PROFINET conformity class	B
network load class / according to PROFINET	II
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	Yes
• GMRP	No
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
number of VLANs / maximum	257

number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• ring redundancy	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	No
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
protocol / is supported	
• STP/RSTP	Yes
• STP	Yes
• RSTP	Yes
• MSTP	No
• RSTP big network support	Yes
• LACP	No
product functions / security	
product function	
• IEEE 802.1x (radius)	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
product functions / time	
product function	
• SICLOCK support	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes
• IEEE 1588 profile default	No
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UKCA marking	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC interference emission	EN 61000-6-4 (Class B)
• for immunity to EMC	EN 61000-6-2
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1, UL 61010-2-201
standards, specifications, approvals / hazardous environments	
certificate of suitability	

• ATEX	Yes
• UKEX	Yes
• IECEx	Yes
• ULhazloc approval	Yes
• CCC / for hazardous zone according to GB standard	Yes
• FM registration	Yes

standards, specifications, approvals / other

certificate of suitability	
• railway application in accordance with EN 50155	No
• RoHS conformity	Yes
resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes

standards, specifications, approvals / Environmental Product Declaration

Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	306.92 kg
• during manufacturing	109.07 kg
• during operation	197.3 kg
• after end of life	0.55 kg

product functions / general

MTBF	56 a
warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022

further information / internet links

internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to website: Industrial communication	https://www.siemens.com/simatic-net
• to web page: SiePortal	https://sieportal.siemens.com/
• to website: Image database	https://www.automation.siemens.com/bilddb
• to website: CAx-Download-Manager	https://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

security information

security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert . (V4.7)
----------------------	--

Approvals / Certificates

General Product Approval



[Declaration of Conformity](#)



[China RoHS](#)



General Product Approval

EMV

For use in hazardous locations

[Declaration of Con-formity](#)



[TUEV](#)



IECEx
IECEx



For use in hazardous locations

Test Certificates

Environment

Industrial Communication

[FM](#)

[CCC-Ex](#)

[Type Test Certific-
ates/Test Report](#)



[PROFINET](#)

last modified:

1/23/2026