


Data sheet

6XV1801-2A

product type designation

product description



Robust Energy Cable 4 x 0,75

Robust, flexible energy cable (4-wire), sold by the meter, unassembled

Robust Energy Cable, 4-core power line, stranded wires 4x 0.75 mm² delivery unit: max. 1000 m, minimum order quantity 20 m sold by the meter

Technical Product Detail Page

<https://i.siemens.com/1P6XV1801-2A>

suitability for use

Cable with FEP jacket (fluorinated plastic, perfluoroethylene propylene) for use in the food, beverage and tobacco industry (IP65/67/69 resistant, EHEDG approval). Cable is water-repellent, weather-proof, resistant to microbes, and extremely resistant to many cleaning agents and disinfectants (such as hypochlorite, chlorine dioxide, peroxyacetic acid, and quaternary ammonium cations).

cable designation

LI9YY6Y 4X1X0.75 GY

electrical data

insulation resistance coefficient	20 GΩ·m
operating voltage / RMS value	300 V
conductor cross section / of the power line	0.75 mm ²
continuous current / of the power lines	8 A

mechanical data

number of electrical cores	4
outer diameter	
• of inner conductor	1.15 mm
• of the wire insulation	1.7 mm
• of cable sheath	5.7 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.2 mm
conductor class	5
material	
• of the conductor	CU, blank
• of the wire insulation	PP
• of cable sheath	PVC/FEP; FEP transparent
product component / PE connection	No
marking / of cores	Color
color	
• of the power line insulation	brown / blue, white / black
• of cable sheath	gray
bending radius	
• with single bend / minimum permissible	23 mm
• with multiple bends / minimum permissible	46 mm
• with continuous bending	100 mm
number of bending cycles	500000; acceleration 4 m/s ²
number of torsion cycles / with torsion by ± 180° on 1 m cable length	1000000
tensile load / maximum	150 N
weight per length	53 kg/km

ambient conditions	
ambient temperature	<ul style="list-style-type: none"> • during operation • during storage • during transport • during installation • note
	-40 ... +90 °C
	electrical characteristics measured at 20 °C, tests according to DIN 47250 Part 4 or DIN VDE 0472
fire behavior	Flame-resistant acc. to IEC 60332-1-2
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	<ul style="list-style-type: none"> • to mineral oil • to grease • to water
	oil resistant according to DIN EN 60811-404 (7x24h/90°C)
	resistant
	resistant
radiological resistance / to UV radiation	resistant according to UL 2556 Sec. 4.2.8.5
product features, product functions, product components / general	
product feature	
• halogen-free	No
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us 3047254, CMG FT4 75°C, (ETL)us PLTC-ER, SUN RES, OIL RES I or E130266 AWM 22161 AWM I A/B 80°C 300V FT2
UL/ETL style / 600 V Rating	No
certificate of suitability	
• EAC approval	Yes
• RoHS conformity	Yes
• for hygienic design	EHEDG, Installation and layout of the cables must fulfil the requirements of EHEDG published in the Guidelines Doc. 13 Hygienic Design of open equipment for processing food and Doc. 44 Hygienic Design Principles for food factories to be accessible for cleaning. Also connections must be easily cleanable by using EHEDG certified cable glands or connectors.
further information / internet links	
internet link	<ul style="list-style-type: none"> • to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to web page: SiePortal • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support
	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/simatic-net https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com
security information	
security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)</p>
Approvals / Certificates	
General Product Approval	

[Manufacturer Declaration](#)



[China RoHS](#)

[Fire safety / Physical security](#)

Food, Pharmaceutical, Medical

Environment

Industrial Communication

[EHEDG](#)

[Environmental Confirmations](#)

[PROFINET](#)

last modified:

10/29/2025