


## Data sheet

6XV1860-2R

product type designation

product description



**PROFIBUS Hybrid Standard Cable GP**

Hybrid cable (data and energy wires), product sold by meter, unassembled

PROFIBUS hybrid standard cable GP, Cable with 2xCU (1.5 mm<sup>2</sup>) and 2xCU (0.64 mm) shielded, ET 200, sold by the meter, delivery unit max. 1000 m minimum order quantity: 20 m.

Technical Product Detail Page

<https://i.siemens.com/1P6XV1860-2R>

suitability for use

Trailing-type, hybrid cable used for supplying data and power to ET 200pro

cable designation

02Y(ST)C 1x2x0.65/2.56-150LI LIY-Z Y 2x1x1.5 VI

**electrical data**

attenuation factor per length

- at 9.6 kHz / maximum 0.004 dB/m
- at 38.4 kHz / maximum 0.004 dB/m
- at 4 MHz / maximum 0.025 dB/m
- at 16 MHz / maximum 0.049 dB/m

impedance

- rated value 150 Ω
- at 9.6 kHz 270 Ω
- at 38.4 kHz 185 Ω
- at 3 MHz ... 20 MHz 150 Ω

relative symmetrical tolerance

- of the characteristic impedance at 9.6 kHz 10 %
- of the characteristic impedance at 38.4 kHz 10 %
- of the characteristic impedance at 3 MHz ... 20 MHz 10 %

loop resistance per length / maximum

138 Ω/km

shield resistance per length / maximum

10 Ω/km

insulation resistance coefficient

20 GΩ·m

operating voltage / maximum

80 V

capacity per length / at 1 kHz

30 pF/m

operating voltage / RMS value

300 V

conductor cross section / of the power line

1.5 mm<sup>2</sup>

continuous current / of the power lines

7.5 A

**mechanical data**

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

number of electrical cores

4

type of electrical connection / FastConnect

No

outer diameter

- of inner conductor 0.67 mm
- of the wire insulation 2.56 mm
- of cable sheath 11 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.5 mm

material

• of the wire insulation	polyethylene (PE)
• of cable sheath	PVC
color	
• of the insulation of data wires	red / green
• of the power line insulation	Black
• of cable sheath	Violet
bending radius	
• with single bend / minimum permissible	44 mm
• with multiple bends / minimum permissible	125 mm
number of bending cycles	1000000; For use in cable carriers, for 1 million bending cycles with a bending radius of 125 mm and an acceleration of 2.5 m/s <sup>2</sup>
tensile load / maximum	450 N
weight per length	140 kg/km
<b>ambient conditions</b>	
ambient temperature	
• during operation	-40 ... +75 °C
• during storage	-40 ... +75 °C
• during transport	-40 ... +75 °C
• during installation	-40 ... +75 °C
• note	Electrical properties measured at 20 Cel, verification according to DIN 47250 part 4 respectively DIN VDE 0490
fire behavior	flame-retardant according to IEC 60332-1-2
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil	Conditional resistance
• to grease	Conditional resistance
radiological resistance / to UV radiation	not resistant
<b>product features, product functions, product components / general</b>	
product feature	
• halogen-free	No
• silicon-free	Yes
<b>standards, specifications, approvals</b>	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us 3047254 CMG FT4 75°C
UL/ETL style / 600 V Rating	Yes
certificate of suitability	
• EAC approval	Yes
• RoHS conformity	Yes
<b>further information / internet links</b>	
internet link	
• to website: Selection guide for cables and connectors	<a href="https://support.industry.siemens.com/cs/ww/en/view/109766358">https://support.industry.siemens.com/cs/ww/en/view/109766358</a>
• to web page: selection aid TIA Selection Tool	<a href="https://www.siemens.com/tstcloud">https://www.siemens.com/tstcloud</a>
• to website: Industrial communication	<a href="https://www.siemens.com/simatic-net">https://www.siemens.com/simatic-net</a>
• to web page: SiePortal	<a href="https://sieportal.siemens.com/">https://sieportal.siemens.com/</a>
• to website: Image database	<a href="https://www.automation.siemens.com/bilddb">https://www.automation.siemens.com/bilddb</a>
• to website: CAx-Download-Manager	<a href="https://www.siemens.com/cax">https://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>security information</b>	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit <a href="http://www.siemens.com/cybersecurity-industry">www.siemens.com/cybersecurity-industry</a> . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase

## Approvals / Certificates

### General Product Approval

[Manufacturer Declaration](#)



[Declaration of Conformity](#)



[China RoHS](#)

General Product Approval

other

Environment

[Fire safety / Physical security](#)

[Miscellaneous](#)

[Environmental Confirmations](#)

last modified:

1/12/2026