

product type designation

product description

IE TP XP Cord RJ45/RJ45, 4x2

Crossover patch cable, preferred length, preassembled with two RJ45 connectors (10/100/1000/10000MB)

Industrial Ethernet TP XP Cord RJ45/RJ45, CAT 6A, crossed TP cable 4x2, pre-assembled with 2 RJ45 plugs, length 1 m.



Technical Product Detail Page

<https://i.siemens.com/1P6XV1870-3RH10>

suitability for use

Easy connection of terminal devices to the IE FC cabling system

cable designation

S/FTP, LI 02YSCH 4x2x0,15 PIMF RD FRNC

wire length

1 m

electrical data

number of electrical connections

2

attenuation factor per length

- at 10 MHz / maximum
- at 100 MHz / maximum
- at 300 MHz / maximum
- at 600 MHz / maximum

0.086 dB/m
0.28 dB/m
0.501 dB/m
0.735 dB/m

impedance

- at 1 MHz ... 100 MHz
- at 10 MHz ... 600 MHz

100 Ω
100 Ω

relative symmetrical tolerance

- of the characteristic impedance at 1 MHz ... 100 MHz
- of the characteristic impedance at 10 MHz ... 600 MHz

15 %
10 %

transfer impedance per length / at 10 MHz

10 mΩ/m

loop resistance per length / maximum

290 mΩ/m

operating voltage

- RMS value

80 V

NVP value in percent

80 %

mechanical data

number of electrical cores

8

design of the shield

S/FTP, overlapped aluminum-clad foil, sheathed in a protective braided shield of tinned copper wires

core diameter

- of AWG26 insulated conductor

0.5 mm

outer diameter

- of inner conductor
- of the wire insulation
- of cable sheath

0.5 mm
1 mm
6.2 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.3 mm

material

- of the wire insulation
- of cable sheath

polyethylene (PE)
FRNC

color

• of the insulation of data wires • of cable sheath	white/blue, white/orange, white/green, white/brown green
bending radius	
• with single bend / minimum permissible • with multiple bends / minimum permissible	31 mm 43.5 mm
weight per length	50 kg/km
plug	
connector type	RJ45
type of plug interlock	latched
design of plug-in connection	RJ45-180
ambient conditions	
ambient temperature	
• during operation • during storage • during transport • during installation • note	-25 ... +80 °C -25 ... +80 °C -25 ... +80 °C -25 ... +80 °C In fixed installation -40 °C to 80 °C
fire behavior	flame resistant according to IEC 60332-1-2, smoke density according to IEC 61034
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil • to grease	oil resistant according to IEC 60811-2-1 (4 h / 70°C) Conditional resistance
radiological resistance / to UV radiation	not resistant
protection class IP	IP20
product features, product functions, product components / general	
product feature	
• halogen-free • PoE capability • PoE+ capability • PoE++ capability • silicon-free	Yes Yes Yes Yes Yes
test voltage	
• at AC / core-to-core • at AC / core shield	500 V 1500 V
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	Yes; E130266 AWM STYLE 21279
certificate of suitability	ISO/IEC 11801-1, IEC 61035
• EAC approval • UL approval • RoHS conformity	Yes Yes Yes
standard for structured cabling	Cat6A
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • Det Norske Veritas (DNV) • Germanische Lloyd (GL) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS)	No No No No No No No
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to web page: SiePortal • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com

security information

security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert . (V4.7)
----------------------	--

Approvals / Certificates

General Product Approval

Manufacturer Declaration			Declaration of Conformity		China RoHS
--	---	---	---	---	----------------------------

General Product Approval	Test Certificates	Industrial Communication
--------------------------	-------------------	--------------------------

Fire safety / Physical security	Special Test Certificate	PROFINET
---	--	--------------------------

last modified:	12/20/2025 
----------------	--