

Data sheet

6XV1870-8AH15

product type designation

product description

IE Connecting Cable M12-180/M12-180

Flexible plug-in cable (4-wire), preferred length, prefabricated with two 4-pole M12 connectors (D-coded, 180° cable outlet)

Industrial Ethernet connecting Cable M12-180/M12-180 pre-assembled IE FC Trailing Cable GP, with 2 M12 connectors (D-coded) length 1.5 m.



Technical Product Detail Page

<https://i.siemens.com/1P6XV1870-8AH15>

suitability for use

For connecting Industrial Ethernet stations (e.g. SIMATIC ET200 and SCALANCE XP-200) in IP 65/67 degree of protection

cable designation

SF/UTP, 2YY (ST) CY 2x2x0,75/1,5-100 LI GN

wire length

1.5 m

electrical data

number of electrical connections

2

attenuation factor per length

0.063 dB/m

• at 10 MHz / maximum

0.213 dB/m

• at 100 MHz / maximum

impedance

100 Ω

• at 1 MHz ... 100 MHz

relative symmetrical tolerance

5 %

near-end crosstalk per length

0.5 dB/m

• at 1 MHz ... 100 MHz

transfer impedance per length / at 10 MHz

20 mΩ/m

loop resistance per length / maximum

120 mΩ/m

operating voltage

80 V

• RMS value

NVP value in percent

66 %

mechanical data

number of electrical cores

4

design of the shield

SF/UTP, overlapped aluminum-clad foil, sheathed in a protective braided shield of tinned copper wires

core diameter

0.75 mm

• of AWG22 insulated conductor

outer diameter

0.75 mm

• of inner conductor

1.5 mm

• of the wire insulation

3.9 mm

• of the inner sheath of the cable

6.5 mm

• of cable sheath

symmetrical tolerance of the outer diameter / of cable sheath

0.2 mm

material

polyethylene (PE)

• of the wire insulation

PVC

• of the inner sheath of the cable

PVC

• of cable sheath

color	white/yellow/blue/orange green
• of the insulation of data wires • of cable sheath	
bending radius	32.5 mm 49 mm 100 mm
• with single bend / minimum permissible • with multiple bends / minimum permissible • with continuous bending	
number of bending cycles	3000000; Drag chain suitable for 3 million bending cycles at a bending radius of 100 mm, a speed of 4 m/s and an acceleration of 4 m/s ²
tensile load / maximum	150 N
weight per length	68 kg/km
plug	
type of plug interlock	screwed
design of plug-in connection	M12-180
tightening torque / for M12 round connector / maximum	0.6 N·m
connector coding	M12 D-coded
• of the M12 circular connector	
ambient conditions	
ambient temperature	-25 ... +75 °C -25 ... +75 °C -25 ... +75 °C -10 ... +60 °C
• during operation • during storage • during transport • during installation	
fire behavior	flame resistant according to UL 1685 (CSA FT 4)
chemical resistance	conditional resistance Conditional resistance
• to mineral oil • to grease	
radiological resistance / to UV radiation	resistant
protection class IP	IP65, IP67
product features, product functions, product components / general	
product feature	
• halogen-free	No
• PoE capability	Yes
• PoE+ capability	Yes
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us, CMG FT4 / (ETL)us PLTC / Sun Res / OIL RES
UL/ETL style / 600 V Rating	Yes; cRUus AWM 21694 AWM I A/B 60°C 600V FT2
certificate of suitability	UL 2238
• EAC approval • CE marking • RoHS conformity	Yes Yes Yes
standard for structured cabling	Cat5e
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
• Polski Rejestr Statków (PRS)	No
further information / internet links	
internet link	<ul style="list-style-type: none"> to website: Selection guide for cables and connectors to web page: selection aid TIA Selection Tool to web page: SiePortal to website: Image database to website: CAx-Download-Manager to website: Industry Online Support https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under [https://www.siemens.com/cert. \(V4.7\)](https://www.siemens.com/cert. (V4.7))

Approvals / Certificates

General Product Approval



[Declaration of Conformity](#)

[Manufacturer Declaration](#)

[China RoHS](#)

General Product Approval

Industrial Communication



[PROFINET](#)

last modified:

12/20/2025