



Figure similar


Integrated signal lamp, single flash light, w. built-in electronic flash, blue, 24 V DC, diameter 70 mm


| General technical data                               |                          |
|------------------------------------------------------|--------------------------|
| product designation                                  | Flashlight element       |
| consumed current maximum                             | 125 mA                   |
| type of voltage of the operating voltage             | DC                       |
| operating voltage                                    | 24 V                     |
| • 1 at DC rated value                                |                          |
| relative positive tolerance of the operating voltage | 10 %                     |
| relative negative tolerance of the operating voltage | -10 %                    |
| reference code according to IEC 81346-2              | P                        |
| fastening method                                     | Bayonet / flush mounting |
| material                                             | PC; PC/ABS; PA           |
| color                                                | blue                     |
| Mechanical data                                      |                          |
| product component light source                       | Yes                      |
| type of electrical connection                        | screw terminal           |
| outer diameter of the signal column element          | 75 mm                    |
| Lamp                                                 |                          |
| design of the optical signal                         | flash light              |
| type of light source                                 | Xenon gas discharge lamp |
| light intensity                                      | 20 713 cd                |
| flash frequency                                      | 1 Hz                     |
| number of flashes of light element                   | 4 000 000                |
| Ambient conditions                                   |                          |
| ambient temperature during operation                 | -20 ... +50 °C           |
| protection class IP                                  | IP65                     |
| depth                                                | 31 mm                    |
| height                                               | 66 mm                    |
| width                                                | 75 mm                    |
| Certificates/ approvals                              |                          |
| General Product Approval                             | other                    |

[Confirmation](#)



|       |             |
|-------|-------------|
| other | Environment |
|-------|-------------|

**Further information****Information on the packaging**<https://support.industry.siemens.com/cs/ww/en/view/109813875>**Information for data generation and storage**<https://support.industry.siemens.com/cs/ww/en/view/109995012>**Information- and Downloadcenter (Catalogs, Brochures,...)**<https://www.siemens.com/ic10>**Industry Mall (Online ordering system)**<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD5320-0CF>**Cax online generator**<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD5320-0CF>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<https://support.industry.siemens.com/cs/ww/en/ps/8WD5320-0CF>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=8WD5320-0CF&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD5320-0CF&lang=en)



last modified:

4/1/2025 