



basic device SIMOCODE pro V PN GP , Ethernet/PROFINET IO, PN system redundancy, OPC UA server, web server, transfer rate 100 Mbps, 1 x bus connection via RJ45, 4 I/3 O freely configurable, Us: 110..240 V AC/DC, input for thermistor connection monostable relay outputs, expandable by 1 expansion module(DM, TM, EM)

product brand name	SIMOCODE	
product designation	Motor management system	
design of the product	basic unit 3	
General technical data		
product function	<ul style="list-style-type: none"> • current measurement • voltage measurement • active power measurement • energy measurement • frequency measurement • bus communication • data acquisition function • diagnostics function • password protection • test function • maintenance function 	No No No No No Yes Yes Yes Yes Yes Yes Yes
product component	<ul style="list-style-type: none"> • input for thermistor connection • digital input • input for analog temperature sensors • input for ground fault detection • relay output 	Yes Yes No No Yes
product extension	<ul style="list-style-type: none"> • temperature monitoring module • current measuring module • current/voltage measuring module • fail-safe digital I/O module • ground-fault monitoring module • decoupling module • analog I/O module • digital I/O module with monostable outputs • digital I/O module with bistable outputs • control unit with display • control unit 	Yes Yes No No Yes No No Yes No No Yes
apparent power consumption	8.3 VA	
consumed active power	4.5 W	
insulation voltage with degree of pollution 3 at AC rated value	300 V	
surge voltage resistance rated value	4 000 V	
shock resistance		

• according to IEC 60068-2-27	15g / 11 ms
• vibration resistance	1-6 Hz / 15 mm; 6-500 Hz / 2 g
switching capacity current of the NO contacts of the relay outputs at AC-15	
• at 24 V	6 A
• at 120 V	6 A
• at 230 V	3 A
switching capacity current of the NO contacts of the relay outputs at DC-13	
• at 24 V	2 A
• at 60 V	0.55 A
• at 125 V	0.25 A
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles) typical	100 000
buffering time in the event of power failure	0.02 s
reference code according to IEC 81346-2	F
continuous current of the NO contacts of the relay outputs	
• at 50 °C	6 A
• at 60 °C	5 A
type of input characteristic	Type 1 in accordance with EN 61131-2
Substance Prohibitance (Date)	08/31/2018
SVHC substance name	Lead - 7439-92-1 Lead monoxide (lead oxide) - 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one - 71868-10-5 4,4'-isopropylidenediphenol (Bisphenol A, BPA) - 80-05-7 2-benzyl-2-dimethylamino-4'-morpholinobutyrophenone - 119313-12-1
Net Weight	0.336 kg
Electromagnetic compatibility	
EMC emitted interference according to IEC 60947-1	class A
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
conducted interference	
• due to burst according to IEC 61000-4-4	2 kV (power ports) / 1 kV (signal ports)
• due to conductor-earth surge according to IEC 61000-4-5	2 kV
• due to conductor-conductor surge according to IEC 61000-4-5	1 kV
• due to high-frequency radiation according to IEC 61000-4-6	10 V
field-based interference according to IEC 61000-4-3	10 V/m
electrostatic discharge according to IEC 61000-4-2	6 kV contact discharge / 8 kV air discharge
conducted HF interference emissions according to CISPR11	corresponds to degree of severity A
field-bound HF interference emission according to CISPR11	corresponds to degree of severity A
Inputs/ Outputs	
product function	
• parameterizable inputs	Yes
• parameterizable outputs	Yes
number of inputs	4
• for thermistor connection	1
number of digital inputs with a common reference potential	4
digital input version	
• type 1 acc. to IEC 61131	Yes
input voltage at digital input at DC	
• rated value	24 V
number of outputs	3
number of semiconductor outputs	0
number of outputs as contact-affected switching element	3
switching behavior	monostable
number of relay outputs	3
type of relay outputs	Monostable
wire length for digital signals maximum	300 m

wire length for thermistor connection	<ul style="list-style-type: none"> with conductor cross-section = 0.5 mm² maximum with conductor cross-section = 1.5 mm² maximum with conductor cross-section = 2.5 mm² maximum 	50 m 150 m 250 m
Protective and monitoring functions		
product function		
<ul style="list-style-type: none"> asymmetry detection blocking current evaluation power factor monitoring ground fault detection ground-fault monitoring phase failure detection phase sequence recognition voltage detection monitoring of number of start operations overvoltage detection overcurrent detection 1 phase undervoltage detection undercurrent detection 1 phase active power monitoring 	Yes Yes No Yes No Yes No No Yes No Yes No Yes No	
product function		
<ul style="list-style-type: none"> current detection overload protection evaluation of thermistor motor protection 	Yes Yes Yes	
total cold resistance number of sensors in series maximum	1.5 kΩ	
response value of thermoresistor	3 400 ... 3 800 Ω	
<ul style="list-style-type: none"> of the short-circuit control 	9 Ω	
release value of thermoresistor	1 500 ... 1 650 Ω	
Motor control functions		
product function		
<ul style="list-style-type: none"> parameterizable overload relay circuit breaker control direct start reverse starting star-delta circuit star-delta reversing circuit Dahlander circuit Dahlander reversing circuit pole-changing switch circuit pole-changing switch reversing circuit slide control valve control 	Yes Yes Yes Yes Yes No No No No No No No	
Communication/ Protocol		
protocol is supported		
<ul style="list-style-type: none"> PROFIBUS DP protocol PROFINET IO protocol PROFIsafe protocol Modbus RTU EtherNet/IP OPC UA Server LLDP Address Resolution Protocol (ARP) SNMP HTTPS NTP Media Redundancy Protocol (MRP) 	No Yes No No No Yes Yes Yes Yes Yes Yes Yes No	
product function		
<ul style="list-style-type: none"> web server shared device 	Yes No	

• at the Ethernet interface Autocrossover	Yes
• at the Ethernet interface Autonegotiation	Yes
• at the Ethernet interface Autosensing	Yes
• Media Redundancy Protocol for Planned Duplication (MRPD)	No
• is supported Device Level Ring (DLR)	No
• is supported PROFINET system redundancy (S2)	Yes
• supports PROFIenergy measured values	Yes
• supports PROFIenergy shutdown	Yes
transfer rate	100 Mbit/s
transfer rate maximum	100 Mbit/s
PROFINET conformity class	C
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
• I&M2 - installation date	Yes
• I&M3 - comment	Yes
type of electrical connection of the communication interface	1 x RJ45
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting
height	111 mm
width	45 mm
depth	124 mm
required spacing	
• top	40 mm
• bottom	40 mm
• left	0 mm
• right	0 mm
Connections/ Terminals	
product component removable terminal for auxiliary and control circuit	Yes
type of electrical connection	
• for auxiliary and control circuit	screw-type terminals
type of connectable conductor cross-sections	
• solid	1x (0.5 ... 4.0mm ²), 2x (0.5 ... 2.5 mm ²)
• finely stranded with core end processing	1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1.5 mm ²)
• for AWG cables solid	1x (20 ... 12), 2x (20 ... 14)
• for AWG cables stranded	1x (20 ... 14), 2x (20 ... 16)
tightening torque with screw-type terminals	0.8 ... 1.2 N·m
tightening torque [lbf-in] with screw-type terminals	7 ... 10.3 lbf-in
Ambient conditions	
installation altitude at height above sea level maximum	2 000 m
• note	Restrictions apply to higher installation altitudes, see: https://support.industry.siemens.com/cs/document/109995153
ambient temperature	
• during operation	-25 ... +60 °C
• during storage	-40 ... +80 °C
• during transport	-40 ... +80 °C
environmental category	
• during operation according to IEC 60721	3K6 (no formation of ice, no condensation, relative humidity 10 ... 95%), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
• during storage according to IEC 60721	1K6 (no condensation, relative humidity 10 ... 95%), 1C2 (no salt mist), 1S2 (sand must not get into the devices), 1M4
• during transport according to IEC 60721	2K2, 2C1, 2S1, 2M2
relative humidity	
• during operation	5 ... 95 %
contact rating of auxiliary contacts according to UL	B300 / R300
Short-circuit protection	
design of short-circuit protection per output	Fuse links: gG 6 A, quick-response 10 A (IEC 60947-5-1), miniature circuit-

		breaker C char.: 1.6 A (IEC 60947-5-1) or 6 A (I_K < 500 A)			
Electrical Safety	touch protection against electrical shock	finger-safe			
ATEX					
certificate of suitability					
<ul style="list-style-type: none"> • IECEx • according to ATEX directive 2014/34/EU • according to UKCA 		Yes; IECEx BVS 20.0020 BVS 06 ATEX F001 ITS21UKEX0464			
explosion device group and category according to ATEX directive 2014/34/EU		II (2) G, II (2) D, I (M2)			
Galvanic isolation					
(electrically) protective separation according to IEC 60947-1		All circuits with protective separation (double creepage paths and clearances), the information in the "Protective Separation" test report, No. A0258, must be observed (link see further information)			
design of the electrical isolation		Protective separation in accordance with IEC 60947-1 for all circuits Test report No. A0258 must be observed (https://support.industry.siemens.com/cs/document/109748152)			
Control circuit/ Control					
product function soft starter control		Yes			
type of voltage of the control supply voltage		AC/DC			
control supply voltage at AC					
<ul style="list-style-type: none"> • at 50 Hz rated value • at 60 Hz rated value 		110 ... 240 V 110 ... 240 V			
control supply voltage frequency					
<ul style="list-style-type: none"> • 1 rated value • 2 rated value 		50 Hz 60 Hz			
relative symmetrical tolerance of the control supply voltage frequency		5 %			
control supply voltage at DC rated value		110 ... 240 V			
operating range factor control supply voltage rated value at DC					
<ul style="list-style-type: none"> • initial value • full-scale value 		0.85 1.1			
operating range factor control supply voltage rated value at AC at 50 Hz					
<ul style="list-style-type: none"> • initial value • full-scale value 		0.85 1.1			
operating range factor control supply voltage rated value at AC at 60 Hz					
<ul style="list-style-type: none"> • initial value • full-scale value 		0.85 1.1			
inrush current peak					
<ul style="list-style-type: none"> • at 240 V 		15 A			
duration of inrush current peak					
<ul style="list-style-type: none"> • at 240 V 		1 ms			
Approvals Certificates					
Environment	General Product Approval				
	Environmental Confirmations	   			
General Product Approval	EMV	For use in hazardous locations			
					

For use in hazardous locations	Test Certificates	Maritime application
--------------------------------	-------------------	----------------------



IECEx

[Miscellaneous](#)

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

[Special Test Certificate](#)



ABS

Maritime application	other	Industrial Communication
----------------------	-------	--------------------------



DNV



LRS



[Confirmation](#)

[PROFINET](#)

Industrial Communication



Profibus

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UF7011-1AU00-2>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UF7011-1AU00-2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3UF7011-1AU00-2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UF7011-1AU00-2&lang=en



