

Current measuring module, Set current 20...200 A overall width 120 mm, straight-through transformer



product brand name	SIMOCODE
product designation	Current measuring module
General technical data	
size of the circuit-breaker	S6
product function	
• current measurement	Yes
• voltage measurement	No
• active power measurement	No
• energy measurement	No
• frequency measurement	No
product component	
• input for thermistor connection	No
consumed active power	0.2 W
insulation voltage	
• with degree of pollution 3 at AC rated value	690 V
• for wires of main circuit according to IEC 60947-1 rated value	8 kV
surge voltage resistance rated value	8 000 V
shock resistance according to IEC 60068-2-27	15g / 11 ms
vibration resistance	1-6 Hz / 15 mm; 6-500 Hz / 2 g
reference code according to IEC 81346-2	F
Substance Prohibitance (Date)	07/01/2006
SVHC substance name	Lead monoxide (lead oxide) - 1317-36-8
Net Weight	634 g
Electromagnetic compatibility	
EMC emitted interference according to IEC 60947-1	class A
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
conducted interference	
• due to burst according to IEC 61000-4-4	2 kV
• due to conductor-earth surge according to IEC 61000-4-5	2 kV
• due to conductor-conductor surge according to IEC 61000-4-5	1 kV
field-based interference according to IEC 61000-4-3	10 V/m
Inputs/ Outputs	
number of outputs as contact-affected switching element	0
Protective and monitoring functions	
product function	
• power factor monitoring	No
• ground-fault monitoring	No

• voltage detection	No
trip class	CLASS 5E
product function	
• current detection	Yes
• overload protection	Yes
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting
height	95 mm
width	120 mm
depth	145 mm
required spacing	
• top	30 mm
• bottom	30 mm
• left	0 mm
• right	0 mm
diameter of inlet opening	25 mm
diameter of inlet opening for current measurement	25 mm
Connections/ Terminals	
type of electrical connection	
• for main current circuit	straight-through transformers
Ambient conditions	
installation altitude at height above sea level	
• 1 maximum	2 000 m
• 2 maximum	3 000 m; max. +50 °C (no protective separation)
• 3 maximum	4 000 m; max. +40 °C (no protective separation)
ambient temperature	
• during operation	-25 ... +60 °C
• during storage	-40 ... +80 °C
• during transport	-40 ... +80 °C
environmental category	
• during operation according to IEC 60721	3K6 (no formation of ice, no condensation, relative humidity 10 ... 95%), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
• during storage according to IEC 60721	1K6 (no condensation, relative humidity 10 ... 95%), 1C2 (no salt mist), 1S2 (sand must not get into the devices), 1M4
• during transport according to IEC 60721	2K2, 2C1, 2S1, 2M2
relative humidity during operation	5 ... 95 %
Short-circuit protection	
product function short circuit protection	No
IEC 61508	
Safety Integrity Level (SIL) according to IEC 61508	1
ATEX	
certificate of suitability	
• according to ATEX directive 2014/34/EU	BVS 06 ATEX F001
• according to UKCA	ITS21UKEX0464
explosion device group and category according to ATEX directive 2014/34/EU	II (2) G, II (2) D, I (M2)
Galvanic isolation	
(electrically) protective separation according to IEC 60947-1	All circuits with protective separation (double creepage paths and clearances), the information in the "Protective Separation" test report, No. A0258, must be observed (link see further information)
Main circuit	
number of poles for main current circuit	3
adjustable current response value current of the current-dependent overload release	20 ... 200 A
operating voltage	
• at AC	
— at 50 Hz rated value	110 ... 690 V
— at 60 Hz rated value	110 ... 690 V
operating frequency rated value	50 ... 60 Hz

Control circuit/ Control	
type of voltage	AC
Approvals Certificates	
Environment	General Product Approval



[Environmental Con-
firmations](#)



EG-Konf.



UL

General Product Ap- proval	EMV	For use in hazardous locations
-------------------------------	-----	--------------------------------



RCM



ATEX



IECEx



ATEX

Test Certificates	Maritime application
-------------------	----------------------

[Type Test Certi-
ficates/Test Report](#)

[Special Test Certi-
ficate](#)



ABS



DNV



LRS



RMRS

other	Industrial Communication
-------	--------------------------



[Confirmation](#)



Profibus

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UF7103-1AA00-0>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UF7103-1AA00-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3UF7103-1AA00-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UF7103-1AA00-0&lang=en



