



Digital module, 4 inputs and 2 relay outputs, input voltage 110-240 V AC/DC relay outputs monostable, max. 2 digital modules, for SIMOCODE pro V basic unit

product brand name	SIMOCODE
product designation	digital modules
product type designation	DM mono
<b>General technical data</b>	
product component	
• input for thermistor connection	No
• digital input	Yes
• input for analog temperature sensors	No
• input for ground fault detection	No
• relay output	Yes
consumed active power	0.7 W
insulation voltage with degree of pollution 3 at AC rated value	300 V
surge voltage resistance rated value	4 000 V
shock resistance according to IEC 60068-2-27	15g / 11 ms
vibration resistance according to IEC 60068-2-6	1 ... 6 Hz: 15 mm, 6 ... 500 Hz: 2g
switching capacity current of the NO contacts of the relay outputs at AC-15	
• at 24 V	6 A
• at 120 V	6 A
• at 230 V	3 A
switching capacity current of the NO contacts of the relay outputs at DC-13	
• at 24 V	2 A
• at 60 V	0.5 A
• at 125 V	0.25 A
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles) typical	100 000
reference code according to IEC 81346-2	K
reference code according to IEC 81346-2:2019	K
continuous current of the NO contacts of the relay outputs	
• at 50 °C	6 A
• at 60 °C	5 A
Substance Prohibitance (Date)	05/01/2012
SVHC substance name	Lead - 7439-92-1 Lead monoxide (lead oxide) - 1317-36-8
Net Weight	147 g
<b>Electromagnetic compatibility</b>	
EMC emitted interference according to IEC 60947-1	class A
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
conducted interference	

● due to burst according to IEC 61000-4-4	1 kV
● due to conductor-earth surge according to IEC 61000-4-5	2 kV
● due to conductor-conductor surge according to IEC 61000-4-5	1 kV
● due to high-frequency radiation according to IEC 61000-4-6	10 V
<b>field-based interference according to IEC 61000-4-3</b>	10 V/m
<b>electrostatic discharge according to IEC 61000-4-2</b>	6 kV contact discharge / 8 kV air discharge
<b>conducted HF interference emissions according to CISPR11</b>	corresponds to degree of severity A
<b>field-bound HF interference emission according to CISPR11</b>	corresponds to degree of severity A
<b>Inputs/ Outputs</b>	
<b>product function</b>	
● parameterizable inputs	Yes
● parameterizable outputs	Yes
<b>number of inputs</b>	4
<b>number of digital inputs</b>	4
● with a common reference potential	4
<b>digital input version</b>	
● type 1 acc. to IEC 61131	No
● type 2 acc. to IEC 61131	No
<b>number of analog inputs</b>	0
input voltage at digital input at DC rated value	110 V
<b>number of outputs</b>	2
<b>number of semiconductor outputs</b>	0
<b>number of outputs as contact-affected switching element</b>	2
<b>number of analog outputs</b>	0
<b>switching behavior</b>	monostable
<b>property of contacts of the relay outputs</b>	Floating NO contacts (NC reaction parameterizable via internal signal conditioning), connected to common ground, can be freely assigned to the control functions (e.g. line, star (wye), delta contactor or signaling of the operating state)
<b>wire length for digital signals maximum</b>	200 m
<b>Installation/ mounting/ dimensions</b>	
<b>mounting position</b>	any
<b>fastening method</b>	screw and snap-on mounting
<b>height</b>	92 mm
<b>width</b>	22.5 mm
<b>depth</b>	124 mm
<b>required spacing</b>	
● top	40 mm
● bottom	40 mm
● left	0 mm
● right	0 mm
<b>Connections/ Terminals</b>	
<b>product component removable terminal for auxiliary and control circuit</b>	Yes
<b>type of electrical connection for auxiliary and control circuit</b>	screw-type terminals
<b>type of connectable conductor cross-sections</b>	
● solid	1x (0.5 ... 4.0mm <sup>2</sup> ), 2x (0.5 ... 2.5 mm <sup>2</sup> )
● finely stranded with core end processing	1x (0.5 ... 2.5 mm <sup>2</sup> ), 2x (0.5 ... 1.5 mm <sup>2</sup> )
● for AWG cables solid	1x (20 ... 14), 2x (20 ... 16)
● for AWG cables stranded	1x (20 ... 12), 2x (20 ... 14)
<b>tightening torque with screw-type terminals</b>	0.8 ... 1.2 N·m
<b>tightening torque [lbf-in] with screw-type terminals</b>	7 ... 10.3 lbf-in
<b>Ambient conditions</b>	
<b>installation altitude at height above sea level</b>	
● 1 maximum	2 000 m
● 2 maximum	3 000 m; max. +50 °C (no protective separation)
● 3 maximum	4 000 m; max. +40 °C (no protective separation)
<b>ambient temperature</b>	

• during operation	-25 ... +60 °C	
• during storage	-40 ... +80 °C	
• during transport	-40 ... +80 °C	
<b>environmental category</b>		
• during operation according to IEC 60721	3K6 (no formation of ice, no condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6	
• during storage according to IEC 60721	3K6 (no formation of ice, no condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6	
• during transport according to IEC 60721	3K6 (no formation of ice, no condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6	
relative humidity during operation	5 ... 95 %	
<b>contact rating of auxiliary contacts according to UL</b>	B300 / R300	
<b>Short-circuit protection</b>		
design of short-circuit protection per output	Fuse links: gG 6 A, quick-response 10 A (IEC 60947-5-1), miniature circuit-breaker C char.: 1.6 A (IEC 60947-5-1) or 6 A ( $I_K < 500 A$ )	
Electrical Safety		
<b>touch protection against electrical shock</b>	finger-safe	
<b>ATEX</b>		
certificate of suitability according to ATEX directive 2014/34/EU	BVS 06 ATEX F001	
explosion device group and category according to ATEX directive 2014/34/EU	II (2) G, II (2) D, I (M2)	
<b>Galvanic isolation</b>		
<b>(electrically) protective separation according to IEC 60947-1</b>	All circuits with protective separation (double creepage paths and clearances), the information in the "Protective Separation" test report, No. A0258, must be observed (link see further information)	
<b>Control circuit/ Control</b>		
<b>type of voltage of the control supply voltage</b>	AC/DC	
<b>control supply voltage at AC</b>		
• at 50 Hz rated value	110 ... 240 V	
• at 60 Hz rated value	110 ... 240 V	
<b>control supply voltage frequency 1</b>	50 ... 60 Hz	
<b>control supply voltage at DC rated value</b>	110 ... 240 V	
<b>operating range factor control supply voltage rated value at DC</b>		
• initial value	0.85	
• full-scale value	1.1	
<b>operating range factor control supply voltage rated value at AC at 50 Hz</b>		
• initial value	0.85	
• full-scale value	1.1	
<b>operating range factor control supply voltage rated value at AC at 60 Hz</b>		
• initial value	0.85	
• full-scale value	1.1	
<b>Approvals Certificates</b>		
General Product Approval	EMV	For use in hazardous locations



For use in hazardous locations	Test Certificates	Maritime application	other
IECEx	<a href="#">Miscellaneous</a>	<a href="#">Type Test Certificates/Test Report</a>	<a href="#">Confirmation</a>

Environment	Industrial Communication
-------------	--------------------------



## Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UF7300-1AU00-0>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UF7300-1AU00-0>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3UF7300-1AU00-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3UF7300-1AU00-0&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UF7300-1AU00-0&lang=en)





last modified:

12/13/2025