



circuit breaker 3VA2 IEC Frame 160 breaking capacity class C $I_{cu}=110 \text{ kA @ 415 V}$ 4-pole, line protection ETU850, LSI, $I_n=100 \text{ A}$ overload protection $I_r=40 \text{ A} \dots 100 \text{ A}$ short-circuit protection $I_{sd}=0.6 \dots 10 \times I_n$, $I_i=1.5 \dots 12 \times I_n$ neutral conductor protection adjustable (OFF, up to 160%) nut keeper kit

Model	
product brand name	SETRON
product designation	Molded case circuit breaker
design of the product	Line protection
design of the overcurrent release	ETU850
protection function of the overcurrent release	LSI
number of poles	4
General technical data	
insulation voltage / rated value	800 V
operating voltage / at AC / rated value	690 V
power loss [W] / maximum	10 W
power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	3.33 W
mechanical service life (operating cycles) / typical	25 000
electrical endurance (operating cycles) / at AC-1 / at 380/415 V	14 000
electrical endurance (operating cycles) / at AC-1 / at 690 V	9 800
product feature / for neutral conductors / upgradable/retrofitable / short-circuit and overload proof	No
ground-fault monitoring version	Without
product function	
• communication function	Yes
• other measurement function	Yes
Net Weight	3.2 kg
Current	
operational current	
• at 40 °C	100 A
• at 45 °C	100 A
• at 50 °C	100 A
• at 55 °C	100 A
• at 60 °C	100 A
• at 65 °C	100 A
• at 70 °C	100 A
Switching capacity according to IEC 60947	
switching capacity class of the circuit breaker	C
maximum short-circuit current breaking capacity (I_{cu})	
• at 240 V	150 kA

• at 415 V • at 440 V • at 500 V • at 690 V	110 kA 110 kA 85 kA 3 kA
operating short-circuit current breaking capacity (Ics)	
• at 240 V • at 415 V • at 440 V • at 500 V • at 690 V	150 kA 110 kA 110 kA 85 kA 2.5 kA
short-circuit current making capacity (Icm)	
• at 240 V • at 415 V • at 440 V • at 500 V • at 690 V	330 kA 242 kA 242 kA 187 kA 3.7 kA
Adjustable parameters	
product feature / for L-tripping / can be switched on/off	No
adjustable response value setting current (Ir) / of the L-trip / with I2t characteristic	
• minimum • maximum	40 A 100 A
adjustable response value delay time (tr) / for L-tripping / with I2t characteristic	
• minimum • maximum	0.5 s 25 s
adjustable response value setting current (Isd) / of S-trip / with I0t characteristic	
• minimum • maximum	60 A 1 000 A
adjustable response value setting current (Isd) / of S-trip / with I2t characteristic	
• minimum • maximum	60 A 1 000 A
adjustable response value delay time (tsd) / for S-tripping / with I0t characteristic	
• minimum • maximum	0.05 s 0.5 s
adjustable response value delay time (tsd) / for S-tripping / with I2t characteristic	
• minimum • maximum	0.05 s 0.5 s
adjustable response value setting current (Ii) / for I-tripping	
• minimum • maximum	150 A 1 200 A
adjustable setting current (InN) / for N-tripping	
• minimum • maximum	20 A 100 A
design of the N-conductor protection	adjustable OFF; 20% to 160%
product function / grounding protection	No
Mechanical Design	
product component	
• undervoltage release • voltage trigger • trip indicator	No No No
height [in]	7.13 in
height	181 mm
width [in]	5.51 in
width	140 mm
depth [in]	3.39 in
depth	86 mm

Connections					
arrangement of electrical connectors / for main current circuit	Front terminal				
type of electrical connection / for main current circuit	on both sides nut keeper kit				
type of connectable conductor cross-sections / for flat-bar terminal connection / minimum	13 x 1 mm				
type of connectable conductor cross-sections / for flat-bar terminal connection / maximum	25 x 8 mm				
design of the surface / of the connections / on the top of the switch (N, 1, 3, 5)	tin				
design of the surface / of the connections / on the bottom of the switch (N, 2, 4, 6)	tin				
Auxiliary circuit					
number of CO contacts / for auxiliary contacts	0				
Accessories					
product extension / optional / motor drive	Yes				
Environmental conditions					
protection class IP / on the front	IP40				
ambient temperature					
• during operation / minimum	-25 °C				
• during operation / maximum	70 °C				
• during storage / minimum	-40 °C				
• during storage / maximum	80 °C				
Environmental footprint					
global warming potential [CO2 eq] / total	61.814 kg				
global warming potential [CO2 eq] / during manufacturing	14.6 kg				
global warming potential [CO2 eq] / during operation	48.9 kg				
global warming potential [CO2 eq] / after end of life	-2.2 kg				
Siemens Eco Profile (SEP)	Siemens EcoTech				
reference code / according to IEC 81346-2	Q				
Approvals / Certificates					
General Product Approval					
		Confirmation		Miscellaneous	
General Product Approval	EMV	Test Certificates		Maritime application	
		Type Test Certificates/Test Report	Miscellaneous	Special Test Certificate	
Maritime application				other	
				CCS (China Classification Society)	
other	Dangerous goods		Environment		
Confirmation	Miscellaneous	Transport Information			Environmental Confirmations
Environment					

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA2110-7KP42-0AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA2110-7KP42-0AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA2110-7KP42-0AA0

CAX-Online-Generator

<https://www.siemens.com/cax>

Tender specifications

<https://www.siemens.com/specifications>

Characteristic curves

https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP='HAUPT'></mmp_prod_no>



