

product type designation	IE Connecting Cable M12-180/IE FC RJ45-145
product description	Flexible plug-in cable (4-core), preferred length, preassembled with one 4-pole M12 connector (D-coded) and one IE FC RJ45 plug 145 IE connecting cable M12-180/IE FC RJ45 Plug-145; IE FC Trailing cable GP pre-assembled with M12 connector (D-coded) and IE FC RJ45 plug; Length 2.0 m.
Technical Product Detail Page	https://i.siemens.com/1P6XV1871-5TH20
suitability for use	For connecting Industrial Ethernet stations (e.g. SIMATIC ET200pro, SCALANCE X208PRO and SIMOTION)
cable designation	2YY (ST) CY 2x2x0,75/1,5-100 LI GN
wire length	2 m
electrical data	
number of electrical connections	2
attenuation factor per length	
• at 10 MHz / maximum	0.063 dB/m
• at 100 MHz / maximum	0.213 dB/m
impedance	
• at 1 MHz ... 100 MHz	100 Ω
relative symmetrical tolerance	
• of the characteristic impedance at 1 MHz ... 100 MHz	5 %
near-end crosstalk per length	
• at 1 MHz ... 100 MHz	0.5 dB/m
transfer impedance per length / at 10 MHz	20 mΩ/m
loop resistance per length / maximum	120 mΩ/m
operating voltage	
• RMS value	80 V
NVP value in percent	66 %
mechanical data	
number of electrical cores	4
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires
core diameter	
• of AWG22 insulated conductor	0.75 mm
outer diameter	
• of inner conductor	0.75 mm
• of the wire insulation	1.5 mm
• of the inner sheath of the cable	3.9 mm
• of cable sheath	6.5 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.2 mm
material	
• of the wire insulation	polyethylene (PE)
• of the inner sheath of the cable	PVC
• of cable sheath	PVC
color	
• of the insulation of data wires	white/yellow/blue/orange
• of cable sheath	green
bending radius	
• with single bend / minimum permissible	32.5 mm
• with multiple bends / minimum permissible	49 mm
• with continuous bending	100 mm
number of bending cycles	3000000; Drag chain suitable for 3 million bending cycles at a bending radius of 100 mm, a speed of 4 m/s and an acceleration of 4 m/s ²
tensile load / maximum	150 N

weight per length	68 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport during installation note 	-25 ... +75 °C -25 ... +75 °C -25 ... +75 °C -10 ... +60 °C electrical properties measured at 20 °C
fire behavior	flame resistant according to UL 1685 (CSA FT 4)
chemical resistance	
<ul style="list-style-type: none"> to mineral oil to grease to water 	conditional resistance Conditional resistance conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free PoE capability PoE+ capability silicon-free 	No Yes Yes Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us, CMG FT4 / (ETL)us PLTC / Sun Res / OIL RES
UL/ETL style / 600 V Rating	Yes; cRUus AWM 21694 AWM I A/B 60°C 600V FT2
certificate of suitability	
<ul style="list-style-type: none"> EAC approval CE marking RoHS conformity 	Yes Yes Yes
standard for structured cabling	Cat5e
Marine classification association	
<ul style="list-style-type: none"> American Bureau of Shipping Europe Ltd. (ABS) French marine classification society (BV) Det Norske Veritas (DNV) Germanische Lloyd (GL) Lloyds Register of Shipping (LRS) Nippon Kaiji Kyokai (NK) Polski Rejestr Statkow (PRS) 	No No No No No No No
further information / internet links	
internet link	
<ul style="list-style-type: none"> to website: Selection guide for cables and connectors to web page: selection aid TIA Selection Tool to web page: SiePortal to website: Image database to website: CAX-Download-Manager to website: Industry Online Support 	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com
security information	
security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under</p>

Approvals / Certificates

General Product Approval



[Declaration of Con-
formity](#)



[Manufacturer Declara-
tion](#)

[China RoHS](#)

other

Industrial Communication

[Miscellaneous](#)

[PROFINET](#)

last modified:

3/10/2026