



SITOP PSU100L/1AC/24VDC/5A

SITOP PSU100L 24 V/5 A Stabilized power supply input: 120/230 V AC, output: 24 V DC/5 A

General information	
Technical Product Detail Page	https://l.siemens.com/1P6EP1333-1LB00
input	
type of the power supply network	1-phase AC
supply voltage at AC	Set by means of selector switch on the device
supply voltage	120 V/230 V
input voltage 1 at AC	93 ... 132 V
input voltage 2 at AC	187 ... 264 V
wide range input	No
overvoltage overload capability	2.3 × Vin rated, 1.3 ms
buffering time for rated value of the output current in the event of power failure minimum	20 ms
operating condition of the mains buffering	at Vin = 93/187 V
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 120 V	2.1 A
• at rated input voltage 230 V	1.15 A
current limitation of inrush current at 25 °C maximum	32 A
duration of inrush current limiting at 25 °C	
• typical	3 ms
I ² t value maximum	0.8 A ² ·s
fuse protection type	T 3,15 A/250 V (not accessible)
fuse protection type in the feeder	Recommended miniature circuit breaker: from 6 A characteristic C
output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
output voltage adjustable	Yes; via potentiometer
adjustable output voltage	22.8 ... 26.4 V
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	0.5 %
residual ripple	
• maximum	150 mV
• typical	50 mV
voltage peak	

<ul style="list-style-type: none"> • maximum 	240 mV
<ul style="list-style-type: none"> • typical 	150 mV
display version for normal operation	Green LED for 24 V OK
behavior of the output voltage when switching on	Overshoot of Vout approx. 4 %
response delay maximum	1.5 s
voltage increase time of the output voltage	
<ul style="list-style-type: none"> • typical 	130 ms
output current	
<ul style="list-style-type: none"> • rated value 	5 A
<ul style="list-style-type: none"> • rated range 	0 ... 5 A; +45 ... +60 °C: Derating 2%/K
supplied active power typical	120 W
bridging of equipment	Yes
number of parallel-switched equipment resources for increasing the power	2
efficiency	
efficiency in percent	86 %
power loss [W]	
<ul style="list-style-type: none"> • at rated output voltage for rated value of the output current typical 	17 W
closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.3 %
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	2 %
setting time	
<ul style="list-style-type: none"> • load step 10 to 90% typical 	0.4 ms
<ul style="list-style-type: none"> • load step 90 to 10% typical 	0.4 ms
protection and monitoring	
design of the overvoltage protection	< 33 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Constant current characteristic
<ul style="list-style-type: none"> • typical 	5.25 A
enduring short circuit current RMS value	
<ul style="list-style-type: none"> • typical 	8 A
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Output voltage: SELV, ES1 (IEC 62368-1), DVC As (IEC 61204-7)
operating resource protection class	Class I
leakage current	
<ul style="list-style-type: none"> • maximum 	3.5 mA
<ul style="list-style-type: none"> • typical 	0.4 mA
protection class IP	IP20
EMC	
standard	
<ul style="list-style-type: none"> • for emitted interference 	EN 55022 Class A
<ul style="list-style-type: none"> • for mains harmonics limitation 	-
<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-2
standards, specifications, approvals	
certificate of suitability	
<ul style="list-style-type: none"> • CE marking 	Yes
<ul style="list-style-type: none"> • UL approval 	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
<ul style="list-style-type: none"> • UKCA marking 	Yes
<ul style="list-style-type: none"> • EAC approval 	Yes
<ul style="list-style-type: none"> • NEC Class 2 	No
type of certification	
<ul style="list-style-type: none"> • BIS 	Yes; R-41183539
<ul style="list-style-type: none"> • CB-certificate 	Yes
MTBF at 40 °C	3 076 166 h
standards, specifications, approvals hazardous environments	

certificate of suitability	
<ul style="list-style-type: none"> • IECEx • ATEX • ULhazloc approval • FM registration 	<p>No</p> <p>No</p> <p>No</p> <p>No</p>
standards, specifications, approvals marine classification	
shipbuilding approval	No
Marine classification association	
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • Det Norske Veritas (DNV) • Lloyds Register of Shipping (LRS) 	<p>No</p> <p>No</p> <p>No</p> <p>No</p>
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
<ul style="list-style-type: none"> • total • during manufacturing • during operation • after end of life 	<p>474.3 kg</p> <p>12.9 kg</p> <p>460.8 kg</p> <p>0.37 kg</p>
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation • during transport • during storage 	<p>0 ... 60 °C; with natural convection</p> <p>-40 ... +85 °C</p> <p>-40 ... +85 °C</p>
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection	screw terminal
<ul style="list-style-type: none"> • at input • at output • for auxiliary contacts 	<p>L, N, PE: 1 screw terminal each for 0.5 ... 2.5 mm² single-core/finely stranded</p> <p>+, -: 2 screw terminals each for 0.5 ... 2.5 mm²</p> <p>-</p>
mechanical data	
width × height × depth of the enclosure	50 × 125 × 120 mm
installation width × mounting height	50 mm × 225 mm
required spacing	
<ul style="list-style-type: none"> • top • bottom • left • right 	<p>50 mm</p> <p>50 mm</p> <p>0 mm</p> <p>0 mm</p>
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
<ul style="list-style-type: none"> • DIN-rail mounting • S7 rail mounting • wall mounting 	<p>Yes</p> <p>No</p> <p>No</p>
housing can be lined up	Yes
net weight	0.5 kg
further information internet links	
internet link	
<ul style="list-style-type: none"> • to website: Industry Mall • to web page: selection aid TIA Selection Tool • to web page: power supplies • to website: CAX-Download-Manager • to website: Industry Online Support 	<p>https://mall.industry.siemens.com</p> <p>https://www.siemens.com/tstcloud</p> <p>https://siemens.com/sitop</p> <p>https://siemens.com/cax</p> <p>https://support.industry.siemens.com</p>
additional information	
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and

solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Classifications

	Version	Classification
eClass	14	27-04-07-01
eClass	12	27-04-07-01
eClass	9.1	27-04-07-01
eClass	9	27-04-07-01
eClass	8	27-04-90-02
eClass	7.1	27-04-90-02
eClass	6	27-04-90-02
ETIM	10	EC002540
ETIM	9	EC002540
ETIM	8	EC002540
ETIM	7	EC002540
IDEA	4	4130
UNSPSC	15	39-12-10-04

Approvals Certificates

Environmental Product Declaration

• global warming potential [CO2 eq] / during manufacturing	12.9 kg
• global warming potential [CO2 eq] / during operation	460.8 kg
• global warming potential [CO2 eq] / after end of life	0.37 kg
• global warming potential [CO2 eq] / total	474.3 kg

Environment

General Product Approval



[Manufacturer Declaration](#)

[Declaration of Conformity](#)



General Product Approval

[China RoHS](#)



[BIS CRS](#)

last modified:

5/5/2026