



*** Spare part *** SIMATIC DP, Electronics module for ET 200S, 1 SI serial interface 1-channel, 15 mm width, RS232/422, 485 MODBUS/USS

Figure similar

Supply voltage	
Rated value (DC)	24 V
Reverse polarity protection	Yes
Input current	
from supply voltage L+, max.	80 mA; Typ. 20 mA
from backplane bus 3.3 V DC, max.	10 mA
Power loss	
Power loss, typ.	1.2 W
Memory	
Standard blocks	11 100 byte; Modbus: S_SEND 2700, S_RCV 2400, S_MODB 6000; USI: S_SEND 2700, S_RCV 2400, S_USST 1900, S_USSR 2600, S_USSI 1500
Interfaces	
Number of interfaces	1
Point-to-point connection	
<ul style="list-style-type: none"> Transmission rate, max. 	115.2 kbit/s; half duplex: 110, 300, 600, 1 200, 2 400, 4 800, 9 600, 19 200, 38 400, 57 600, 76 800, 115 200 bps
Integrated protocol driver	
— Modbus	Yes
— USS	Yes
Signals	
— RS 232C	RS 232C signals: 8 (TxD, RxD, RTS, CTS, DTR, DSR, DCD, PE)
— RS 422	TxD(A), RxD(A), TxD(B), RxD(B), GND
— RS 485	R/T(A), R/T(B), GND
Character frame (adjustable)	
— Bits per character	8
— Number of start/stop bits	1 or 2 (USS only 1)
— Bits per character frame	10 or 11 (USS only 11 bit)
— Parity	none, odd, even (USI even only)
Data quantity per PLC sampling cycle	
— Send	32 byte; With IM151-1 Standard as of 6ES7151-1AA04-0AB0; with IM151-1 High Feature as of 6ES7151-1BA01-0AB0; otherwise 8 bytes
— Receive	32 byte; With IM151-1 Standard as of 6ES7151-1AA04-0AB0; with IM151-1 High Feature as of 6ES7151-1BA01-0AB0; otherwise 8 bytes
Interface types	
RS 232	
<ul style="list-style-type: none"> Cable length, max. 	15 m
RS 485	
<ul style="list-style-type: none"> Cable length, max. 	1 200 m
Interrupts/diagnostics/status information	

Diagnostics indication LED	
• Receive RxD	Yes
• Transmit TxD	Yes
• Group error SF (red)	Yes

Potential separation	
Potential separation interface	
• Between RS 422/485 and internal power supply	Yes
• between RS 232 and internal power supply	Yes

Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	60 °C

Dimensions	
Width	15 mm
Height	81 mm
Depth	52 mm

Weights	
Weight, approx.	50 g

Classifications			
		Version	Classification
	eClass	14	27-24-26-08
	eClass	12	27-24-26-08
	eClass	9.1	27-24-26-08
	eClass	9	27-24-26-08
	eClass	8	27-24-26-08
	eClass	7.1	27-24-26-08
	eClass	6	27-24-26-08
	ETIM	10	EC001604
	ETIM	9	EC001604
	ETIM	8	EC001604
	ETIM	7	EC001604
	IDEA	4	3564
	UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval



EG-Konf.

[Miscellaneous](#)

[Manufacturer Declaration](#)



UL



RCM

General Product Approval

EMV **For use in hazardous locations**



RCM



ATEX



ATEX



UL



IECEX

For use in hazardous locations **Maritime application**



ATEX

[Miscellaneous](#)

[CCC-Ex](#)



ABS



BUREAU VERITAS



DNV

Maritime application



[NK / Nippon Kaiji Ky-
okai](#)



[CCS \(China Classifica-
tion Society\)](#)

last modified:

8/22/2025