



Miniature circuit breaker 240 V 14kA, 3-pole, C, 40A, D=70 mm according to UL 489

Figure similar


| Model | |
|---|--|
| product brand name | SENTRON |
| product designation | Miniature circuit breakers |
| design of the product | Miniature circuit-breaker 5SJ4 |
| General technical data | |
| number of poles | 3 |
| design of pole | 3P |
| tripping characteristic class | C |
| mechanical service life (operating cycles) typical | 10 000 |
| installation environment regarding EMC | Suitable for environment B (immunity to interference not applicable) |
| reference code according to DIN 40719 extended according to IEC 204-2 according to IEC 750 | F |
| overvoltage category | 3 |
| degree of pollution | 3 |
| Voltage | |
| insulation voltage (Ui) at AC rated value | 440 V |
| <ul style="list-style-type: none"> • operational current <ul style="list-style-type: none"> — at 30 °C rated value — at 40 °C rated value — at 50 °C rated value — at 55 °C rated value — at 60 °C rated value | |
| • operational current at AC rated value | 40 A |
| • at 30 °C rated value | 40 A |
| • at 40 °C rated value | 40 A |
| • at 50 °C rated value | 38 A |
| • at 55 °C rated value | 37 A |
| • at 60 °C rated value | 36 A |
| Supply voltage | |
| supply voltage | |
| • at AC | 400 V |
| • at DC rated value | 60 V |
| value range of the supply voltage frequency | 50/60 Hz |
| Operating voltage | |
| • at AC according to UL 489 and CSA C22.2 No. 5-02 maximum | 240 V |
| • at DC rated value maximum | 60 V |
| • at DC 1-channel according to UL 489 and CSA C22.2 No. 5-02 maximum | 60 V |
| • at DC 2-channel according to UL 489 and CSA C22.2 No. 5-02 maximum | 125 V |
| supply voltage frequency rated value | 50 Hz |
| Protection class | |

| | |
|---|--|
| protection class IP | IP 0 in the handle range |
| Breaking Capacity | |
| switching capacity current | |
| • according to EN 60898 rated value | 10 kA |
| • according to IEC 60947-2 rated value | 15 kA |
| Dissipation | |
| power loss [W] for rated value of the current at AC in hot operating state per pole | 4.8 W |
| Main circuit | |
| type of voltage supply at AC according to UL 489 and CSA C22.2 No. 5-02 | 240 |
| suitability for operation | Infrastructure / Industry |
| Product details | |
| product feature touch protection | Yes |
| product component | |
| • tunnel terminals top | No |
| • tunnel terminals bottom | No |
| • combined terminal top | Yes |
| • combined terminal bottom | Yes |
| • neutral conductor switching | No |
| product feature halogen-free | Yes |
| product feature sealable | Yes |
| product feature silicon-free | Yes |
| product extension installable supplementary devices | Yes |
| Product function | |
| set values setting current (li) for I-tripping | 7,5 |
| reference value setting current (li) for I-tripping | x In |
| product function note | Terminal tightening torque for Cu, 60/75°C; 3.5Nm/31lb.in |
| Short circuit | |
| short-circuit current breaking capacity (Icn) at AC according to UL 1077 and CSA C22.2 No.235 | 14 kA |
| Connections | |
| connectable conductor cross-section finely stranded with core end processing | |
| • minimum | 0.75 mm ² |
| • maximum | 25 mm ² |
| tightening torque with screw-type terminals maximum | 3.5 N·m |
| position of power supply cord | Any |
| Mechanical Design | |
| height | 110 mm |
| width | 54 mm |
| depth | 70 mm |
| installation depth | 70 mm |
| number of modular width units | 3 |
| fastening method | on standard mounting rail |
| mounting position | any |
| Net Weight | 492 g |
| Environmental conditions | |
| standard | IEC / EN 60947-2 / UL 489 |
| vibration resistance | 50 m/s ² at 25 to 150Hz and 60m/s ² at 35Hz (4sec) |
| vibration resistance according to IEC 60068-2-6 | ±1 mm at 5 to 25 Hz; 50 m/s ² at 25 to 150 Hz |
| ambient temperature during operation | |
| • minimum | -25 °C |
| • maximum | 55 °C |
| ambient temperature during operation | max. 95% humidity |
| ambient temperature during storage | |
| • minimum | -40 °C |
| • maximum | 75 °C |
| Approvals Certificates | |

[Environmental Confirmations](#)[Environmental Confirmations](#)[Confirmation](#)[Special Test Certificate](#)[Confirmation](#)

Further information

Information on the packaging<https://support.industry.siemens.com/cs/ww/en/view/109813875>**Information for data generation and storage**<https://support.industry.siemens.com/cs/ww/en/view/109995012>**Information- and Downloadcenter (Catalogs, Brochures,...)**<https://www.siemens.com/lowvoltage/catalogs>**Industry Mall (Online ordering system)**<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SJ4340-7HG41>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<https://support.industry.siemens.com/cs/ww/en/ps/5SJ4340-7HG41>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SJ4340-7HG41**CAx-Online-Generator**<https://www.siemens.com/cax>**Tender specifications**<https://www.siemens.com/specifications>**Characteristic curves**[https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP=)



last modified:

1/11/2026

