



DP/AS-Interface F-Link. gateway PROFIBUS DP/AS-i for safety-oriented data transmission from ASIsafe to PROFIBUS-DP-PROFIsafe. Master profile M3/M4 according to AS-i specification V3.0. degree of protection IP20. screw terminals

General technical data		
product designation		PROFIsafe/ASIsafe F-Link
product type designation		DP/AS-i F-Link
protection class IP		IP20
type of electrical connection of the AS-Interface		Screw-type connection
type of voltage supply		via 24 V DC
consumed current		
<ul style="list-style-type: none"> from profile conductors of the AS-Interface — at 24 V with AS-i Power24V maximum 	mA	100
power loss [W]	W	3
insulation voltage rated value	V	500
product feature redundancy capability		No
product function suitable for AS-i Power24V		No
product function		
<ul style="list-style-type: none"> web-based management diagnostics via email galvanic isolation 		No No Yes
display version		
<ul style="list-style-type: none"> as status display by LED as status indication through display 		DEVICE, ASi, BF, SF Dot-matrix display, 2-line
type of configuration of the AS-Interface		Set pushbutton on device, STEP7, GSD, command interface
Communication/ Protocol		
version of the AS-Interface specification		V 3.0
AS-Interface master profile is supported		M4 (in acc. with AS-interface specification V 3.0)
type of data transmission		PROFIBUS
number of interfaces		
<ul style="list-style-type: none"> as AS-Interface according to RS 485 according to Industrial Ethernet according to PROFINET according to wireless according to USB other 		1 1 0 0 0 0 0
product component optical interface		No
protocol is supported		
<ul style="list-style-type: none"> ASIsafe (Safety at work) protocol PROFIsafe protocol PROFIBUS protocol PROFINET IO protocol 		Yes Yes Yes No

<ul style="list-style-type: none"> • PROFINET CBA protocol 		No
<ul style="list-style-type: none"> • TCP/IP 		No
<ul style="list-style-type: none"> • SNMP 		No
standard for wireless communication IEEE 802.11		No

Inputs/ Outputs

number of inputs for AS-Interface maximum		496
number of outputs for AS-Interface maximum		496
number of AS-i devices per AS-Interface maximum		62
bus cycle time of the AS-Interface		
<ul style="list-style-type: none"> • for 31 devices 	ms	5
<ul style="list-style-type: none"> • for 62 devices 	ms	10
access to digital I/O data		via process image/peripheral addresses
access to analog I/O data		via process diagram/peripheral addresses and data record transfer

Mechanical data

width	mm	45
height	mm	111
depth	mm	124
fastening method		snap-on fastening on 35 mm DIN rail or screw fastening using an additional push-in lug
module format		IP20

Ambient conditions

ambient temperature		
<ul style="list-style-type: none"> • if installed on horizontal mounting rail during operation 	°C	0 ... 50
<ul style="list-style-type: none"> • during transport 	°C	-40 ... +85
<ul style="list-style-type: none"> • during storage 	°C	-40 ... +85
relative humidity at 25 °C during operation maximum	%	95
installation altitude at height above sea level maximum	m	2 000

Safety related data

suitability for use safety-related function		Yes
category according to EN 954-1		4
Safety Integrity Level (SIL) according to IEC 61508		SIL 3
SIL Claim Limit (subsystem) according to EN 62061		3
performance level (PL) according to EN ISO 13849-1		e
requirement class according to DIN V 19250		AK7, AK8
explosion protection marking for intrinsic safety of related equipment		
<ul style="list-style-type: none"> • EEx ia 		No
<ul style="list-style-type: none"> • EEx ib 		No
explosion protection category for gas		none
explosion protection category for dust		none

Certificates/ approvals

General Product Approval	EMV	Functional Safety
--------------------------	-----	-------------------



[Type Examination Certificate](#)

Test Certificates	other	Environment	Industrial Communication
-------------------	-------	-------------	--------------------------

[Type Test Certificates/Test Report](#)

[Confirmation](#)



[Environmental Confirmations](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK3141-1CD10>

Cax online generator



<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK3141-1CD10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK3141-1CD10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK3141-1CD10&lang=en



last modified:

9/5/2025 