

SIPLUS HMI TP1200 Comfort based on 6AV2124-0MC01-0AX0 with conformal coating, 0...+50 °C,




Figure similar

General information	
Product type designation	TP1200 Comfort
based on	<a href="#">6AV2124-0MC01-0AX0</a>
Display	
Design of display	TFT
Screen diagonal	12.1 in
Display width	261.1 mm
Display height	163.2 mm
Number of colors	16 777 216
Resolution (pixels)	
• Horizontal image resolution	1 280 pixel
• Vertical image resolution	800 pixel
Backlighting	
• MTBF backlighting (at 25 °C)	80 000 h
• Backlight dimmable	Yes; 0-100 %
Control elements	
Keyboard fonts	
• Function keys	
— Number of function keys	0
— Number of function keys with LEDs	0
• Keys with LED	No
• System keys	No
• Numeric keyboard	Yes; Onscreen keyboard
• alphanumeric keyboard	Yes; Onscreen keyboard
Touch operation	
• Design as touch screen	Yes; Analog-resistive
Expansions for operator control of the process	
• DP direct LEDs (LEDs as S7 output I/O)	
— F1...Fx	0
• Direct keys (keys as S7 input I/O)	
— F1...Fx	0
• Direct keys (touch buttons as S7 input I/O)	40
Installation type/mounting	
Mounting position	vertical
Wall mounting/direct mounting	No
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
maximum permissible angle of inclination without external	35°

ventilation	
<b>Supply voltage</b>	
Type of supply voltage	DC
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
<b>Input current</b>	
Current consumption (rated value)	0.85 A
Starting current inrush $I^2t$	0.5 A <sup>2</sup> ·s
<b>Power</b>	
Active power input, typ.	20 W
<b>Processor</b>	
Processor type	X86
<b>Memory</b>	
Flash	Yes
RAM	Yes
Memory available for user data	12 Mbyte
<b>Type of output</b>	
Info LED	No
Power LED	No
Error LED	No
Acoustics	
• Buzzer	No
• Speaker	Yes
<b>Time of day</b>	
Clock	
• Hardware clock (real-time)	Yes
• Software clock	Yes
• retentive	Yes; Back-up duration typically 6 weeks
• synchronizable	Yes
<b>Interfaces</b>	
Number of industrial Ethernet interfaces	1; 2 ports (switch)
Number of RS 485 interfaces	1; RS 422 / 485 combined
Number of RS 422 interfaces	0; together with RS 485
Number of RS 232 interfaces	0
Number of USB interfaces	2; USB 2.0
• USB Mini B	1; 5-pole
Number of 20 mA interfaces (TTY)	0
Number of parallel interfaces	0
Number of other interfaces	0
Number of SD card slots	2
With software interfaces	No
Industrial Ethernet	
• Industrial Ethernet status LED	2
• Number of ports of the integrated switch	2
<b>Protocols</b>	
PROFINET	Yes
Supports protocol for PROFINET IO	Yes
IRT	Yes; As of WinCC V12
PROFIBUS	Yes
EtherNet/IP	Yes
MPI	Yes
<b>Protocols (Ethernet)</b>	
• TCP/IP	Yes
• DHCP	Yes
• SNMP	Yes
• DCP	Yes
• LLDP	Yes

<b>WEB characteristics</b>	
• HTTP	Yes
• HTTPS	Yes
• HTML	Yes
• XML	Yes
• CSS	Yes
• Active X	Yes
• JavaScript	Yes
• Java VM	No
<b>Redundancy mode</b>	
<b>Media redundancy</b>	
— MRP	Yes; As of WinCC V12
<b>Further protocols</b>	
• CAN	No
• MODBUS	Yes
<b>Interrupts/diagnostics/status information</b>	
<b>Diagnoses</b>	
• Diagnostic information readable	Yes; S7 controller
<b>EMC</b>	
Emission of radio interference acc. to EN 55 011	
• Limit class A, for use in industrial areas	Yes
• Limit class B, for use in residential areas	No
<b>Degree and class of protection</b>	
IP (at the front)	IP65
IP (rear)	IP20
NEMA (front)	
• Enclosure Type 4 at the front	Yes
• Enclosure Type 4x at the front	Yes
<b>Standards, approvals, certificates</b>	
<b>Ecological footprint</b>	
• environmental product declaration	Yes
<b>Global warming potential</b>	
— global warming potential, (total) [CO <sub>2</sub> eq]	301 kg
— global warming potential, (during production) [CO <sub>2</sub> eq]	81.2 kg
— global warming potential, (during operation) [CO <sub>2</sub> eq]	221 kg
— global warming potential, (after end of life cycle) [CO <sub>2</sub> eq]	-2.25 kg
<b>Ambient conditions</b>	
Ambient temperature during operation	
Operation (vertical installation)	
— For vertical installation, min.	0 °C; = Tmin
— For vertical installation, max.	50 °C; = Tmax
Operation (max. tilt angle)	
— At maximum tilt angle, min.	0 °C; = Tmin
— At maximum tilt angle, max.	40 °C; = Tmax
Operation (vertical installation, portrait format)	
— For vertical installation, min.	0 °C; = Tmin
— For vertical installation, max.	40 °C; = Tmax
Operation (max. tilt angle, portrait format)	
— At maximum tilt angle, min.	0 °C; = Tmin
— At maximum tilt angle, max.	35 °C; = Tmax
Ambient temperature during storage/transportation	
• min.	-20 °C
• max.	60 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m
• Ambient air temperature-barometric pressure-altitude	Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m) // Tmin ... (Tmax - 10 K) at 795 hPa ... 658 hPa (+2 000 m ... +3 500 m) // Tmin ... (Tmax -20 K)

		at 658 hPa ... 540 hPa (+3 500 m ... +5 000 m)
Relative humidity	• With condensation, tested in accordance with IEC 60068-2-38, max.	100 %; RH incl. condensation/frost (no commissioning under condensation conditions)
Resistance		
Coolants and lubricants	— Resistant to commercially available coolants and lubricants	Yes; Incl. diesel and oil droplets in the air
Use in stationary industrial systems	<ul style="list-style-type: none"> <li>— to biologically active substances according to EN 60721-3-3</li> <li>— to chemically active substances according to EN 60721-3-3</li> <li>— to mechanically active substances according to EN 60721-3-3</li> </ul>	<p>Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request</p> <p>Yes; Class 3C4 (RH &lt; 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *</p> <p>Yes; Class 3S4 incl. sand, dust, *</p>
Use on ships/at sea	<ul style="list-style-type: none"> <li>— to biologically active substances according to EN 60721-3-6</li> <li>— to chemically active substances according to EN 60721-3-6</li> <li>— to mechanically active substances according to EN 60721-3-6</li> </ul>	<p>Yes; Class 6B2 mold and fungal spores (excluding fauna); Class 6B3 on request</p> <p>Yes; Class 6C3 (RH &lt; 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *</p> <p>Yes; Class 6S3 incl. sand, dust; *</p>
Usage in industrial process technology	<ul style="list-style-type: none"> <li>— Against chemically active substances acc. to EN 60654-4</li> <li>— Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04</li> </ul>	<p>Yes; Class 3 (excluding trichlorethylene)</p> <p>Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)</p>
Remark	<ul style="list-style-type: none"> <li>— Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04</li> </ul> <p>* The supplied plug covers must remain in place over the unused interfaces during operation!</p>	
Conformal coating	<ul style="list-style-type: none"> <li>• Coatings for printed circuit board assemblies acc. to EN 61086</li> <li>• Protection against fouling acc. to EN 60664-3</li> <li>• Military testing according to MIL-I-46058C, Amendment 7</li> <li>• Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A</li> </ul>	
Operating systems		
proprietary	No	
pre-installed operating system	<ul style="list-style-type: none"> <li>• Windows CE</li> </ul>	
Configuration		
Message indicator	Yes	
Alarm system (incl. buffer and acknowledgment)	Yes	
Process value display (output)	Yes	
Process value default (input) possible	Yes	
Recipe management	Yes	
Configuration software		
<ul style="list-style-type: none"> <li>• STEP 7 Basic (TIA Portal)</li> <li>• STEP 7 Professional (TIA Portal)</li> <li>• WinCC flexible Compact</li> <li>• WinCC flexible Standard</li> <li>• WinCC flexible Advanced</li> <li>• WinCC Basic (TIA Portal)</li> <li>• WinCC Comfort (TIA Portal)</li> <li>• WinCC Advanced (TIA Portal)</li> <li>• WinCC Professional (TIA Portal)</li> </ul>	<ul style="list-style-type: none"> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>Yes; from V11</li> <li>Yes; from V11</li> <li>Yes; from V11</li> </ul>	
Languages		
Online languages	• Number of online/runtime languages	32

Project languages	
• Languages per project	32
Functionality under WinCC (TIA Portal)	
Libraries	Yes
Applications/options	
• Web browser	Yes
• Pocket Word	Yes
• Pocket Excel	Yes
• PDF Viewer	Yes
• Media Player	Yes
• SIMATIC WinCC Sm@rtServer	Yes
• SIMATIC WinCC Audit	Yes
Number of Visual Basic Scripts	Yes
Task planner	
• time-controlled	Yes
• task-controlled	Yes
Help system	
• Number of characters per info text	70
Message system	
• Number of alarm classes	32
• Bit messages	Yes
— Number of bit messages	4 000
• Analog messages	Yes
— Number of analog messages	200
• S7 alarm number procedure	Yes
• System messages HMI	Yes
• System event, more (SIMATIC S7, SINUMERIK, SIMOTION, ... )	Yes
• Number of characters per message	80
• Number of process values per message	8
• Acknowledgment groups	Yes
• Message indicator	Yes
• Message buffer	
— Number of entries	1 024
— Circulating buffer	Yes
— retentive	Yes
— maintenance-free	Yes
Recipe management	
• Number of recipes	300
• Data records per recipe	500
• Entries per data record	1 000
• Size of internal recipe memory	2 Mbyte
• Recipe memory expandable	Yes
Variables	
• Number of variables per device	2 048
• Number of variables per screen	400
• Limit values	Yes
• Multiplexing	Yes
• Structures	Yes
• Arrays	Yes
Images	
• Number of configurable images	500
• Permanent window/default	Yes
• Global image	Yes
• Pop-up images	Yes
• Slide-in images	Yes
• Image selection by PLC	Yes
• Image number in the PLC	Yes
Image objects	

● Number of objects per image	400
● Text fields	Yes
● I/O fields	Yes
● Graphic I/O fields (graphics list)	Yes
● Symbolic I/O fields (text list)	Yes
● Date/time fields	Yes
● Switches	Yes
● Buttons	Yes
● Graphic display	Yes
● Icons	Yes
● Geometric objects	Yes
<b>Complex image objects</b>	
● Number of complex objects per screen	20
● Alarm view	Yes
● Trend view	Yes
● User view	Yes
● Status/control	Yes
● Sm@rtClient view	Yes
● Recipe view	Yes
● f(x) trend view	Yes
● System diagnostics view	Yes
● Media Player	Yes
● HTML browser	Yes
● PDF display	Yes
● IP camera display	Yes
● Bar graphs	Yes
● Sliders	Yes
● Pointer instruments	Yes
● Analog/digital clock	Yes
<b>Lists</b>	
● Number of text lists per project	500
● Number of entries per text list	500
● Number of graphics lists per project	500
● Number of entries per graphics list	500
<b>Archiving</b>	
● Number of archives per device	50
● Number of entries per archive	20 000
● Message archive	Yes
● Process value archive	Yes
● Archiving methods	
— Sequential archive	Yes
— Short-term archive	Yes
● Memory location	
— Memory card	Yes
— USB memory	Yes
— Ethernet	Yes
● Data storage format	
— CSV	Yes
— TXT	Yes
— RDB	Yes
<b>Security</b>	
● Number of user groups	50
● Number of user rights	32
● Number of users	50
● Password export/import	Yes
● SIMATIC Logon	Yes
<b>Logging through printer</b>	
● Alarms	Yes
● Report (shift log)	Yes

• Hardcopy	Yes
• Electronic print to file	Yes; PDF, HTML
<b>Character sets</b>	
• Keyboard fonts — US English	Yes
<b>Transfer (upload/download)</b>	
• MPI/PROFIBUS DP	Yes
• USB	Yes
• Ethernet	Yes
• using external storage medium	Yes
<b>Process coupling</b>	
• S7-1200	Yes
• S7-1500	Yes
• S7-200	Yes
• S7-300/400	Yes
• LOGO!	Yes
• WinAC	Yes
• SINUMERIK	Yes; with SINUMERIK option package
• SIMOTION	Yes
• Allen Bradley (EtherNet/IP)	Yes
• Allen Bradley (DF1)	Yes
• Mitsubishi (MC TCP/IP)	Yes
• Mitsubishi (FX)	Yes
• OMRON (FINS TCP)	No
• OMRON (LINK/Multilink)	Yes
• Modicon (Modbus TCP/IP)	Yes
• Modicon (Modbus)	Yes
• OPC UA Client	Yes
• OPC UA Server	Yes
<b>Service tools/configuration aids</b>	
• Backup/Restore manually	Yes
• Backup/Restore automatically	Yes
• Simulation	Yes
• Device switchover	Yes
<b>Peripherals/Options</b>	
Printer	Yes
SIMATIC HMI MM memory card: Multi Media Card	Yes; Up to 128 MB
SIMATIC HMI SD memory card: Secure Digital memory card	Yes; Up to 2 GB
SIMATIC HMI CF memory card Compact Flash Card	No
USB memory	Yes
SIMATIC IPC USB Flashdrive (USB stick)	Yes; Up to 16 GB
SIMATIC HMI USB stick	Yes; Up to 8 GB
Network camera	Yes
<b>Mechanics/material</b>	
Enclosure material (front)	
• Plastic	No
• Aluminum	Yes
• Stainless steel	No
<b>Dimensions</b>	
Width of the housing front	330 mm
Height of housing front	241 mm
Mounting cutout, width	310 mm
Mounting cutout, height	221 mm
mounting depth	64 mm
<b>Weights</b>	
Weight (without packaging)	2.8 kg
Weight (with packaging)	3.5 kg
<b>Classifications</b>	

	Version	Classification
eClass	14	27-33-02-01
eClass	12	27-33-02-01
eClass	9.1	27-33-02-01
eClass	9	27-33-02-01
eClass	8	27-24-23-02
eClass	7.1	27-24-23-02
eClass	6	27-24-23-02
ETIM	10	EC001412
ETIM	9	EC001412
ETIM	8	EC001412
ETIM	7	EC001412
IDEA	4	6607
UNSPSC	15	43-21-15-06

#### Approvals / Certificates

##### General Product Approval

EMV

[Manufacturer Declaration](#)



[China RoHS](#)



EMV

For use in hazardous locations

Environment



IECEx



[CCC-Ex](#)



last modified:

7/28/2025