



SITOP PSU100L/1AC/24VDC/2.5A

SITOP PSU100L 24 V/2.5 A Stabilized power supply input: 120/230 V AC, output: DC 24 V/2.5 A

Technical Product Detail Page

<https://i.siemens.com/1P6EP1332-1LB00>

input	
type of the power supply network	1-phase AC
supply voltage at AC	Set by means of selector switch on the device
supply voltage	120 V/230 V
input voltage 1 at AC	93 ... 132 V
input voltage 2 at AC	187 ... 264 V
wide range input	No
overvoltage overload capability	2.3 × Vin rated, 1.3 ms
buffering time for rated value of the output current in the event of power failure minimum	20 ms
operating condition of the mains buffering	at Vin = 93/187 V
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 120 V	1.1 A
• at rated input voltage 230 V	0.65 A
current limitation of inrush current at 25 °C maximum	27 A
duration of inrush current limiting at 25 °C	
• typical	3 ms
I <sub>2t</sub> value maximum	0.3 A <sup>2</sup> ·s
fuse protection type	T 2 A/250 V (not accessible)
fuse protection type in the feeder	Recommended miniature circuit breaker: from 3 A characteristic C
output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
output voltage adjustable	Yes; via potentiometer
adjustable output voltage	22.8 ... 26.4 V
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	0.5 %
residual ripple	
• maximum	150 mV
• typical	10 mV
voltage peak	
• maximum	240 mV

• typical	50 mV
display version for normal operation	Green LED for 24 V OK
behavior of the output voltage when switching on	Overshoot of Vout approx. 4 %
response delay maximum	1.5 s
voltage increase time of the output voltage	
• typical	150 ms
output current	
• rated value	2.5 A
• rated range	0 ... 2.5 A; +45 ... +60 °C: Derating 2%/K
supplied active power typical	60 W
bridging of equipment	Yes
number of parallel-switched equipment resources for increasing the power	2
<b>efficiency</b>	
efficiency in percent	85 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	9 W
<b>closed-loop control</b>	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.3 %
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	2 %
setting time	
• load step 10 to 90% typical	0.5 ms
• load step 90 to 10% typical	0.7 ms
<b>protection and monitoring</b>	
design of the overvoltage protection	< 33 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Constant current characteristic
• typical	2.6 A
enduring short circuit current RMS value	
• typical	4 A
<b>safety</b>	
galvanic isolation between input and output	Yes
galvanic isolation	Output voltage: SELV, ES1 (IEC 62368-1), DVC As (IEC 61204-7)
operating resource protection class	Class I
leakage current	
• maximum	3.5 mA
• typical	0.4 mA
protection class IP	IP20
<b>EMC</b>	
standard	
• for emitted interference	EN 55022 Class A
• for mains harmonics limitation	not applicable
• for interference immunity	EN 61000-6-2
<b>standards, specifications, approvals</b>	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
• UKCA marking	Yes
• EAC approval	Yes
• NEC Class 2	No
type of certification	
• CB-certificate	Yes
MTBF at 40 °C	3 153 082 h
<b>standards, specifications, approvals hazardous environments</b>	
certificate of suitability	
• IECEx	No

• ATEX	No
• ULhazloc approval	No
• FM registration	No
<b>standards, specifications, approvals marine classification</b>	
shipbuilding approval	No
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• Det Norske Veritas (DNV)	No
• Lloyds Register of Shipping (LRS)	No
<b>standards, specifications, approvals Environmental Product Declaration</b>	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	252 kg
• during manufacturing	7.7 kg
• during operation	244 kg
• after end of life	0.22 kg
<b>ambient conditions</b>	
ambient temperature	
• during operation	0 ... 60 °C; with natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
<b>connection method</b>	
type of electrical connection	screw terminal
• at input	L, N, PE: 1 screw terminal each for 0.5 ... 2.5 mm <sup>2</sup> single-core/finely stranded
• at output	+, -: 2 screw terminals each for 0.5 ... 2.5 mm <sup>2</sup>
• for auxiliary contacts	-
<b>mechanical data</b>	
width x height x depth of the enclosure	32.5 x 125 x 120 mm
installation width x mounting height	32.5 mm x 225 mm
required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
• DIN-rail mounting	Yes
• S7 rail mounting	No
• wall mounting	No
housing can be lined up	Yes
net weight	0.3 kg
<b>further information internet links</b>	
internet link	
• to website: Industry Mall	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
• to web page: selection aid TIA Selection Tool	<a href="https://www.siemens.com/tstcloud">https://www.siemens.com/tstcloud</a>
• to web page: power supplies	<a href="https://siemens.com/sitop">https://siemens.com/sitop</a>
• to website: CAx-Download-Manager	<a href="https://siemens.com/cax">https://siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>additional information</b>	
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
<b>security information</b>	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected

to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit [www.siemens.com/cybersecurity-industry](http://www.siemens.com/cybersecurity-industry). Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

## Classifications

	Version	Classification
eClass	14	27-04-07-01
eClass	12	27-04-07-01
eClass	9.1	27-04-07-01
eClass	9	27-04-07-01
eClass	8	27-04-90-02
eClass	7.1	27-04-90-02
eClass	6	27-04-90-02
ETIM	10	EC002540
ETIM	9	EC002540
ETIM	8	EC002540
ETIM	7	EC002540
IDEA	4	4130
UNSPSC	15	39-12-10-04

## Approvals Certificates

### General Product Approval



[Manufacturer Declaration](#)

[Declaration of Conformity](#)



[China RoHS](#)

### General Product Approval

### Environment



[Miscellaneous](#)



last modified:

2/5/2026