



SITOP Battery module/24V/7AH

SITOP battery module 24 V/7 Ah with maintenance free sealed lead-acid batteries for SITOP DC UPS module 6 A, 15 A and 40 A

Technical Product Detail Page

<https://i.siemens.com/1P6EP1935-6ME21>

electrical data	
end-of-charge voltage at DC	
• at -10 °C recommended	29 V
• at 0 °C recommended	28.4 V
• at 10 °C recommended	27.8 V
• at 20 °C recommended	27.3 V
• at 30 °C recommended	26.8 V
• at 40 °C recommended	26.6 V
• at 50 °C recommended	26.3 V
output	
battery capacity	7 A·h
output current in buffering mode maximum	30 A
peak current	30 A
charging current maximum	1.75 A
output voltage at DC rated value	24 V
interfaces	
communication function	No
protection and monitoring	
design of short-circuit protection	Battery fuse 20 A/32 V (solid-state circuitry blade-type fuse + support)
design of the overload protection	Valve control
safety	
operating resource protection class	Class III
protection class IP	IP00
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627
• EAC approval	Yes
standards, specifications, approvals hazardous environments	
certificate of suitability	
• ATEX	No
standards, specifications, approvals marine classification	
shipbuilding approval	Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• Det Norske Veritas (DNV)	Yes
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes

global warming potential [CO2 eq]	<ul style="list-style-type: none"> total during manufacturing during operation after end of life 	23.293 kg 12.827 kg 8.167 kg 0.676 kg
ambient conditions		
ambient condition		For storage, mounting and operation of lead-acid batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/EN 50272-2) must be observed. You must ensure that the battery site is sufficiently ventilated. Possible sources of ignition must be at least 50 cm away.
ambient temperature	<ul style="list-style-type: none"> during operation during transport during storage 	-15 ... +50 °C -20 ... +50 °C -20 ... +50 °C
relative temporary capacity loss at 20 °C in a month typical		3 %
service life		
service life of energy storage	<ul style="list-style-type: none"> typical at 20 °C typical at 30 °C typical at 40 °C typical at 50 °C typical 	capacity falls to 80 % of original capacity (according to EUROBAT) 4 a 2 a 1 a 0.5 a
note	Along with the storage and operating temperature, other factors such as the duration of the storage period and the charge status during storage have a decisive influence on the possible useful life. Batteries should therefore be stored as briefly as possible, always fully charged, and within the temperature range 0 to +20 °C.	
connection method		
type of electrical connection	spring-loaded terminals <ul style="list-style-type: none"> for UPS module 1 screw terminal each for 0.08 ... 4 mm ² for + BAT and - BAT	
mechanical data		
width x height x depth of the enclosure	186 x 168 x 121 mm	
installation width x mounting height	206 mm x 188 mm	
fastening method	can be screwed onto flat surface (keyhole mounting for hooking in to M4 screws) <ul style="list-style-type: none"> DIN-rail mounting S7 rail mounting wall mounting No No Yes	
net weight	6 kg	
number of cells	12	
accessories		
product component included	Accessories pack with solid-state circuitry fuse 20 A and 30 A	
further information internet links		
internet link	<ul style="list-style-type: none"> to website: Industry Mall to web page: selection aid TIA Selection Tool to web page: power supplies to website: CAx-Download-Manager to website: Industry Online Support https://mall.industry.siemens.com https://www.siemens.com/tstcloud https://siemens.com/sitop https://www.siemens.com/cax https://support.industry.siemens.com	
additional information		
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	
security information		
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial	

cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Classifications

	Version	Classification
eClass	14	27-05-04-03
eClass	12	27-05-04-03
eClass	9.1	27-05-04-03
eClass	9	27-05-04-03
eClass	8	27-05-04-03
eClass	7.1	27-05-04-03
eClass	6	27-05-04-90
ETIM	10	EC000357
ETIM	9	EC000357
ETIM	8	EC000357
ETIM	7	EC000357
UNSPSC	15	26-11-17-01

Approvals Certificates

General Product Approval

[Manufacturer Declaration](#)

[Declaration of Conformity](#)



[Miscellaneous](#)

Maritime application



[Dangerous goods information](#)

[Transport Information](#)



[Dangerous goods information](#)

[Transport Information](#)

Environment

last modified:

11/25/2025