

Data sheet

6EP3437-8MB00-2CY0



SITOP PSU8600/3AC/24VDC/40A/4X10A PN

SITOP PSU8600 3AC 40 A/4x10 A PN stabilized power supply input: 400-500 V 3 AC output: 24 V DC/40 A/4x 10 A with PN/IE connection web server integrated OPC UA server integrated

Technical Product Detail Page

<https://i.siemens.com/1P6EP3437-8MB00-2CY0>

input	
type of the power supply network	3-phase AC
supply voltage at AC	
• minimum rated value	400 V
• maximum rated value	500 V
• initial value	320 V
• full-scale value	575 V
supply voltage at AC	Derating 320 ... 360 and 530 ... 575 V
wide range input	Yes
buffering time for rated value of the output current in the event of power failure minimum	15 ms
operating condition of the mains buffering	at Vin = 400 V; Prioritized supply of Output 1 in case of power failure selectable via DIP switch
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 400 V	2.75 A
• at rated input voltage 500 V	2.2 A
current limitation of inrush current at 25 °C maximum	14 A
I _{2t} value maximum	2.24 A ² ·s
fuse protection type	none
fuse protection type in the feeder	Required: 3-pole connected miniature circuit breaker 10 ... 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)
output	
voltage curve at output	Controlled, isolated DC voltage
number of outputs	4
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
• at output 2 at DC rated value	24 V
• at output 3 at DC rated value	24 V
• at output 4 at DC rated value	24 V
output voltage adjustable	Yes; via potentiometer or IE/PN interface
adjustable output voltage	4 ... 28 V; Derating > 24 V: 4%/V; max. 240 W per output, max. 960 W overall system
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.2 %
• on slow fluctuation of ohm loading	0.1 %

residual ripple	100 mV
• maximum	
voltage peak	200 mV
• maximum	
display version for normal operation	3-color LED for operating state device; LED for operating mode manual/remote; 4 LEDs for communication PROFINET; 3-color LED per output for operating state output; LED green for parallel operation Output 1 and 2 / 3 and 4
type of signal at output	Relay contact (changeover contact, contact current capacity DC 60 V/0.3 A) for "Operating state OK"
behavior of the output voltage when switching on	No overshoot of Vout (soft start)
response delay maximum	1 s; Without on-delay of the outputs
type of outputs connection	Simultaneous connecting-in of all outputs after device booting or delay time of 25 ms, 100 ms or "load-optimized" for sequential cutting-in of the outputs via DIP switches can be set
voltage increase time of the output voltage	
• maximum	500 ms
output current	
• rated value	40 A
• per output	10 A
• at output 1 rated value	10 A
• at output 2 rated value	10 A
• at output 3 rated value	10 A
• at output 4 rated value	10 A
• rated range	0 ... 40 A; +50 ... +60 °C: Derating 2.5%/K; no derating in connection with expansion module CNX8600 and total load of the outputs at the basic device max. 480 W
supplied active power typical	960 W
parallel switching of outputs	Yes; Parallel circuit Output 1 with 2 or Output 3 with 4 can be selected via DIP switch
bridging of equipment	No
efficiency	
efficiency in percent	93 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	72 W
• during no-load operation maximum	20 W
closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.1 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	0.4 %
setting time	
• maximum	10 ms
protection and monitoring	
design of the overvoltage protection	max. 35 V (max. 500 ms)
property of the output short-circuit proof	Yes
design of short-circuit protection	electronic overload cut-off; optionally constant current operation can be selected for Output 4 via DIP switches
adjustable current response value current of the current-dependent overload release	0.5 ... 10 A
type of response value setting	via potentiometer or IE/PN interface
switching characteristic	
• of the excess current	$I_a > 1.0 \dots < 1.5 \times I_a$ threshold permissible for 5 s; I_a limit ($= 1.5 \times I_a$ threshold) permissible for 200 ms
• of the current limitation	I_a limit ($= 1.5 \times I_a$ threshold) permissible for 5 s, afterwards I_a threshold continuous
overcurrent overload capability	
• in normal operation	Total system overloadable 150% I_a rated to 5 s/min
display version for overload and short circuit	3-color LED for operating state device; 3-color LED per output for operating state output
design of the reset device/resetting mechanism	via sensor per output or IE/PN interface
remote reset function	Non-electrically isolated 24 V input (signal level "high" at > 15 V)
interfaces	

product function communication function	Yes
design of the interface <ul style="list-style-type: none"> design of the interface PROFINET protocol 	Ethernet/PROFINET
protocol is supported <ul style="list-style-type: none"> OPC UA 	Yes
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Safety extra low output voltage V_{out} according to EN 61204-7
operating resource protection class	Class I
leakage current <ul style="list-style-type: none"> maximum 	3.5 mA
protection class IP	IP20
EMC	
standard <ul style="list-style-type: none"> for emitted interference for mains harmonics limitation for interference immunity 	EN 55022 Class B EN 61000-3-2 EN 61000-6-2
standards, specifications, approvals	
certificate of suitability <ul style="list-style-type: none"> CE marking UL approval EAC approval NEC Class 2 SEMI F47 	Yes Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 Yes No Yes
type of certification <ul style="list-style-type: none"> BIS CB-certificate 	Yes; R-41188271 Yes
MTBF at 40 °C	207 612 h
standards, specifications, approvals hazardous environments	
certificate of suitability <ul style="list-style-type: none"> IECEx ATEX ULhazloc approval FM registration 	No No No No
standards, specifications, approvals marine classification	
shipbuilding approval	Yes
Marine classification association <ul style="list-style-type: none"> American Bureau of Shipping Europe Ltd. (ABS) French marine classification society (BV) Det Norske Veritas (DNV) Lloyds Register of Shipping (LRS) 	Yes No Yes No
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq] <ul style="list-style-type: none"> total during manufacturing during operation after end of life 	2 295.1 kg 41 kg 2 252.9 kg 0.59 kg
ambient conditions	
ambient temperature <ul style="list-style-type: none"> during operation during transport during storage 	-25 ... +60 °C; with natural convection -40 ... +85 °C -40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection <ul style="list-style-type: none"> at input at output 	Plug-in terminals with screwed connection L1, L2, L3, PE: Plug-in terminal with 1 screwed connection each for 0.2 ... 4 mm ² single-wire / fine stranded 1, 2, 3, 4: Two plug-in terminals (1, 2 and 3, 4) with 2 screwed connections

• for auxiliary contacts	each for 0.2 ... 2.5 mm ² ; 0 V: Plug-in terminal with 3 screwed connections for 0.2 ... 10 mm ² (max. 6 mm ² with ferrule)		
• for signaling contact	RST (Reset): Plug-in terminal (together with alarm signal) with 1 screwed connection for 0.2 ... 1.5 mm ²		
removable terminal at input	11, 12, 14 (alarm signal): Plug-in terminal (together with Reset) with 1 screwed connection each for 0.2 ... 1.5 mm ²		
removable terminal at output			
design of the interface for communication	PROFINET/Ethernet: two RJ45 sockets (2-port switch)		
suitability for interaction modular system	Yes		
mechanical data			
width x height x depth of the enclosure	125 x 125 x 150 mm		
installation width x mounting height	125 mm x 225 mm		
required spacing			
• top	50 mm		
• bottom	50 mm		
• left	0 mm		
• right	0 mm		
fastening method	Snaps onto DIN rail EN 60715 35x15		
• DIN-rail mounting	Yes		
• S7 rail mounting	No		
• wall mounting	No		
housing can be lined up	Yes		
net weight	2.6 kg		
accessories			
electrical accessories	Expansion modules CNX8600, buffer modules BUF8600, module UPS8600		
mechanical accessories	Device identification label 20 mm x 7 mm, TI-grey 3RT2900-1SB20		
further information internet links			
internet link			
• to website: Industry Mall	https://mall.industry.siemens.com		
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud		
• to web page: power supplies	https://siemens.com/sitop		
• to website: CAx-Download-Manager	https://siemens.com/cax		
• to website: Industry Online Support	https://support.industry.siemens.com		
additional information			
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)		
security information			
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert . (V4.7)		
Classifications			
		Version	Classification
	eClass	14	27-04-07-01
	eClass	12	27-04-07-01
	eClass	9.1	27-04-07-01
	eClass	9	27-04-07-01

eClass	8	27-04-90-02
eClass	7.1	27-04-90-02
eClass	6	27-04-90-02
ETIM	10	EC002540
ETIM	9	EC002540
ETIM	8	EC002540
ETIM	7	EC002540
IDEA	4	4130
UNSPSC	15	39-12-10-04

Approvals Certificates

General Product Approval



[Manufacturer Declaration](#)

[Declaration of Conformity](#)



[China RoHS](#)

General Product Approval



[Miscellaneous](#)

[BIS CRS](#)



Maritime application

last modified:

11/14/2025